

GC/GF Series Quartz Crystal Legacy 49SMLB Series 11.5 x 4.5 x 4.0mm & 11.5 x 4.5 x 3.0mm

## **Quartz Crystal Metal Can (SMD)**





11.5 x 4.5 x 4.0mm SMD

### **Product Features**

- Standard: 4.0mm Max height GC Series
- Low profile: 3.0mm Max height GF Series
- Available on tape & reel, 24mm tape, 1000 units per reel
- Pb-free and RoHS/Green compliant.

### **Product Description**

The crystals are miniature AT or BT cut strip resonators housed in low profile packages for surface mounting. The parts utilize a proven, low-cost, metal package technology with a precision molded base and universal contact configuration.

### **Applications**

- Set-Top Box/Multimedia
- Clock/VCXO Multiplier
- Network Adapter Cards
- Modems
- Microcontrollers and Processors
- Remote control devices

### **Frequency Range:**

- •3.2 to 40.000 MHz, AT Fundamental
- •30.0 to 54.000 MHz, AT 3rd Overtone
- •40.0 to 54.000 MHz, BT Fundamental

### Characteristics at 25°C ±2°C:

- Frequency Calibration Tolerance: ±30ppm
- •Load Capacitance: 8 to 32pF or Series Resonance
- Effective Series Resistance (ESR):
  - Fundamental: 20 to 200Ω max depending on frequencey 3rd Overtone: 40 to 100Ω max depending on frequency
- Drive Level:  $100\mu$ W typ. ( $500\mu$ W Max)
- •Shunt Capacitance: 7pF Max

### **Temperature Range:**

- •Operating: -20 to +70°C or -40 to +85°C
- •Storage: -55 to +125°C

### **Temperature Stability:**

- ±10, ±20, ±30ppm (-20 to +70°C) AT Cut
- ±30, ±50 ppm (-40 to +85°C) AT Cut
- •0 to -100ppm (-20 to +70°C) BT Cut

### Aging @ 25°C, first year:

•±5ppm Max

### **Reflow Temperature:**

•260°C Max, 10 seconds Max (RoHS package)

SaRonix-eCera™ is a Pericom® Semiconductor company • US: +1-408-435-0800 TW: +886-3-4518888

14-0002



• www.saronix-ecera.com

1

## Quartz Crystal Metal Can (SMD) GC GF

### GC/GF Series Quartz Crystal Legacy 49SMLB Series


### **Mechanical:**

- •Shock: JESD22-B104 Condition B
- •Solderability: MIL-STD-883, Method 2003 (non-RoHS package)
- •Solderability: J-STD-002( RoHS package )
- •Terminal Strength: MIL-STD-883 Method 2004
- •Vibration: JESD22-B103
- •Solvent Resistance: JESD22-B107
- •Resistance to Soldering Heat: MIL-STD-202, Method 210, Condition I or J (Non-RoHS package)
- Resistance to Soldering Heat: J-STD-020C Table 5-2 Pb-free devices (3 cycles max) (RoHS package)

### **Environmental:**

- •Gross Test Leak: JESD22-A109, Condition C
- Fine Test Leak: JESD22-A109, Condition A1
- •Moisture Resistance: JESD22-A113
- •Insulation Resistance: 500 MΩ min (100 VDC)


### **Part Ordering Information:**



Following the above format, Saronix-eCera part numbers will be assigned upon confirmation of exact customer requirements.

### **Legacy Ordering Information - For Reference Only:**

14-0002



All specifications are subject to change without notice. GC/GF REV2014\_JAN21 2


Downloaded from Arrow.com.


Enabling Serial Connectivity

# Quartz Crystal Metal Can (SMD) GC GF


### GC/GF Series Quartz Crystal Legacy 49SMLB Series


### **Mechanical Drawings: GC Series**





### Mechanical Drawings: GF Series (Low Profile)





SaRonix-eCera™ is a Pericom® Semiconductor company • US: +1-408-435-0800 TW: +886-3-4518888 • www.saronix-ecera.com



14-0002