





REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	YCH 06/20/12'		



RECOMMEND PCB LAYOUT  
TOLERANCE=±0.05mm



**NOTES:**

**1.Materials:**

1.1. Insulator: High Temperature ,UL94 V-0 Rated, RoHS,REACH compliance.

1.2. Contact: Copper Alloy, Plating Matt Tin .

**2.Specifications:**

2.1. Temperature Range: -35~+105°C.

2.2. Contact Resistance: 20mΩ maximum.

2.3. Insulation Resistance: 1000MΩ minimum.

2.4. Voltage Rating: 320V AC/DC.

2.5. Current Rating: 9A max per pin.

2.6. Application wire range:

1.single solid wire: 0.2-0.75mm².

2.stranded type wire: 24-18AWG.

2.7. Resistance to soldering heat: 260°C,3-5seconds.

**3. Product Number Code:**

DS1137-03 - X X X X X

Packing Type  
R: Tape On Reel.

Pin plating  
6: Full matt tin.

Housing Color  
A: Gray

Connector Type  
F: Female

No. of positions  
01: 1p  
02: 2p  
03: 3p

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	4.00mm LED Series terminal block SMT Type				
X.	±0.60	X.	±5°	UNITS	mm						
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1137-03 SERIES				
.XX	±0.25	.XX	±2°								
DRAWING TYPE		CUSTOMER			晨翔电子有限公司 <b>CONNFLY CONNFLY ELECTRONIC CO. LTD</b>						
SCALE		1:1	SHEET							1 OF 1	
DRAWING NO.		C-DS1137-03-XXXXX									

TEL:86-574-63508787  
 Fax:86-574-63510817  
 E-mail:sale@zhenqin.com.cn  
 Http://www.connfly.com