

Chip beads
For general signal line
MMZ series



MMZ1608 type



FEATURES

- Noise reduction solution for general signal line.
- Various frequency characteristics with 8 materials of different features for countermeasures against everything from general signals to high-speed signals.
- Operating temperature range: -55 to +125°C

APPLICATION

- Noise removal for mobile devices such as smartphones and tablet terminals, and various modules.
- Noise removal for PCs and recorders, household appliances such as STBs, smart grids, and industrial equipment.

PART NUMBER CONSTRUCTION

| | | | | | | |
|-------------|--|---------------|-------------------------------------|---------------------|-----------------|---------------|
| MMZ | 1608 | S | 121 | A | T | A00 |
| Series name | LxWxT dimensions 1.6x0.8x0.6 mm 1.6x0.8x0.8 mm | Material name | Impedance (Ω) at 100MHz | Characteristic type | Packaging style | Internal code |


CHARACTERISTICS SPECIFICATION TABLE

| Impedance [100MHz] (Ω) | DC resistance (Ω)max. | Rated current (mA)max. | Thickness T (mm) | Part No. | |
|---------------------------------------|-----------------------------------|---------------------------|---------------------|----------|----------------------------------|
| 120 | $\pm 25\%$ | 0.15 | 600 | 0.6 | MMZ1608B121CTAH0 |
| 220 | $\pm 25\%$ | 0.25 | 500 | 0.6 | MMZ1608B221CTAH0 |
| 300 | $\pm 25\%$ | 0.25 | 500 | 0.6 | MMZ1608B301CTAH0 |
| 470 | $\pm 25\%$ | 0.30 | 500 | 0.6 | MMZ1608B471CTAH0 |
| 600 | $\pm 25\%$ | 0.40 | 500 | 0.6 | MMZ1608B601CTAH0 |
| 1000 | $\pm 25\%$ | 0.60 | 300 | 0.8 | MMZ1608B102CTA00 |
| 15 | $\pm 25\%$ | 0.05 | 1500 | 0.8 | MMZ1608R150ATA00 |
| 30 | $\pm 25\%$ | 0.05 | 1500 | 0.8 | MMZ1608R300ATA00 |
| 60 | $\pm 25\%$ | 0.10 | 800 | 0.8 | MMZ1608R600ATA00 |
| 120 | $\pm 25\%$ | 0.18 | 500 | 0.8 | MMZ1608R121ATA00 |
| 300 | $\pm 25\%$ | 0.25 | 500 | 0.8 | MMZ1608R301ATA00 |
| 470 | $\pm 25\%$ | 0.30 | 500 | 0.8 | MMZ1608R471ATA00 |
| 600 | $\pm 25\%$ | 0.40 | 500 | 0.8 | MMZ1608R601ATA00 |
| 1000 | $\pm 25\%$ | 0.50 | 400 | 0.8 | MMZ1608R102ATA00 |

Measurement equipment

| Measurement item | Product No. | Manufacturer |
|------------------|---------------|-----------------------|
| Impedance | E4991A+16192A | Keysight Technologies |
| DC resistance | Type-7556 | Yokogawa |

* Equivalent measurement equipment may be used.



MMZ1608 type

CHARACTERISTICS SPECIFICATION TABLE

| Impedance [100MHz] (Ω) | | DC resistance (Ω)max. | Rated current (mA)max. | Thickness T (mm) | Part No. |
|---------------------------------------|-------------|-----------------------------------|---------------------------|---------------------|----------------------------------|
| Tolerance | | | | | |
| 40 | ±25% | 0.10 | 600 | 0.8 | MMZ1608S400ATA00 |
| 80 | ±25% | 0.15 | 500 | 0.8 | MMZ1608S800ATA00 |
| 120 | ±25% | 0.15 | 500 | 0.8 | MMZ1608S121ATA00 |
| 180 | ±25% | 0.20 | 500 | 0.8 | MMZ1608S181ATA00 |
| 220 | ±25% | 0.20 | 500 | 0.8 | MMZ1608S221ATA00 |
| 300 | ±25% | 0.30 | 500 | 0.8 | MMZ1608S301ATA00 |
| 470 | ±25% | 0.30 | 500 | 0.8 | MMZ1608S471ATA00 |
| 600 | ±25% | 0.35 | 500 | 0.8 | MMZ1608S601ATA00 |
| 1000 | ±25% | 0.50 | 400 | 0.8 | MMZ1608S102ATA00 |
| 2000 | ±25% | 0.90 | 200 | 0.8 | MMZ1608S202ATA00 |
| 15 | ±25% | 0.05 | 1500 | 0.8 | MMZ1608Y150BTA00 |
| 30 | ±25% | 0.05 | 1500 | 0.8 | MMZ1608Y300BTA00 |
| 60 | ±25% | 0.15 | 500 | 0.8 | MMZ1608Y600BTA00 |
| 120 | ±25% | 0.20 | 500 | 0.8 | MMZ1608Y121BTA00 |
| 220 | ±25% | 0.30 | 500 | 0.8 | MMZ1608Y221BTA00 |
| 300 | ±25% | 0.30 | 500 | 0.8 | MMZ1608Y301BTA00 |
| 470 | ±25% | 0.35 | 500 | 0.8 | MMZ1608Y471BTA00 |
| 600 | ±25% | 0.40 | 500 | 0.8 | MMZ1608Y601BTA00 |
| 750 | ±25% | 0.45 | 500 | 0.8 | MMZ1608Y751BTA00 |
| 1000 | ±25% | 0.50 | 400 | 0.8 | MMZ1608Y102BTA00 |
| 1500 | ±25% | 0.60 | 300 | 0.8 | MMZ1608Y152BTA00 |
| 1800 | ±25% | 0.80 | 200 | 0.8 | MMZ1608A182BTA00 |
| 2200 | ±25% | 0.80 | 200 | 0.8 | MMZ1608A222BTA00 |
| 2500 | ±25% | 0.80 | 200 | 0.8 | MMZ1608A252BTA00 |
| 120 | ±25% | 0.30 | 500 | 0.8 | MMZ1608Q121BTA00 |
| 220 | ±25% | 0.40 | 500 | 0.8 | MMZ1608Q221BTA00 |
| 330 | ±25% | 0.50 | 400 | 0.8 | MMZ1608Q331BTA00 |
| 470 | ±25% | 0.70 | 300 | 0.8 | MMZ1608Q471BTA00 |
| 600 | ±25% | 0.80 | 200 | 0.8 | MMZ1608Q601BTA00 |
| 1000 | ±25% | 1.00 | 200 | 0.8 | MMZ1608Q102BTA00 |
| 5 | ±2 Ω | 0.05 | 700 | 0.8 | MMZ1608D050CTA00 |
| 10 | ±5 Ω | 0.10 | 500 | 0.6 | MMZ1608D100CTA00 |
| 22 | ±25% | 0.20 | 500 | 0.6 | MMZ1608D220CTA00 |
| 50 | ±25% | 0.25 | 500 | 0.6 | MMZ1608D500CTA00 |
| 80 | ±25% | 0.30 | 500 | 0.6 | MMZ1608D800CTA00 |
| 80 | ±25% | 0.30 | 500 | 0.8 | MMZ1608D800BTA00 |
| 120 | ±25% | 0.30 | 400 | 0.6 | MMZ1608D121CTA00 |
| 120 | ±25% | 0.30 | 400 | 0.8 | MMZ1608D121BTA00 |
| 240 | ±25% | 0.60 | 300 | 0.8 | MMZ1608D241CTA00 |
| 300 | ±25% | 0.70 | 300 | 0.8 | MMZ1608D301BTA00 |
| 3typ. | | 0.05 | 700 | 0.8 | MMZ1608F030BTA00 |
| 47 | ±25% | 0.40 | 500 | 0.8 | MMZ1608F470BTA00 |
| 75 | ±25% | 0.55 | 300 | 0.8 | MMZ1608F750BTA00 |
| 120 | ±25% | 0.75 | 200 | 0.8 | MMZ1608F121BTA00 |

Measurement equipment


| Measurement item | Product No. | Manufacturer |
|------------------|---------------|-----------------------|
| Impedance | E4991A+16192A | Keysight Technologies |
| DC resistance | Type-7556 | Yokogawa |

* Equivalent measurement equipment may be used.


MMZ1608 type

Z VS. FREQUENCY CHARACTERISTICS (BY SERIES)


MMZ1608B series




MMZ1608R series




MMZ1608S series




MMZ1608Y series




MMZ1608A series




MMZ1608Q series



MMZ1608D series



MMZ1608F series




⚠ Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (3/9)
Please note that the contents may change without any prior notice due to reasons such as upgrading.


MMZ1608 type

Z, X, R VS. FREQUENCY CHARACTERISTICS


MMZ1608B121CTAH0




MMZ1608B221CTAH0




MMZ1608B301CTAH0




MMZ1608B471CTAH0




MMZ1608B601CTAH0




MMZ1608B102CTA00




MMZ1608R150ATA00




MMZ1608R300ATA00




MMZ1608R600ATA00




MMZ1608R121ATA00




MMZ1608R301ATA00




MMZ1608R471ATA00




MMZ1608R601ATA00



MMZ1608R102ATA00



MMZ1608S400ATA00



⚠ Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (4/9)
Please note that the contents may change without any prior notice due to reasons such as upgrading.


20200717

beads_commercial_signal_mmz1608_en


MMZ1608 type

Z, X, R VS. FREQUENCY CHARACTERISTICS


MMZ1608S800ATA00




MMZ1608S121ATA00




MMZ1608S181ATA00




MMZ1608S221ATA00




MMZ1608S301ATA00




MMZ1608S471ATA00




MMZ1608S601ATA00




MMZ1608S102ATA00




MMZ1608S202ATA00




MMZ1608Y150BTA00




MMZ1608Y300BTA00




MMZ1608Y600BTA00




MMZ1608Y121BTA00



MMZ1608Y221BTA00



MMZ1608Y301BTA00




⚠ Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (5/9)
Please note that the contents may change without any prior notice due to reasons such as upgrading.


MMZ1608 type

Z, X, R VS. FREQUENCY CHARACTERISTICS


MMZ1608Y471BTA00




MMZ1608Y601BTA00




MMZ1608Y751BTA00




MMZ1608Y102BTA00




MMZ1608Y152BTA00




MMZ1608A182BTA00




MMZ1608A222BTA00




MMZ1608A252BTA00




MMZ1608Q121BTA00




MMZ1608Q221BTA00




MMZ1608Q331BTA00




MMZ1608Q471BTA00



MMZ1608Q601BTA00



MMZ1608Q102BTA00



⚠ Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (6/9)
Please note that the contents may change without any prior notice due to reasons such as upgrading.


20200717

beads_commercial_signal_mmz1608_en


MMZ1608 type

Z, X, R VS. FREQUENCY CHARACTERISTICS


MMZ1608D050CTA00




MMZ1608D100CTAH0




MMZ1608D220CTAH0




MMZ1608D500CTAH0




MMZ1608D800CTAH0




MMZ1608D800BTA00




MMZ1608D121CTAH0




MMZ1608D121BTA00




MMZ1608D241CTA00




MMZ1608D301BTA00




MMZ1608F030BTA00




MMZ1608F470BTA00



MMZ1608F750BTA00




MMZ1608F121BTA00




MMZ1608 type

SHAPE & DIMENSIONS




PACKAGING STYLE


REEL DIMENSIONS




RECOMMENDED LAND PATTERN




TAPE DIMENSIONS



RECOMMENDED REFLOW PROFILE



| Type | A | B | K |
|---------|---------|---------|---------|
| MMZ1608 | 1.1±0.2 | 1.9±0.2 | 1.1max. |



PACKAGE QUANTITY

| | |
|------------------|----------------|
| Package quantity | 4,000 pcs/reel |
|------------------|----------------|

TEMPERATURE RANGE, INDIVIDUAL WEIGHT

| Type | Operating temperature range | Storage temperature range* | Individual weight |
|---------|-----------------------------|----------------------------|-------------------|
| t=0.6mm | -55 to +125°C | -55 to +125°C | 3 mg |
| t=0.8mm | -55 to +125°C | -55 to +125°C | 4 mg |

* The storage temperature range is for after the assembly.

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

REMINDERS

- The storage period is within 12 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 10 to 75% RH or less).
If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
- Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
- Before soldering, be sure to preheat components.
The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C.
- Soldering corrections after mounting should be within the range of the conditions determined in the specifications.
If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.
- When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.
- Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.
- Carefully lay out the coil for the circuit board design of the non-magnetic shield type.
A malfunction may occur due to magnetic interference.
- Use a wrist band to discharge static electricity in your body through the grounding wire.
- Do not expose the products to magnets or magnetic fields.
- Do not use for a purpose outside of the contents regulated in the delivery specifications.
- The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.
The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.
If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions set forth in the each catalog, please contact us.

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.