




Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**
 Die Sets Type: **Removable/Interchangeable**
 Specification Type: **TE Product Specification (114-)**
 TE Certification: **Cannot be Certified**
 Tooling Type: **SDE Crimp Die Set**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Cannot be Certified
Tooling Type	SDE Crimp Die Set

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233)



Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-T4827-T273
TIMER, RECEPTACLE AND TAB



TE Part # 2362810-1
SDE CRIMP HAND TOOL FRAME W /O DIES



TE Part # 2390276-1
SDE F JR PWR TIMER 0.50-1.00mm2 ASSY



TE Part # 2-964300-2
TAB A 2.8x0.8 CONTACT CF SWS Ag ASSY



TE Part # 964285-2
JPT A REC 2.8 Contact SRC Sn (LP)



TE Part # 4-964299-1
TAB A 2.8x0.8 CONTACT CS2 SWS Sn (LP)



TE Part # 4-964300-1
TAB A 2.8x0.8 CONTACT SWS



TE Part # 964285-4
JPT A REC 2.8 Contact SRC AU (LP)



TE Part # 964285-1
JPT A REC 2.8 Contact SRC Sn (LP)


Customers Also Bought



TE Part #HDP26-24-16SE
PLG, 16P, BLK, E, 12, S



TE Part #6-1579007-0
EXTRACTION TOOL



TE Part #0411-354-1605
EXT TOOL, SIZE 16, 16-18 AWG, N,
BRN



TE Part #4-1579007-3
EXTRACTION TOOL KIT



TE Part #1-1579018-4
EXTRACTION TOOL



TE Part #342184-1
12-10 F.E.P.G. RING TERMINAL



TE Part #2063525-1
SDE MQS 0.5-0.75mm2 ASSY



TE Part #2063525-2
SDE MQS 0.5-0.75mm2 DIE SET



TE Part #2362810-1
SDE CRIMP HAND TOOL FRAME W
/O DIES



TE Part #2390277-2
SDE F JR PWR TIMER 1.50-2.50mm2
DIE SET

Documents

Datasheets & Catalog Pages

Bottoming Dies

English

SDE Crimp Commercial Tool System

English

Instruction Sheets

Instruction Sheet (U.S.)

English