

## Specifications

- Input Voltage: 12Vdc
- Input Voltage(limits): 13.5Vdc
- Output Voltage: 5Vdc
- Output Current(maximum): 600mA
- Transmitter Coil Inductance: 30uH
- Transmit-receive distance: 1-20mm
- Transmitter : 17\*12\*4mm
- Receiver: 24\*10\*3mm
- Coil Diameter: 38mm
- Coil Height: 2mm