


# KERN DAB200-2



Moisture analyser which is particularly easy to use - now also as a version with [d] = 10 mg, ideal for recurring rapid tests



## Measuring system

Adjustment options:	External calibration
Eccentric loading at 1/3 [Max]:	50 mg
Linearity:	30 mg
Load cell connection:	4-wire
Measuring capacity [Max]:	199 °C
Minimum weight (USP):	20 g
Readability (moisture):	0,050 %
Readability [d]:	10 mg
Repeatability:	10 mg
Resolution:	20000
Stabilisation time under laboratory conditions:	3 s
Tare range:	200 g
Warm up time:	30 min
Weighing capacity [Max]:	200 g
Weighing system:	Strain gauge
Weighing units:	% Trockenmasse g % Feuchte

## Display

Display digit height (large):	1,400 cm
Display digit height (small):	6 mm

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	5 °C
Minimum humidity:	5 %

## Power supply

Battery:	no battery
Input voltage:	230 V AC 50 Hz
Mains adapter/adapter included:	EURO

## Services (optional)

Adjustment at the location of installation: 961-247

DAkkS Certificate:	963-127
Factory calibration certificate (temperature):	964-305

## Category

Brand:	KERN
Product Group:	Moisture analyser

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	490 x 350 x 360 mm
Gross weight:	7,100 kg
Net weight:	4,820 kg
Shipping method:	Parcel service

## Construction

Level indicator:	yes
Material weighing plate:	Aluminium dish
Overall dimensions mounted (WxDxH):	240 x 365 x 180 mm
Revolving screw feet:	yes
Weighing surface (d):	92

## Piktogramme

### STANDARD



### OPTION

