


50 mA, 100 mA and 150 mA CMOS LDOs with Shutdown and Reference Bypass

- Low Supply Current (50 µA, typical)
- Low Dropout Voltage
- Choice of 50 mA (TC1014), 100 mA (TC1015) and 150 mA (TC1185) Output
- High Output Voltage Accuracy
- Standard or Custom Output Voltages
- · Power-Saving Shutdown Mode
- Reference Bypass Input for Ultra Low-Noise
 Operation
- Overcurrent and Overtemperature Protection
- Space-Saving 5-Pin SOT-23 Package
- · Pin-Compatible Upgrades for Bipolar Regulators
- Standard Output Voltage Options:
- 1.8V, 2.5V, 2.6V, 2.7V, 2.8V, 2.85V, 3.0V,
 3.3V, 3.6V, 4.0V, 5.0V

Applications:

- · Battery-Operated Systems
- Portable Computers
- Medical Instruments
- Instrumentation
- Cellular/GSM/PHS Phones
- Linear Post-Regulator for SMPS
- Pagers

Typical Application




The TC1014/TC1015/TC1185 are high accuracy (typically $\pm 0.5\%$) CMOS upgrades for older (bipolar) Low Dropout Regulators (LDOs) such as the LP2980. Designed specifically for battery-operated systems, the devices' CMOS construction eliminates wasted ground current, significantly extending battery life. Total supply current is typically 50 µA at full load (20 to 60 times lower than in bipolar regulators).

The devices' key features include ultra low-noise operation (plus optional Bypass input), fast response to step changes in load, and very low dropout voltage, typically 85 mV (TC1014), 180 mV (TC1015), and 270 mV (TC1185) at full-load. Supply current is reduced to 0.5 μ A (max) and V_{OUT} falls to zero when the shutdown input is low. The devices incorporate both overtemperature and overcurrent protection.

The TC1014/TC1015/TC1185 are stable with an output capacitor of only 1 μ F and have a maximum output current of 50 mA, 100 mA and 150 mA, respectively. For higher output current regulators, please see the TC1107 (DS21356), TC1108 (DS21357), TC1173 (DS21362) (I_{OUT} = 300 mA) data sheets.

Package Type



© 2007 Microchip Technology Inc.

1.0 ELECTRICAL **CHARACTERISTICS**

Absolute Maximum Ratings†

Input Voltage	6.5V
Output Voltage	(-0.3V) to (V _{IN} + 0.3V)
Power DissipationInter	mally Limited (Note 7)
Maximum Voltage on Any Pin	V _{IN} +0.3V to -0.3V
Operating Temperature Range	40°C < T_J < 125°C
Storage Temperature	65°C to +150°C

+ Notice: Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions above those indicated in the operation sections of the specifications is not implied. Exposure to Absolute Maximum Rating conditions for extended periods may affect device reliability.

TC1014/TC1015/TC1185 ELECTRICAL SPECIFICATIONS

Electrical Specifications: $V_{IN} = V_R + 1V$, $I_L = 100 \mu$ A, $C_L = 1.0 \mu$ F, $\overline{SHDN} > V_{IH}$, $T_A = +25^{\circ}$ C, unless otherwise noted. Boldface type specifications apply for junction temperatures of -40°C to +125°C.

Dolutace type specifications a							
Parameter	Symbol	Min	Тур	Мах	Units	Device	Test Conditions
Input Operating Voltage	V _{IN}	2.7	—	6.0	V	—	Note 1
Maximum Output Current	I _{OUTMAX}	50 100 150			mA	TC1014 TC1015 TC1185	
Output Voltage	V _{OUT}	V _R – 2.5%	$V_R \pm 0.5\%$	V _R + 2.5%	V	_	Note 2
V _{OUT} Temperature Coefficient	TCV _{OUT}	_	20 40		ppm/°C	—	Note 3
Line Regulation	ΔV _{OUT} / ΔV _{IN}	—	0.05	0c.35	%	_	$(V_R + 1V) \le V_{IN} \le 6V$
Load Regulation	ΔV _{OUT} / V _{OUT}		0.5 0.5	2 3	%	TC1014; TC1015 TC1185	$I_{L} = 0.1 \text{ mA to } I_{OUTMAX}$ $I_{L} = 0.1 \text{ mA to } I_{OUTMAX}$ (Note 4)
Dropout Voltage	V _{IN} -V _{OUT}	 	2 65 85 180 270	 120 250 400	mV		I _L = 100 μA I _L = 20 mA I _L = 50 mA I _L = 100 mA I _L = 150 mA (Note 5)
Supply Current (Note 8)	I _{IN}	_	50	80	μA	—	$\overline{\text{SHDN}} = V_{\text{IH}}, I_{\text{L}} = 0$
Shutdown Supply Current	I _{INSD}	_	0.05	0.5	μA	—	SHDN = 0V
Power Supply Rejection Ratio	PSRR	—	64	_	dB	—	F _{RE} ≤ 1 kHz
Output Short Circuit Current	I _{OUTsc}	—	300	450	mA	—	V _{OUT} = 0V
Thermal Regulation	$\Delta V_{OUT} / \Delta P_D$	—	0.04	_	V/W	—	Notes 6, 7
Thermal Shutdown Die Temperature	T _{SD}	—	160	_	°C	—	
Thermal Shutdown Hysteresis	ΔT_{SD}	_	10	_	°C	_	

Note 1: The minimum V_{IN} has to meet two conditions: $V_{IN} \ge 2.7V$ and $V_{IN} \ge V_R + V_{DROPOUT}$.

 V_R is the regulator output voltage setting. For example: V_R = 1.8V, 2.5V, 2.6V, 2.7V, 2.8V, 2.85V, 3.0V, 3.3V, 3.6V, 4.0V, 5.0V. 2: 3:

TC V_{OUT} = $(V_{OUTMAX} - V_{OUTMIN}) \times 10^6$

 $V_{OUT} x \Delta T$

- 4: Regulation is measured at a constant junction temperature using low duty cycle pulse testing. Load regulation is tested over a load range from 1.0 mA to the maximum specified output current. Changes in output voltage due to heating effects are covered by the thermal regulation specification.
- 5: Dropout voltage is defined as the input to output differential at which the output voltage drops 2% below its nominal value at a 1V differential.
- Thermal Regulation is defined as the change in output voltage at a time T after a change in power dissipation is applied, excluding load 6: or line regulation effects. Specifications are for a current pulse equal to ILMAX at VIN = 6V for T = 10 ms.
- 7: The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the thermal resistance from junction-to-air (i.e., T_A , T_J , θ_{JA}). Exceeding the maximum allowable power dissipation causes the device to initiate thermal shutdown. Please see Section 5.0 "Thermal Considerations" for more details.
- 8: Apply for Junction Temperatures of -40°C to +85°C.

TC1014/TC1015/TC1185 ELECTRICAL SPECIFICATIONS (CONTINUED)

Electrical Specifications: $V_{IN} = V_R + 1V$, $I_L = 100 \ \mu$ A, $C_L = 1.0 \ \mu$ F, $\overline{SHDN} > V_{IH}$, $T_A = +25^{\circ}$ C, unless otherwise noted. Boldface type specifications apply for junction temperatures of -40°C to +125°C.

,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,		-					
Parameter	Symbol	Min	Тур	Max	Units	Device	Test Conditions
Output Noise	eN		600	_	nV/√Hz		$I_L = I_{OUTMAX},$ F = 10 kHz 470 pF from Bypass to GND
SHDN Input High Threshold	V _{IH}	45	_	_	%V _{IN}		V _{IN} = 2.5V to 6.5V
SHDN Input Low Threshold	V _{IL}			15	%V _{IN}		V _{IN} = 2.5V to 6.5V

Note 1: The minimum V_{IN} has to meet two conditions: V_{IN} \ge 2.7V and V_{IN} \ge V_R + V_{DROPOUT}.

2: V_R is the regulator output voltage setting. For example: V_R = 1.8V, 2.5V, 2.6V, 2.7V, 2.8V, 2.85V, 3.0V, 3.3V, 3.6V, 4.0V, 5.0V.

3: TC $V_{OUT} = (V_{OUTMAX} - V_{OUTMIN})x \ 10^6$

4: Regulation is measured at a constant junction temperature using low duty cycle pulse testing. Load regulation is tested over a load range from 1.0 mA to the maximum specified output current. Changes in output voltage due to heating effects are covered by the thermal regulation specification.

5: Dropout voltage is defined as the input to output differential at which the output voltage drops 2% below its nominal value at a 1V differential.

6: Thermal Regulation is defined as the change in output voltage at a time T after a change in power dissipation is applied, excluding load or line regulation effects. Specifications are for a current pulse equal to I_{LMAX} at V_{IN} = 6V for T = 10 ms.

7: The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the thermal resistance from junction-to-air (i.e., T_A, T_J, θ_{JA}). Exceeding the maximum allowable power dissipation causes the device to initiate thermal shutdown. Please see Section 5.0 "Thermal Considerations" for more details.

8: Apply for Junction Temperatures of -40°C to +85°C.

TEMPERATURE CHARACTERISTICS


Electrical Specifications: $V_{IN} = V_R + 1V$, $I_L = 100 \ \mu$ A, $C_L = 1.0 \ \mu$ F, $\overline{SHDN} > V_{IH}$, $T_A = +25^{\circ}$ C, unless otherwise noted. Boldface type specifications apply for junction temperatures of -40°C to +125°C.


Boldiace type specifications apply for junction	Boldiace type specifications apply for junction temperatures of -40 C to +125 C.					
Parameters	Sym	Min	Тур	Max	Units	Conditions
Temperature Ranges:						
Extended Temperature Range	T _A	-40	—	+125	°C	
Operating Temperature Range	T _A	-40	—	+125	°C	
Storage Temperature Range	T _A	-65	-	+150	°C	
Thermal Package Resistances:						
Thermal Resistance, 5L-SOT-23	θ_{JA}	_	256	_	°C/W	


2.0 TYPICAL PERFORMANCE CURVES

Note: The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.

Note: Unless otherwise specified, all parts are measured at temperature = +25°C.







Dropout Voltage vs.

FIGURE 2-2: Temperature.




FIGURE 2-3: Voltage (V_{IN}).

Ground Current vs. Input




FIGURE 2-4: Temperature.

Dropout Voltage vs.




FIGURE 2-5: Temperature.

Dropout Voltage vs.





FIGURE 2-6: Voltage (V_{IN}).

Ground Current vs. Input

Note: Unless otherwise specified, all parts are measured at temperature = +25°C.



Voltage (V_{IN}).




FIGURE 2-8: Output Voltage (V_{OUT}) vs. Input Voltage (V_{IN}).




FIGURE 2-9: Temperature.

Output Voltage (V_{OUT}) vs.




FIGURE 2-10: Output Voltage (V_{OUT}) vs. Input Voltage (V_{IN}).




FIGURE 2-11: Temperature.

Output Voltage (V_{OUT}) vs.

Note: Unless otherwise specified, all parts are measured at temperature = +25°C.







FIGURE 2-12:












FIGURE 2-14: Temperature.

Output Voltage (V_{OUT}) vs.




FIGURE 2-15:

I_{GND} vs. Temperature.




FIGURE 2-16: AC Characteristics.




FIGURE 2-17: Measure Rise Time of 3.3V with Bypass Capacitor.




FIGURE 2-18: Measure Fall Time of 3.3V with Bypass Capacitor.




FIGURE 2-19: Measure Rise Time of 3.3V without Bypass Capacitor.




FIGURE 2-20: Measure Fall Time of 3.3V without Bypass Capacitor.




FIGURE 2-21: Measure Rise Time of 5.0V with Bypass Capacitor.




FIGURE 2-22: Measure Fall Time of 5.0V with Bypass Capacitor.




FIGURE 2-23: Measure Rise Time of 5.0V without Bypass Capacitor.







FIGURE 2-24: Measure Fall Time of 5.0V without Bypass Capacitor.














FIGURE 2-27: Load Regulation of 3.3V LDO.



LDO.

Load Regulation of 3.3V








FIGURE 2-30: Thermal Shutdown Response of 5.0V LDO.

3.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in Table 3-1.

Pin No. (5-Pin SOT-23)	Symbol	Description
1	V _{IN}	Unregulated supply input.
2	GND	Ground terminal.
3	SHDN	Shutdown control input. The regulator is fully enabled when a logic high is applied to this input. The regulator enters shutdown when a logic low is applied to this input. During shutdown, output voltage falls to zero and supply current is reduced to 0.5 μ A (maximum).
4	Bypass	Reference bypass input. Connecting a 470 pF to this input further reduces output noise.
5	V _{OUT}	Regulated voltage output.

TABLE 3-1:PIN FUNCTION TABLE

3.1 Input Voltage (V_{IN})

Connect the V_{IN} pin to the unregulated source voltage. Like all low dropout linear regulators, low source impedance is necessary for the stable operation of the LDO. The amount of capacitance required to ensure low source impedance will depend on the proximity of the input source capacitors or battery type. For most applications, 1.0 μ F of capacitance will ensure stable operation of the LDO circuit. The type of capacitor used can be ceramic, tantalum or aluminum electrolytic. The low Effective Series Resistance (ESR) characteristics of the ceramic will yield better noise and Power Supply Ripple Rejection (PSRR) performance at high frequency.

3.2 Ground Terminal (GND)

Connect the ground pin to the input voltage return. For the optimal noise and PSRR performance, the GND pin of the LDO should be tied to a quiet circuit ground. For applications have switching or noisy inputs tie the GND pin to the return of the output capacitor. Ground planes help lower inductance and voltage spikes caused by fast transient load currents and are recommended for applications that are subjected to fast load transients.

3.3 Shutdown (SHDN)

The Shutdown input is used to turn the LDO on and off. When the SHDN pin is at a logic high level, the LDO output is enabled. When the SHDN pin is pulled to a logic low, the LDO output is disabled. When disabled, the quiescent current used by the LDO is less than $0.5 \ \mu A \ max$.

3.4 Bypass

Connecting a low-value ceramic capacitor to the Bypass pin will further reduce output voltage noise and improve the PSRR performance of the LDO. While smaller and larger values can be used, these affect the speed at which the LDO output voltage rises when the input power is applied. The larger the bypass capacitor, the slower the output voltage will rise.

3.5 Output Voltage (V_{OUT})

Connect the output load to V_{OUT} of the LDO. Also connect one side of the LDO output capacitor as close as possible to the V_{OUT} pin.

4.0 DETAILED DESCRIPTION

The TC1014, TC1015 and TC1185 are precision fixed output voltage regulators (if an adjustable version is needed, see the TC1070, TC1071 and TC1187 data sheet (DS21353). Unlike bipolar regulators, the TC1014, TC1015 and TC1185 supply current does not increase with load current. In addition, the LDOs' output voltage is stable using 1 μ F of capacitance over the entire specified input voltage range and output current range.

Figure 4-1 shows a typical application circuit. The regulator is enabled anytime the shutdown input (SHDN) is at or above V_{IH}, and disabled when SHDN is at or below V_{IL}. SHDN may be controlled by a CMOS logic gate or I/O port of a microcontroller. If the SHDN input is not required, it should be connected directly to the input supply. While in shutdown, the supply current decreases to 0.05 μ A (typical) and V_{OUT} falls to zero volts.




FIGURE 4-1:

Typical Application Circuit.

4.1 Bypass Input

A 470 pF capacitor connected from the Bypass input to ground reduces noise present on the internal reference, which in turn, significantly reduces output noise. If output noise is not a concern, this input may be left unconnected. Larger capacitor values may be used, but results in a longer time period to rated output voltage when power is initially applied.

4.2 Output Capacitor

A 1 μ F (min) capacitor from V_{OUT} to ground is required. The output capacitor should have an effective series resistance greater than 0.1 Ω and less than 5 Ω . A 1 μ F capacitor should be connected from V_{IN} to GND if there is more than 10 inches of wire between the regulator and the AC filter capacitor, or if a battery is used as the power source. Aluminum electrolytic or tantalum capacitor types can be used. (Since many aluminum electrolytic capacitors freeze at approximately -30°C, solid tantalums are recommended for applications operating below -25°C.) When operating from sources other than batteries, supply-noise rejection and transient response can be improved by increasing the value of the input and output capacitors and employing passive filtering techniques.

4.3 Input Capacitor

A 1 µF capacitor should be connected from V_{IN} to GND if there is more than 10 inches of wire between the regulator and this AC filter capacitor, or if a battery is used as the power source. Aluminum electrolytic or tantalum capacitors can be used (since many aluminum electrolytic capacitors freeze at approximately -30°C, solid tantalum is recommended for applications operating below -25°C). When operating from sources other than batteries, supplynoise rejection and transient response can be improved by increasing the value of the input and output capacitors and employing passive filtering techniques.

5.0 THERMAL CONSIDERATIONS

5.1 Thermal Shutdown

Integrated thermal protection circuitry shuts the regulator off when die temperature exceeds 160°C. The regulator remains off until the die temperature drops to approximately 150°C.

5.2 Power Dissipation

The amount of power the regulator dissipates is primarily a function of input and output voltage, and output current. The following equation is used to calculate worst-case actual power dissipation:

EQUATION 5-1:

$$P_D \approx (V_{INMAX} - V_{OUTMIN}) I_{LOADMAX}$$

Where:

P_D = Worst-case actual power dissipation

 V_{INMAX} = Maximum voltage on V_{IN}

V_{OUTMIN} = Minimum regulator output voltage

I_{LOADMAX} = Maximum output (load) current

The maximum allowable power dissipation (Equation 5-2) is a function of the maximum ambient temperature (T_{AMAX}), the maximum allowable die temperature (T_{JMAX}) and the thermal resistance from junction-to-air (θ_{JA}). The 5-pin SOT-23 package has a θ_{JA} of approximately 220°C/Watt.

EQUATION 5-2:

$$P_{DMAX} = \frac{(T_{JMAX} - T_{AMAX})}{\theta_{JA}}$$

Where all terms are previously defined.

Equation 5-1 can be used in conjunction with Equation 5-2 to ensure regulator thermal operation is within limits. For example:

Given:

V _{INMAX}	=	3.0V +10%
V _{OUTMIN}	=	2.7V – 2.5%
I _{LOADMAX}	=	40 mA
T_{JMAX}	=	125°C
T_{AMAX}	=	55°C

Find:

- 1. Actual power dissipation
- 2. Maximum allowable dissipation

Actual power dissipation:

$$P_{D} \approx (V_{\text{INMAX}} - V_{\text{OUTMIN}})I_{\text{LOADMAX}}$$

= [(3.0 x 1.1) - (2.7 x .975)]40 x 10⁻³
= 26.7 mW

Maximum allowable power dissipation:

$$P_{DMAX} = \frac{(T_{JMAX} - T_{AMAX})}{\theta_{JA}}$$
$$= \frac{(125 - 55)}{220}$$
$$= 318 \text{ mW}$$

In this example, the TC1014 dissipates a maximum of 26.7 mW below the allowable limit of 318 mW. In a similar manner, Equation 5-1 and Equation 5-2 can be used to calculate maximum current and/or input voltage limits.


5.3 Layout Considerations

The primary path of heat conduction out of the package is via the package leads. Therefore, layouts having a ground plane, wide traces at the pads, and wide power supply bus lines combine to lower θ_{JA} and therefore increase the maximum allowable power dissipation limit.

TC1014/TC1015/TC1185

6.0 PACKAGING INFORMATION

6.1 Package Marking Information




- ① & ② represents part number code + temperature range and voltage
- ③ represents year and 2-month period code
- (4) represents lot ID number

TC1014 TC1015 TC1185 (V) Code Code Code AY ΒY NY 1.8 2.5 A1 Β1 N1 2.6 NB ΒT NT 2.7 A2 B2 N2 2.8 ΑZ ΒZ ΝZ 2.85 A8 B8 N8 3.0 A3 B3 N3 A5 N5 3.3 Β5 3.6 A9 B9 N9 4.0 A0 B0 N0 5.0 A7 B7 N7

PART NUMBER CODE AND TEMPERATURE RANGE


TABLE 6-1:




6.2 Taping Form


5-Lead Plastic Small Outline Transistor (OT) [SOT-23]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging





11



	Units			MILLIMETERS			
Dimen	sion Limits	MIN	NOM	MAX			
Number of Pins	N	5					
Lead Pitch	е		0.95 BSC				
Outside Lead Pitch	e1	1.90 BSC					
Overall Height	Α	0.90	-	1.45			
Molded Package Thickness	A2	0.89	-	1.30			
Standoff	A1	0.00	-	0.15			
Overall Width	E	2.20	-	3.20			
Molded Package Width	E1	1.30	-	1.80			
Overall Length	D	2.70	-	3.10			
Foot Length	L	0.10	-	0.60			
Footprint	L1	0.35	-	0.80			
Foot Angle	φ	0°	-	30°			
Lead Thickness	С	0.08	-	0.26			
Lead Width	b	0.20	-	0.51			

Notes:

1. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.127 mm per side.

2. Dimensioning and tolerancing per ASME Y14.5M.

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-091B

TC1014/TC1015/TC1185

NOTES:

APPENDIX A: REVISION HISTORY

Revision E (February 2007)

- Section 1.0 "Electrical characteristics": Changed Dropout Voltage from mA to μA.
- Updated "Product Identification System", page 19.
- Updated Section 6.0 "Packaging Information".

Revision D (April 2006)

- Removed "ERROR is open circuited" from SHDN pin description in Pin Function Table.
- Added verbiage for pinout descriptions in Pin Function Table.
- Replaced verbiage in first paragraph of Section 4.0 Detailed Description.
- Added Section 4.3 Input Capacitor

Revision C (January 2006)

 Changed TR suffix to 713 suffix in Taping Form in Package Marking Section

Revision B (May 2002)

• Converted Telcom data sheet to Microchip standard for Analog Handbook

Revision A (February 2001)

• Original Release of this Document under Telcom.

^{© 2007} Microchip Technology Inc.

TC1014/TC1015/TC1185

NOTES:

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

<u>PART NOX</u>	<u>tx x xxxxx</u>	Examples:
	 tput Temperature Package	a) TC1014-1.8VCT713: 1.8V, 5LD SOT-23, Tape and Reel.
VOI	tage Range	b) TC1014-2.85VCT713: 2.85V, 5LD SOT-23, Tape and Reel.
Device:	TC1014: 50 mA LDO with Shutdown and V _{REF} Bypass TC1015: 100 mA LDO with Shutdown and V _{REF} Bypass TC1185: 150 mA LDO with Shutdown and V _{REF} Bypass	
Output Voltage:	1.8 = 1.8V	a) TC1015-1.8VCT713: 1.8V, 5LD SOT-23, Tape and Reel.
Oulput voltage.	2.5 = 2.5V 2.6 = 2.6V	b) TC1015-2.85VCT713: 2.85V, 5LD SOT-23, Tape and Reel.
	2.7 = 2.7V 2.8 = 2.8V 2.85 = 2.85V 3.0 = 3.0V	c) TC1015-3.0VCT713: 3.0V, 5LD SOT-23, Tape and Reel.
	3.3 = 3.3V 3.6 = 3.6V	a) TC1185-1.8VCT713: 1.8V, 5LD SOT-23, Tape and Reel.
	4.0 = 4.0V 5.0 = 5.0V	b) TC1185-2.8VCT713: 2.8V, 5LD SOT-23, Tape and Reel.
Temperature Range:	$V = -40^{\circ} \text{ C to } +125^{\circ} \text{ C}$	
Package:	CT713 = Plastic Small Outline Transistor (SOT-23), 5-lead, Tape and Reel	

^{© 2007} Microchip Technology Inc.

TC1014/TC1015/TC1185

NOTES:

Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights.

QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV <u>ISO/TS 16949:2002</u>

Trademarks

The Microchip name and logo, the Microchip logo, Accuron, dsPIC, KEELOQ, KEELOQ logo, microID, MPLAB, PIC, PICmicro, PICSTART, PRO MATE, PowerSmart, rfPIC, and SmartShunt are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AmpLab, FilterLab, Linear Active Thermistor, Migratable Memory, MXDEV, MXLAB, PS logo, SEEVAL, SmartSensor and The Embedded Control Solutions Company are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Analog-for-the-Digital Age, Application Maestro, CodeGuard, dsPICDEM, dsPICDEM.net, dsPICworks, ECAN, ECONOMONITOR, FanSense, FlexROM, fuzzyLAB, In-Circuit Serial Programming, ICSP, ICEPIC, Mindi, MiWi, MPASM, MPLAB Certified logo, MPLIB, MPLINK, PICkit, PICDEM, PICDEM.net, PICLAB, PICtail, PowerCal, PowerInfo, PowerMate, PowerTool, REAL ICE, rfLAB, rfPICDEM, Select Mode, Smart Serial, SmartTel, Total Endurance, UNI/O, WiperLock and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

All other trademarks mentioned herein are property of their respective companies.

© 2007, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.



Printed on recycled paper.

Microchip received ISO/TS-16949:2002 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona, Gresham, Oregon and Mountain View, California. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.

© 2007 Microchip Technology Inc.



WORLDWIDE SALES AND SERVICE

AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: http://support.microchip.com Web Address: www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075

Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit Farmington Hills, MI Tel: 248-538-2250 Fax: 248-538-2260

Kokomo Kokomo, IN Tel: 765-864-8360 Fax: 765-864-8387

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

Santa Clara Santa Clara, CA Tel: 408-961-6444 Fax: 408-961-6445

Toronto Mississauga, Ontario, Canada Tel: 905-673-0699 Fax: 905-673-6509

ASIA/PACIFIC

Asia Pacific Office Suites 3707-14, 37th Floor Tower 6, The Gateway Habour City, Kowloon Hong Kong Tel: 852-2401-1200 Fax: 852-2401-3431 Australia - Sydney

Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

China - Beijing Tel: 86-10-8528-2100 Fax: 86-10-8528-2104

China - Chengdu Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

China - Fuzhou Tel: 86-591-8750-3506 Fax: 86-591-8750-3521

China - Hong Kong SAR Tel: 852-2401-1200 Fax: 852-2401-3431

China - Qingdao Tel: 86-532-8502-7355 Fax: 86-532-8502-7205

China - Shanghai Tel: 86-21-5407-5533 Fax: 86-21-5407-5066

China - Shenyang Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

China - Shenzhen Tel: 86-755-8203-2660 Fax: 86-755-8203-1760

China - Shunde Tel: 86-757-2839-5507 Fax: 86-757-2839-5571

China - Wuhan Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

China - Xian Tel: 86-29-8833-7250 Fax: 86-29-8833-7256

ASIA/PACIFIC

India - Bangalore Tel: 91-80-4182-8400 Fax: 91-80-4182-8422

India - New Delhi Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune Tel: 91-20-2566-1512 Fax: 91-20-2566-1513

Japan - Yokohama Tel: 81-45-471- 6166 Fax: 81-45-471-6122

Korea - Gumi Tel: 82-54-473-4301 Fax: 82-54-473-4302

Korea - Seoul Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Penang Tel: 60-4-646-8870 Fax: 60-4-646-5086

Philippines - Manila Tel: 63-2-634-9065 Fax: 63-2-634-9069

Singapore Tel: 65-6334-8870 Fax: 65-6334-8850

Taiwan - Hsin Chu Tel: 886-3-572-9526 Fax: 886-3-572-6459

Taiwan - Kaohsiung Tel: 886-7-536-4818 Fax: 886-7-536-4803

Taiwan - Taipei Tel: 886-2-2500-6610 Fax: 886-2-2508-0102

Thailand - Bangkok Tel: 66-2-694-1351 Fax: 66-2-694-1350

EUROPE

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393 Denmark - Copenhagen Tel: 45-4450-2828 Fax: 45-4485-2829

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

UK - Wokingham Tel: 44-118-921-5869 Fax: 44-118-921-5820

12/08/06