

Radial Lead Type, High Capacitance

- High Capacitance type (2.7V).
- Higher capacitance than JUM.
- Wide temperature range (- 25 to +70°C).
- Compliant to the RoHS directive (2011/65/EU).






■ Specifications

Item	Performance Characteristics				
Category Temperature Range	− 25 to +70°C				
Rated Voltage	2.7V				
Rated Capacitance Range	1 to 82F See Note				
Capacitance Tolerance	±20%,20°C				
Stability at Low Temperature	Capacitance (- 25°C) / Capacitance (+20°C) ×100 ≥ 70% ESR (- 25°C) / ESR (+20°C) ≤ 4				
ESR, DCR*	Refer to the table below (20°C). *DC internal resistance				
Endurance	The specifications listed at right shall be met when the capacitors	Capacitance change	Within ±30% of the initial capacitance value		
	are restored to 20°C after the rated voltage is applied for 1000 hours at 70°C.	ESR	300% or less than the initial specified value		
	at 70 C.				
	The specifications listed at right shall be met when the capacitors	Capacitance change	Within ±30% of the initial capacitance value		
Shelf Life	are restored to 20°C after storing the capacitors under no load	ESR	300% or less than the initial specified value		
	for 1000 hours at 70°C.				
Humidity Endurance	The specifications listed at right shall be met when the capacitors	Capacitance change	Within ±30% of the initial capacitance value		
	are restored to 20°C after the rated voltage is applied for 500 hours	ESR	300% or less than the initial specified value		
	at 40°C 90%RH.				
Marking	Printed with white color letter on black sleeve.				

Drawing






						(mm)
φD	6.3	8	10	12.5	16	18
Р	2.5	3.5	5.0	5.0	7.5	7.5
φd	0.5	0.6	0.6*	0.6*	8.0	0.8

α,	(φD < 10) 1.5
ια	(¢D ≥10) 2.0

- ※ In case L>25 for the φ10 and φ12.5 dia unit, lead dia φd=0.8
- Please refer to page 20 about the end seal configuration.

Type numbering system (Example: 2.7V 1F)



※ Configuration

A Configuration			
φD	Pb-free lead finishing Pb-free PET sleeve		
6.3	CD		
8 • 10	PD		
12.5 to 18	HD		

Dimensions

2 Interiorence					
Rated Voltage (Code)	Rated Capacitance (F)	Code	ESR (Ω) (at 1kHz)	DCR* Typical (Ω)	Case size $_{\varphi}$ D × L (mm)
2.7V (T1)	1.0	105	1.8	4	6.3 × 9
	1.5	155	1.2	2.5	8 × 11.5
	2.7	275	0.6	1.2	8 × 20
	3.3	335	0.5	1.1	10 × 12.5
	4.7	475	0.4	0.8	10 × 20
	6.8	685	0.3	0.7	12.5 × 20
	12	126	0.3	0.6	10 × 31.5
	22	226	0.2	0.4	12.5 × 31.5
	33	336	0.12	0.28	16 × 31.5
	47	476	0.1	0.22	18 × 31.5
	82	826	0.06	0.13	18 × 40

^{*} The listed DCR value is typical and therefore not a guaranteed value.

Note:

The capacitance calculated from discharge time (ΔT) with constant current (i) after 30minuite charge with rated voltage (2.7V).

The discharge current (i) is 0.01 × rated capacitance (F).

The discharge time (ΔT) measured between 2V and 1V with constant current.

The capacitance calculated bellow.

Capacitance (F) = $i \times \Delta T$