PulseJack™ Single-Port Gigabit PoE+



Description:

1000 Base-T RJ45 single port with integrated magnetics - Designed for most leading PHY manufacturers with the addition of Power over Ethernet, according to IEEE 802.3at





Features and Benefits:

RoHS peak wave solder temperature rating 260°C

Single port Connector for PoE applications

High performance for maximum EMI suppression

Electrical Specifications @ 25°C - Operating Temperature 0°C to +70°C												
RoHS Compliant Part No.	Tab Option		Insertion Loss TX/RX (dB TYP)	Return Loss (dB TYP) $100\Omega~(\pm~15~\Omega)$			Crosstalk (dB TYP)			Common Mode Rejection (dB TYP)		Hipot (Vrms MIN)
			1-100 MHz	30 MHz	60-80 MHz	100 MHz	30 MHz	60 MHz	100 MHz	1-50 MHz	50-130 MHz	@ 60Hz 1 MIN
JK0-0177NL	UP	Y-G/G	-1.0	-16	-12	-10	-44	-37	-33	-27	-20	1500
JXKO-0190NL ²	UP	Y-G/G	-1.0	-16	-12	-10	-44	-37	-33	-27	-20	1500

Notes:

1. LEDs Left/Right: **G** = green; **Y** = yellow

2. JXKO: Operating temperature -40°C to +85°C.

RJ45 Durability Testing Rating								
Part Number	Mating Force (MAX)	Unmating Force (MAX)	Durability	Plug to Jack Retention (MIN)				
JKO/JXKO Series	5 lbs./2.268 kgs.	5 lbs./2.268 kgs.	500 Insertions	20 lbs./9.072 kgs.				

RJ45 Material Specification									
Part		Shield		Contact	Housing		MSL ²		
Number	Material Finish		Material	Plating Area	Solder Area	Material	Specification	Rating	
JKO/JXKO Series	Brass	20-40µ inches thick Nickel over brass	Phosphor Bronze	30µ inches gold over 30-50µ inches nickel	Tin Matte finish over nickel	Thermoplastic	UL 94 V-0	1	

Notes:

1. Connector dimensions comply with FCC dimension requirements.


2. MSL = Moisture Sensitivity Level class limits = 1 to 5 (Highest: 1; Lowest: 5)

J432.A (03/19)

PulseJack™ Single-Port Gigabit PoE+

Mechanical


JKO-0177NL, JXKO-0190NL



PulseJack™ Single-Port Gigabit PoE+

Schematic

JKO-0177NL, JXKO-0190NL



For More Information:

Americas - prodinfonetworkamericas@pulseelectronics.com | Europe - comms-Apps-Europe@pulseelectronics.com | Asia - prodinfonetworkapac@pulseelectronics.com | Asia - prodinfonetworkapac@pulseelectronics.com |

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2019. Pulse Electronics, Inc. All rights reserved.

