


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0050579204](#)
Status: **Active**
Overview: [SL Modular Connectors](#)
Description: SL Crimp Housing, Single Row, Version C, Front Ribs, 4 Circuits, Black

Documents:

3D Model	Product Specification TS-70058-001-001 (PDF)
Drawing (PDF)	Product Specification TS-70541-001-001 (PDF)
Product Specification PS-70058-001 (PDF)	Packaging Specification PK-70066-100 (PDF)
Product Specification PS-70400-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-71851-001 (PDF)	



Series image - Reference only

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	70066
Application	Signal, Wire-to-Board
Comments	Version C, Version C
Overview	SL Modular Connectors
Product Name	SL
UPC	800753578036

Physical

Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Resin	Polyester Alloy
Net Weight	0.400/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	70066-0073
--------------------	------------

Reference - Drawing Numbers

Packaging Specification	PK-70066-100
Product Specification	PS-70058-001, PS-70400-001, PS-71851-001, TS-70058-001-001, TS-70541-001-001
Sales Drawing	SD-70066-0071-0094

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[70066](#) Series

Mates With

[70543](#) , [70545](#) , [70553](#) , [70555](#) , [70541](#) ,
[70551](#) , [70634](#) , [74099](#)

Use With

SL Crimp Terminal [70058](#) , [71851](#)