

DCD800E2T-QW

18V XR Brushless Hammer Drill Driver - 2 X POWERSTACK

The DCD800 is our latest and most powerful brushless 2 speed Drill Driver that delivers up to 90Nm of torque in a compact 164mm body, engineered to give you the greatest performance on the toughest jobsites. 2 speed and 15 torque settings give you the ultimate control over your drilling and fastening applications. An enhanced pivoting LED positioned on the foot offers greater visibility in dark and confined spaces. POWERSTACK batteries deliver 50% more power** with a 25% smaller** footprint that works with all the 18V XR tools you already have. **Regarding 50% more power: vs. DCB183 battery, not in application. Regarding 25% smaller pack and more compact: footprint vs. DCB183 battery. **Regarding 50% more power: vs. DCB183 battery, not in application. Regarding 25% smaller pack and more compact: footprint vs. DCB183 battery. Regarding our lightest and most powerful: vs. DEWALT 18V XR batteries 2Ah or lower. Regarding 2x lifetime: charge cycles vs DCB183 battery."

Selling Propositions

- Brushless Motor Technology for excellent efficiency
- powerful 18V XR Brushless XRP Drill Driver with Compact Design
- Ultra compact, lightweight design allows use in confined spaces
- 3-Mode Foot LED light with Pivoting Feature for working better in low visibility area
- 15 position adjustable torque control for consistent screw driving into a variety of materials
- Intelligent trigger design allows for total control of application
- Steel belt hook and magnetic bit holder ensures strong storage solutions

Standard Equipment

Warranty specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Max. Drilling Capacity (Wood)	55.0 mm
Max. Cutting Capacity (Metal)	13.0 mm
No Load Speed	2000 rpm
Max Torque (Hard)	90.0 Nm
Battery Capacity	2.0 Ah
No. of Speeds	2.0
Battery Voltage	18 V
Battery Chemistry	Li-Ion
Power Output	850.0 W
Chuck capacity	13 mm
Weight	1.28 kg