KPA-1606SURCK

1.6 x 0.6 mm Right Angle SMD Chip LED Lamp



DESCRIPTIONS

- The Hyper Red source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode
- · Electrostatic discharge and power surge could damage the LEDs
- · It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- · All devices, equipments and machineries must be electrically grounded

FEATURES

- 1.6 x 1.2 x 0.6 mm right angle SMD LED, 0.6 mm thickness
- Low power consumption
- · Wide viewing angle
- Ideal for backlight and indicator
- Package: 2000 pcs / reel
- Moisture sensitivity level: 3
- · Halogen-free
- Tinned pads for improved solderability
- RoHS compliant

APPLICATIONS


- Backlight
- · Status indicator
- · Home and smart appliances
- · Wearable and portable devices
- Healthcare applications

ATTENTION

Observe precautions for handling electrostatic discharge sensitive devices




PACKAGE DIMENSIONS



RECOMMENDED SOLDERING PATTERN

(units : mm; tolerance : ± 0.1)



All dimensions are in millimeters (inches).
 Tolerance is ±0.1(0.004") unless otherwise noted.

3. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

The device has a single mounting surface. The device must be mounted according to the specifications.

SELECTION GUIDE

| Part Number | Emitting Color | Lens Type | lv (mcd) @ 20mA ^[2] | | Viewing Angle ^[1] | |
|---------------|---------------------|-------------|--------------------------------|-----|------------------------------|--|
| r art Number | (Material) | Lens Type | Min. Typ. | | 201/2 | |
| KPA-1606SURCK | Hyper Red (AlGaInP) | Water Clear | 120 | 220 | 110° | |
| | | | *40 | *80 | 110 | |

Notes

Holes.
 Holes.

KPA-1606SURCK

ELECTRICAL / OPTICAL CHARACTERISTICS at T_A=25°C

| Devenuetor | Symbol | Emitting Color | Value | | |
|---|--------------------------------|----------------|-------|------|-------|
| Parameter | | | Тур. | Max. | Unit |
| Wavelength at Peak Emission I_F = 20mA | λ_{peak} | Hyper Red | 645 | - | nm |
| Dominant Wavelength $I_F = 20 \text{mA}$ | λ_{dom} ^[1] | Hyper Red | 630 | - | nm |
| Spectral Bandwidth at 50% Φ REL MAX I _F = 20mA | Δλ | Hyper Red | 28 | - | nm |
| Capacitance | С | Hyper Red | 35 | - | pF |
| Forward Voltage $I_F = 20 \text{mA}$ | V _F ^[2] | Hyper Red | 1.95 | 2.5 | V |
| Reverse Current (V _R = 5V) | I _R | Hyper Red | - | 10 | μA |
| Temperature Coefficient of λ_{peak} I_F = 20mA, -10°C $\leq T \leq 85^\circ C$ | TC _{λpeak} | Hyper Red | 0.14 | - | nm/°C |
| Temperature Coefficient of λ_{dom} I_F = 20mA, -10°C \leq T \leq 85°C | TC _{λdom} | Hyper Red | 0.05 | - | nm/°C |
| Temperature Coefficient of V_F I_F = 20mA, -10°C \leq T \leq 85°C | TCv | Hyper Red | -1.9 | - | mV/°C |

Notes:

The dominant wavelength (λd) above is the setup value of the sorting machine. (Tolerance λd : ±1nm.)
 Forward voltage: ±0.1V.
 Wavelength value is traceable to CIE127-2007 standards.
 Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.


ABSOLUTE MAXIMUM RATINGS at T_A=25°C

| Parameter | Symbol | Value | Unit |
|--|-----------------------------------|------------|------|
| Power Dissipation | P _D | 75 | mW |
| Reverse Voltage | V _R | 5 | V |
| Junction Temperature | Tj | 115 | °C |
| Operating Temperature | T _{op} | -40 to +85 | °C |
| Storage Temperature | T _{stg} | -40 to +85 | °C |
| DC Forward Current | l _F | 30 | mA |
| Peak Forward Current | I _{FM} ^[1] | 185 | mA |
| Electrostatic Discharge Threshold (HBM) | - | 3000 | V |
| Thermal Resistance (Junction / Ambient) | R _{th JA} ^[2] | 630 | °C/W |
| Thermal Resistance (Junction / Solder point) | R_{th} JS $^{[2]}$ | 450 | °C/W |


Notes: 1. 1/10 Duty Cycle, 0. 1ms Pulse Width. 2. R_{th JA}, R_{th JS} Results from mounting on PC board FR4 (pad size ≥ 16 mm² per pad). 3. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.

TECHNICAL DATA

RELATIVE INTENSITY vs. WAVELENGTH




SPATIAL DISTRIBUTION







50

40






Luminous Intensity vs. Ambient Temperature




REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS




Notes

- Notes: 1. Don't cause stress to the LEDs while it is exposed to high temperature. 2. The maximum number of reflow soldering passes is 2 times. 3. Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.

TAPE SPECIFICATIONS (units : mm)




REEL DIMENSION (units : mm)



S 2021 Kingbright. All Rights Reserved. Spec No: DSAD2552 / 1203000476 Rev No: V.23A Date: 01/06/2021

KPA-1606SURCK

KPA-1606SURCK



PRECAUTIONARY NOTES

- The information included in this document reflects representative usage scenarios and is intended for technical reference only. 1.
- The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications. 2.
- the latest datasheet for the updated specifications.
 When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
 The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
 The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
 All design applications should refer to Kingbright application notes available at https://www.kingbright.com/application.notes