

# Series PVT212PbF

### Microelectronic Power IC

HEXFET® Power MOSFET Photovoltaic Relay Single-Pole, Normally-Open, 0-150V, 550mA AC / 825mA DC

## **General Description**

The PVT212 Series Photovoltaic Relay is a singlepole, normally open solid-state relay that can replace electromechanical relays in many applications. It utilizes International Rectifier's proprietary HEXFET power MOSFET as the output switch, driven by an integrated circuit photovoltaic generator of novel construction. The output switch is controlled by radiation from a GaAlAs light emitting diode (LED) which is optically isolated from the photovoltaic generator.

These SSRs are specifically designed for industrial control and peripheral telecom applications. Series PVT212 Relays are packaged in a 6-lead molded DIP package with either thru-hole or surface mount ('gull-wing') terminals. It is available in standard plastic shipping tubes or on tape-and-reel. Please refer to part identification information.

# **Applications**

- Control of AC (up to 90 VAC) industrial loads
- Control of DC industrial loads up to +/-120 VDC
- Telecom line switching

### Part Identification

PVT212PbF thru-hole PVT212SPbF surface-mount


PVT212S-TPbF surface-mount, Tape and Reel

#### **Features**

- **HEXFET Power MOSFET output**
- Bounce-free operation
- 4,000 V<sub>RMS</sub> I/O isolation
- Very low on-resistance (R<sub>DD-ON</sub>)
- Linear AC/DC operation
- Solid-State Reliability
- **UL** recognized
- **ESD Tolerance:**

Submit Datasheet Feedback

4000V Human Body Model 500V Machine Model



(HEXFET is the registered trademark for International Rectifier Power MOSFETs)



# **Electrical Specifications** ( $T_{A=}+25^{\circ}C$ unless otherwise specified)


INPUT CHARACTERISTICS	Limits	Units
Minimum Control Current (see figure 1)	5.0	mA
Maximum Control Current for Off-State Resistance	0.4	mA
Control Current Range (Caution: current limit input LED, see figure 5)	5.0 to 25	mA
Maximum Reverse Voltage	6.0	V


OUTPUT CHARACTERISTICS	Limits	Units
Operating Voltage Range	0 to ±150	V peak
Maximum Load Current @ T <sub>A</sub> =+40°C 5mA Control (see figure 1)		
A Connection	550	mA
B Connection	600	mA
C Connection	825	mA
Maximum On-State Resistance @TA=+25°C		
100mA Pulsed Load, 5mA Control (see figures 2 & 3)		
A Connection	0.75	Ω
B Connection	0.40	Ω
C Connection	0.25	Ω
Max. pulsed Load Current @Ta=+25°C, 10mA Control (10mS @ 10% duty cycle)	1200	mA
Maximum Off-State Leakage @T <sub>A</sub> =+25°C, ±150V	1.0	μA
Maximum Turn-On Time @Ta=+25°C (see figures 6 & 7)		
For 50mA, 100 V <sub>DC</sub> load, 10mA Control (5mS pulse width @ 50% duty cycle)	3.0	ms
Maximum Turn-Off Time @T <sub>A</sub> =+25°C (see figures 6 & 7)		
For 50mA, 100 V <sub>DC</sub> load, 10mA Control (5mS pulse width @ 50% duty cycle)	0.5	ms
Maximum Output Capacitance @ 50V <sub>DC</sub> , f=1MHz (Cout, see figure 8)	100	pF


GENERAL CHARACTERISTICS		Limits	Units
Minimum Dielectric Strength, Input-Output		4000	V <sub>RMS</sub>
Minimum Insulation Resistance, Input-Output		10 <sup>12</sup>	Ω
Maximum Capacitance, Input-Output Vd=0V, f=1MHz		1.0	pF
Maximum Pin Soldering Temperature (10 seconds maximum)		+260	
Ambient Temperature Range:	Operating	-40 to +85	°C
	Storage	-40 to +100	

International Rectifier does not recommend the use of this product in aerospace, avionics, military or life support applications. Users of this International Rectifier product in such applications assume all risks of such use and indemnify International Rectifier against all damages resulting from such use.


# **Connection Diagrams**














Figure 1. Typical Current Derating Curves

Figure 2. Typical On Characteristics




Figure 3. Typical On-Characteristics







Figure 4. Typical Normalized Off-State Leakage



10.0 "A" Connection Ton Delay Time (mS) Tdly 1.0 Toff 0.1 0 5 10 15 I LED (mA)

Figure 5. Input Characteristics (Current Controlled)








Figure 7. Delay Time Definitions






Figure 8. Typical Output Capacitance



#### **Case Outlines**





Note: For the most current drawing please refer to IR website at: http://www.irf.com/package/



### Qualification information<sup>†</sup>

Qualification level	Industrial (per JEDEC JESD47I <sup>††</sup> guidelines)	
Moisture Sensitivity Level	PVT212PbF	N/A
	PVT212SPbF	MSL4
	PVT212S-TPbF	(per JEDEC J-STD-020E & JEDEC J-STD-033C <sup>††</sup> )
RoHS compliant		Yes

<sup>†</sup> Qualification standards can be found at International Rectifier's web site: http://www.irf.com/product-info/reliability

#### **Revision History**

Date	Comments
I 5/18/2015	Added Qualification Information Table on page 6
	Updated data sheet with new IR corporate template



IR WORLD HEADQUARTERS: 101 N. Sepulveda Blvd., El Segundo, California 90245, USA

Data and specifications subject to change without notice

To contact International Rectifier, please visit http://www.irf.com/whoto-call/

<sup>††</sup> Applicable version of JEDEC standard at the time of product release