




**2101S-160**  
**ERGO™ Side Cutting Pliers with**  
**Insulated Handles and Phosphate**  
**Finish 160 mm**



**PRODUCT DETAILS**

- Two-component ERGO™ insulated handles: thermoplastic surface on tough polypropylene provides superior grip
- Suitable for cutting Cu, Fe+ and piano wire
- Insulated side cutting pliers developed according to the scientific ERGO™ process for working on live equipment up to 1000 V
- Comfortable 1000 V insulated handles
- Distance from joint to centre of cutting edges is reduced for greater leverage and increased cutting capacity
- High-performance alloy steel
- Phosphate finish, anti-corrosion treated
- Cutting radius progresses along edge in order to cut hard material such as piano wire close to the joint as well as soft materials
- Screw joint provides excellent running and accurate alignment of cutting edges
- Round-shaped jaws give improved accessibility in confined spaces
- Induction hardened cutting edges
- Heavy-duty induction hardened cutting edge
- Less effort required compared to conventional cutting pliers
- Reduced shank width ideally for carrying in the pocket
- Each and every tool is tested to 10.000V for 10 seconds at the end of the manufacturing cycle







**Follow the Fish!**



## PRODUCT ATTRIBUTES

Product: **2101S-160**

<b>A</b>	160 mm	<b>B</b>	18,1 mm	<b>C</b>	21 mm
<b>D</b>	9 mm	<b>E</b>	2 mm	<b>F</b>	1.5 mm
<b>G</b>	18,1 mm	 Cu	3.8 mm	 Fe+	2.5 mm
 Plano	2.0 mm	 g	162 g		

Follow the Fish!

