5mm, Blue LED Round With Flange Type



1/7

Page:

Technical Data Sheet

Features:

- Low power consumption.
- General purpose leads.
- Bulk, Available on tape and reel.
- High efficiency.
- Reliable and robust.
- Compliance with EU REACH.
- The product itself will remain within RoHS compliant Version.

Descriptions:

- The series is specially designed for applications requiring higher brightness.
- The LED lamps are available with different colors, intensities.

Applications:

- Telephone.
- Computer.
- Circuit board.
- Status indicators.
- Commercial use.

Device Selection Guide

Part No.	Emitting Color	Lens Color
504BD2E-B4-2B	Blue	Blue Diffused

Spec No.: B508X285 Date: 19-Jul-2017

Issue No.: G-Rev-4 E-mail: sales@luckylight.cn
Luckylight Electronics Co., Ltd http:// www.luckylight.cn


Copyright © 2017 Luckylight All Rights Reserved


5mm, Blue LED Round With Flange Type



Technical Data Sheet

Package Dimension:





Notes:

- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is \pm 0.25 mm (.010") unless otherwise noted.
- 3. Protruded resin under flange is 1.00mm (.039") max.

Spec No.: B508X285 Date: 19-Jul-2017

Issue No.:G-Rev-4E-mail:sales@luckylight.cnLuckylight Electronics Co., Ltdhttp://www.luckylight.cn

Copyright © 2017 Luckylight All Rights Reserved Page: 2 / 7

5mm, Blue LED Round With Flange Type



Technical Data Sheet

Absolute Maximum Ratings at Ta=25℃

Parameters	Symbol	Max.	Unit	
Power Dissipation	P_d	90	mW	
Peak Forward Current (a)	I _{FP}	100	mA	
DC Forward Current (b)	l _F	25	mA	
Reverse Voltage	V_{R}	5	V	
Operating Temperature Range	T_{opr}	-40°C to +	-80°C	
Storage Temperature Range	T_{stg}	-40°C to +	-85°C	
Soldering Temperature	T_{sld}	260°C for 5 Seconds		

Notes:

- a. Derate linearly as shown in derating curve.
- b. Duty Factor = 10%, Frequency = 1 kHz.

Electrical Optical Characteristics at Ta=25 $^{\circ}$ C

Parameters	Symbol	Min.	Тур.	Max.	Unit	Test Condition
Luminous Intensity ^(a)	lv	350	600		mcd	IF=20mA
Viewing Angle (b)	2θ _{1/2}		60		deg.	IF=20mA
Peak Emission Wavelength	λр		468		nm	IF=20mA
Dominant Wavelength (c)	λd		470		nm	IF=20mA
Spectral Line Half-Width	$\triangle \lambda$		25		nm	IF=20mA
Forward Voltage	VF	2.6	3.2	3.6	V	IF=20mA
Reverse Current	IR			10	μΑ	VR=5V

Notes:

- a. Luminous intensity is measured with a light sensor and filter combination that approximates the CIE eye-response curve.
- b. $2\theta_{1/2}$ is the o-axis angle where the luminous intensity is 1/2 the peak intensity.
- c. The dominant wavelength (λ d) is derived from the CIE chromaticity diagram and represents the single wavelength which defines the color of the device.

Spec No.: B508X285 Issue No.: G-Rev-4

Luckylight Electronics Co., Ltd

Copyright © 2017 Luckylight All Rights Reserved

Date: 19-Jul-2017

E-mail: sales@luckylight.cn http:// www.luckylight.cn


Page: **3** / **7**


5mm, Blue LED Round With Flange Type





Technical Data Sheet


Typical Electrical / Optical Characteristics Curves (25°C Ambient Temperature Unless Otherwise Noted)




















Spec No.: B508X285 Issue No.: G-Rev-4 Luckylight Electronics Co., Ltd Copyright © 2017 Luckylight All Rights Reserved

19-Jul-2017 Date: sales@luckylight.cn E-mail: www.luckylight.cn http://


4/7 Page:

5mm, Blue LED Round With Flange Type



Technical Data Sheet

Packing & Label Specifications:



Packing Quantity:

- a. 1000 PCS/bag.
- b. 10000 PCS/Inner Box.
- c. 6 Inner Boxes/Outside Box.

Spec No.: B508X285 Date: 19-Jul-2017

 Issue No.:
 G-Rev-4
 E-mail:
 sales@luckylight.cn

 Luckylight Electronics Co., Ltd
 http://
 www.luckylight.cn

Copyright © 2017 Luckylight All Rights Reserved Page: 5 / 7

5mm, Blue LED Round With Flange Type



Technical Data Sheet

CAUTIONS

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

2. Storage

- 2.1 The LEDs should be stored at 30°C or less and 70%RH or less after being shipped from Luckylight and the storage life limits are 3 months. If the LEDs are stored for 3 months or more, they can be stored for a year in a sealed container with a nitrogen atmosphere and moisture absorbent material.
- 2.2 Please avoid rapid transitions in ambient temperature, especially, in high humidity environments where condensation can occur.

3. Cleaning

Use alcohol-based cleaning solvents such as isopropyl alcohol to clean the LEDs if necessary.

4. Lead Forming & Assembly

During lead forming, the leads should be bent at a point at least 1.6mm from the base of LED lens. Do not use the base of the lead frame as a fulcrum during forming. Lead forming must be done before soldering, at normal temperature. During assembly on PCB, use minimum clinch force possible to avoid excessive mechanical stress.

5. Soldering

When soldering, for Lamp without stopper type and must be leave a minimum of 3mm clearance from the base of the lens to the soldering point. Do not apply any external stress to the lead frame during soldering while the LED is at high temperature.

Recommended soldering conditions:

Sold	ering Iron	Wave S	Soldering
Temperature Soldering Time	300°C Max. 3 sec. Max. (one time only)	Pre-heat Pre-heat Time Solder Wave	100°C Max. 60 sec. Max.
		Soldering Time	260°C Max. 5 sec. Max.

Note: Excessive soldering temperature and / or time might result in deformation of the LED lens or catastrophic failure of the LED.

6. Drive Method

An LED is a current-operated device. In order to ensure intensity uniformity on multiple LEDs connected in parallel in an application, it is recommended that a current limiting resistor be incorporated in the drive circuit, in series with each LED as shown in Circuit A below.

Circuit model A Circuit model B



Spec No.: B508X285

Issue No.: G-Rev-4

Luckylight Electronics Co., Ltd

Copyright © 2017 Luckylight All Rights Reserved

Date: 19-Jul-2017
E-mail: sales@luckylight.cn

www.luckylight.cn

Page: 6 / 7

http://

5mm, Blue LED Round With Flange Type



Technical Data Sheet

- (A) Recommended circuit
- (B) The brightness of each LED might appear different due to the differences in the I-V characteristics of those LEDs.

7. Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used. It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.

8. ESD (Electrostatic Discharge)

Static Electricity or power surge will damage the LED. Suggestions to prevent ESD damage:

- 8.1. Use a conductive wrist band or anti- electrostatic glove when handling these LEDs.
- 8.2. All devices, equipment, and machinery must be properly grounded.
- 8.3. Work tables, storage racks, etc. should be properly grounded.
- 8.4. Use ion blower to neutralize the static charge which might have built up on surface of the LEDs plastic lens as a result of friction between LEDs during storage and handing.

ESD-damaged LEDs will exhibit abnormal characteristics such as high reverse leakage current, low forward voltage, or "no light up" at low currents.

To verify for ESD damage, check for "light up" and VF of the suspect LEDs at low currents.

The VF of "good" LEDs should be >2.0V@0.1mA for InGaN product and >1.4V@0.1mA for AllnGaP product.

9. Others

- 9.1 The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- 9.2 The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- 9.3 When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Luckylight will not be responsible for any subsequent issues.
- 9.4 The LEDs described here are intended to be used for ordinary electronic equipment (such as office equipment, communication equipment and household applications). Consult Luckylight's Sales in advance for information on applications in which exceptional reliability is required, particularly when the failure or malfunction of the LEDs may directly jeopardize life or health, such as in aviation, transportation, traffic control equipment, medical and life support systems and safety devices.

Spec No.: B508X285 Date: 19-Jul-2017

 Issue No.:
 G-Rev-4
 E-mail:
 sales@luckylight.cn

 Luckylight Electronics Co., Ltd
 http://
 www.luckylight.cn

Copyright © 2017 Luckylight All Rights Reserved Page: 7 / 7