

## Mastech MS8233E - 2000 counts Digital Multimeter

- DC Voltage: 200mV/2V/20V/200V  $\pm$  (0.5%rdg+3dgt)  
600V  $\pm$ (0.8%rdg+5dgt)  
400mV/4V/40V/400V/600V
- AC Volatge: 2V/20V/200V  $\pm$ (1.2%rdg+5dgt)  
600V  $\pm$ (1.2%rdg+3dgt)  
4V/40V/400V/600V
- DC Current: 200uA/2mA/20mA/200mA  $\pm$ (1.0%rdg+3dgt)  
400uA4mA/40mA/400mA  
10A  $\pm$ (3.0%rdg+3dgt)
- AC Current : 200uA/2mA/20mA/200mA/10A  
 $\pm$ (1.2%rdg+4dgt)  
400uA4mA/40mA/400mA/10A
- Resistor: 200 $\Omega$ /2K $\Omega$ /20K $\Omega$ /200  
K $\Omega$ /2M $\Omega$ /20M $\Omega$   $\pm$ (0.8%rdg+2dgt)  
400 $\Omega$ /4K $\Omega$ /40K $\Omega$ /400 K $\Omega$ /4M $\Omega$ /40M $\Omega$
- Continuity Check: yes
- Diode Check: yes
- Temperature: -20°C to 1000°C (3.0%rdg+3dgt)