

# HEF4052B

## Dual 4-channel analog multiplexer/demultiplexer

Rev. 9 — 11 September 2014

Product data sheet

### 1. General description

---

The HEF4052B is a dual 4-channel analog multiplexer/demultiplexer with common channel select logic. Each multiplexer/demultiplexer has four independent inputs/outputs ( $nY0$  to  $nY3$ ) and a common input/output ( $nZ$ ). The common channel select logic includes two select inputs ( $S1$  and  $S2$ ) and an active LOW enable input ( $\bar{E}$ ). Both multiplexers/demultiplexers contain four bidirectional analog switches, each with one side connected to an independent input/output ( $nY0$  to  $nY3$ ) and the other side connected to a common input/output ( $nZ$ ). With  $\bar{E}$  LOW, one of the four switches is selected (low-impedance ON-state) by  $S1$  and  $S2$ . With  $\bar{E}$  HIGH, all switches are in the high-impedance OFF-state, independent of  $S1$  and  $S2$ . If break before make is needed, then it is necessary to use the enable input.

$V_{DD}$  and  $V_{SS}$  are the supply voltage connections for the digital control inputs ( $S1$  and  $S2$ , and  $\bar{E}$ ). The  $V_{DD}$  to  $V_{SS}$  range is 3 V to 15 V. The analog inputs/outputs ( $nY0$  to  $nY3$ , and  $nZ$ ) can swing between  $V_{DD}$  as a positive limit and  $V_{EE}$  as a negative limit.  $V_{DD} - V_{EE}$  may not exceed 15 V. Unused inputs must be connected to  $V_{DD}$ ,  $V_{SS}$ , or another input. For operation as a digital multiplexer/demultiplexer,  $V_{EE}$  is connected to  $V_{SS}$  (typically ground).  $V_{EE}$  and  $V_{SS}$  are the supply voltage connections for the switches.

### 2. Features and benefits

---

- Fully static operation
- 5 V, 10 V, and 15 V parametric ratings
- Standardized symmetrical output characteristics
- Specified from  $-40\text{ }^{\circ}\text{C}$  to  $+85\text{ }^{\circ}\text{C}$  and  $-40\text{ }^{\circ}\text{C}$  to  $+125\text{ }^{\circ}\text{C}$
- Complies with JEDEC standard JESD 13-B

### 3. Applications

---

- Analog multiplexing and demultiplexing
- Digital multiplexing and demultiplexing
- Signal gating




### 4. Ordering information

**Table 1. Ordering information**  
All types operate from -40 °C to +125 °C.

| Type number | Package |  | Version  |
|-------------|---------|--|----------|
|             | Name    | Description  |          |
| HEF4052BP   | DIP16   | plastic dual in-line package; 16 leads (300 mil)                       | SOT38-4  |
| HEF4052BT   | SO16    | plastic small outline package; 16 leads; body width 3.9 mm             | SOT109-1 |
| HEF4052BTT  | TSSOP16 | plastic thin shrink small outline package; 16 leads; body width 4.4 mm | SOT403-1 |

### 5. Functional diagram



**Fig 1. Functional diagram**




Fig 2. Schematic diagram (one switch)




Fig 3. Logic symbol




Fig 4. IEC logic symbol




Fig 5. Logic diagram

## 6. Pinning information

### 6.1 Pinning




Fig 6. Pin configuration SOT38-4 and SOT109-1

Fig 7. Pin configuration SOT338-1 and SOT403-1

### 6.2 Pin description

Table 2. Pin description

| Symbol                                 | Pin                        | Description                 |
|--|----------------------------|-----------------------------|
| $\bar{E}$                              | 6                          | enable input (active LOW)   |
| $V_{EE}$                               | 7                          | supply voltage              |
| $V_{SS}$                               | 8                          | ground supply voltage       |
| S1, S2                                 | 10, 9                      | select input                |
| 1Y0, 1Y1, 1Y2, 1Y3, 2Y0, 2Y1, 2Y2, 2Y3 | 12, 14, 15, 11, 1, 5, 2, 4 | independent input or output |
| 1Z, 2Z                                 | 13, 3                      | common output or input      |
| $V_{DD}$                               | 16                         | supply voltage              |

## 7. Functional description

### 7.1 Function table

Table 3. Function table<sup>[1]</sup>

| Input          |    |    | Channel on   |
|----------------|----|----|--------------|
| $\overline{E}$ | S2 | S1 |              |
| L              | L  | L  | nY0 to nZ    |
| L              | L  | H  | nY1 to nZ    |
| L              | H  | L  | nY2 to nZ    |
| L              | H  | H  | nY3 to nZ    |
| H              | X  | X  | switches off |

- [1] H = HIGH voltage level;  
L = LOW voltage level;  
X = don't care.

## 8. Limiting values

Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to  $V_{SS} = 0$  V (ground).

| Symbol    | Parameter               | Conditions   | Min                | Max            | Unit |
|-----------|-------------------------|--|--------------------|----------------|------|
| $V_{DD}$  | supply voltage          |  | -0.5               | +18            | V    |
| $V_{EE}$  | supply voltage          | referenced to $V_{DD}$   | <sup>[1]</sup> -18 | +0.5           | V    |
| $I_{IK}$  | input clamping current  | pins Sn and $\overline{E}$ ;<br>$V_I < -0.5$ V or $V_I > V_{DD} + 0.5$ V | -                  | $\pm 10$       | mA   |
| $V_I$     | input voltage           |  | -0.5               | $V_{DD} + 0.5$ | V    |
| $I_{I/O}$ | input/output current    |  | -                  | $\pm 10$       | mA   |
| $I_{DD}$  | supply current          |  | -                  | 50             | mA   |
| $T_{stg}$ | storage temperature     |  | -65                | +150           | °C   |
| $T_{amb}$ | ambient temperature     |  | -40                | +125           | °C   |
| $P_{tot}$ | total power dissipation | $T_{amb} = -40$ °C to +125 °C  | <sup>[2]</sup>     |                |      |
|           |                         | DIP16 package  | -                  | 750            | mW   |
|           |                         | SO16 package   | -                  | 500            | mW   |
|           |                         | TSSOP16 package  | -                  | 500            | mW   |
| P         | power dissipation       | per output   | -                  | 100            | mW   |

- [1] To avoid drawing  $V_{DD}$  current out of terminal Z, when switch current flows into terminals Y, the voltage drop across the bidirectional switch must not exceed 0.4 V. If the switch current flows into terminal Z, no  $V_{DD}$  current will flow out of terminals Y, and in this case there is no limit for the voltage drop across the switch, but the voltages at Y and Z may not exceed  $V_{DD}$  or  $V_{EE}$ .
- [2] For DIP16 package:  $P_{tot}$  derates linearly with 12 mW/K above 70 °C.  
For SO16 package:  $P_{tot}$  derates linearly with 8 mW/K above 70 °C.  
For SSOP16 package:  $P_{tot}$  derates linearly with 5.5 mW/K above 60 °C.

## 9. Recommended operating conditions

Table 5. Recommended operating conditions

| Symbol              | Parameter                           | Conditions                   | Min | Typ | Max      | Unit            |
|---------------------|-------------------------------------|------------------------------|-----|-----|----------|-----------------|
| $V_{DD}$            | supply voltage                      | see <a href="#">Figure 8</a> | 3   | -   | 15       | V               |
| $V_I$               | input voltage                       |                              | 0   | -   | $V_{DD}$ | V               |
| $T_{amb}$           | ambient temperature                 | in free air                  | -40 | -   | +125     | °C              |
| $\Delta t/\Delta V$ | input transition rise and fall rate | $V_{DD} = 5\text{ V}$        | -   | -   | 3.75     | $\mu\text{s/V}$ |
|                     |                                     | $V_{DD} = 10\text{ V}$       | -   | -   | 0.5      | $\mu\text{s/V}$ |
|                     |                                     | $V_{DD} = 15\text{ V}$       | -   | -   | 0.08     | $\mu\text{s/V}$ |




Fig 8. Operating area as a function of the supply voltages

## 10. Static characteristics

Table 6. Static characteristics

$V_{SS} = V_{EE} = 0\text{ V}$ ;  $V_I = V_{SS}$  or  $V_{DD}$  unless otherwise specified.

| Symbol   | Parameter                | Conditions               | $V_{DD}$ | $T_{amb} = -40\text{ °C}$ |           | $T_{amb} = 25\text{ °C}$ |           | $T_{amb} = 85\text{ °C}$ |           | $T_{amb} = 125\text{ °C}$ |           | Unit          |
|----------|--------------------------|--------------------------|----------|---------------------------|-----------|--------------------------|-----------|--------------------------|-----------|---------------------------|-----------|---------------|
|          |                          |                          |          | Min                       | Max       | Min                      | Max       | Min                      | Max       | Min                       | Max       |               |
| $V_{IH}$ | HIGH-level input voltage | $ I_O  < 1\ \mu\text{A}$ | 5 V      | 3.5                       | -         | 3.5                      | -         | 3.5                      | -         | 3.5                       | -         | V             |
|          |                          |                          | 10 V     | 7.0                       | -         | 7.0                      | -         | 7.0                      | -         | 7.0                       | -         | V             |
|          |                          |                          | 15 V     | 11.0                      | -         | 11.0                     | -         | 11.0                     | -         | 11.0                      | -         | V             |
| $V_{IL}$ | LOW-level input voltage  | $ I_O  < 1\ \mu\text{A}$ | 5 V      | -                         | 1.5       | -                        | 1.5       | -                        | 1.5       | -                         | 1.5       | V             |
|          |                          |                          | 10 V     | -                         | 3.0       | -                        | 3.0       | -                        | 3.0       | -                         | 3.0       | V             |
|          |                          |                          | 15 V     | -                         | 4.0       | -                        | 4.0       | -                        | 4.0       | -                         | 4.0       | V             |
| $I_I$    | input leakage current    |                          | 15 V     | -                         | $\pm 0.1$ | -                        | $\pm 0.1$ | -                        | $\pm 1.0$ | -                         | $\pm 1.0$ | $\mu\text{A}$ |

**Table 6. Static characteristics ...continued**  
 $V_{SS} = V_{EE} = 0\text{ V}$ ;  $V_I = V_{SS}$  or  $V_{DD}$  unless otherwise specified.

| Symbol       | Parameter                 | Conditions   | $V_{DD}$ | $T_{amb} = -40\text{ }^\circ\text{C}$ |     | $T_{amb} = 25\text{ }^\circ\text{C}$ |      | $T_{amb} = 85\text{ }^\circ\text{C}$ |     | $T_{amb} = 125\text{ }^\circ\text{C}$ |     | Unit          |
|--------------|---------------------------|--|----------|---------------------------------------|-----|--------------------------------------|------|--------------------------------------|-----|---------------------------------------|-----|---------------|
|              |                           |  |          | Min                                   | Max | Min                                  | Max  | Min                                  | Max | Min                                   | Max |               |
| $I_{S(OFF)}$ | OFF-state leakage current | Z port; all channels OFF; see <a href="#">Figure 9</a> | 15 V     | -                                     | -   | -                                    | 1000 | -                                    | -   | -                                     | -   | nA            |
|              |                           | Y port; per channel; see <a href="#">Figure 10</a>     | 15 V     | -                                     | -   | -                                    | 200  | -                                    | -   | -                                     | -   | nA            |
| $I_{DD}$     | supply current            | $I_O = 0\text{ A}$                                     | 5 V      | -                                     | 5   | -                                    | 5    | -                                    | 150 | -                                     | 150 | $\mu\text{A}$ |
|              |                           |  | 10 V     | -                                     | 10  | -                                    | 10   | -                                    | 300 | -                                     | 300 | $\mu\text{A}$ |
|              |                           |  | 15 V     | -                                     | 20  | -                                    | 20   | -                                    | 600 | -                                     | 600 | $\mu\text{A}$ |
| $C_I$        | input capacitance         | $S_n, \bar{E}$ inputs                                  | -        | -                                     | -   | 7.5                                  | -    | -                                    | -   | -                                     | pF  |               |

10.1 Test circuits




Fig 9. Test circuit for measuring OFF-state leakage current Z port




Fig 10. Test circuit for measuring OFF-state leakage current nYn port




10.2 On resistance

Table 7. ON resistance

$T_{amb} = 25\text{ }^{\circ}\text{C}$ ;  $I_{SW} = 200\text{ }\mu\text{A}$ ;  $V_{SS} = V_{EE} = 0\text{ V}$ .

| Symbol          | Parameter                               | Conditions   | $V_{DD} - V_{EE}$ | Typ | Max  | Unit     |
|-----------------|---|--|-------------------|-----|------|----------|
| $R_{ON(peak)}$  | ON resistance (peak)                    | $V_I = 0\text{ V to }V_{DD} - V_{EE}$ ;<br>see <a href="#">Figure 11</a> and <a href="#">Figure 12</a> | 5 V               | 350 | 2500 | $\Omega$ |
|                 |   |  | 10 V              | 80  | 245  | $\Omega$ |
|                 |   |  | 15 V              | 60  | 175  | $\Omega$ |
| $R_{ON(rail)}$  | ON resistance (rail)                    | $V_I = 0\text{ V}$ ; see <a href="#">Figure 11</a> and <a href="#">Figure 12</a>                       | 5 V               | 115 | 340  | $\Omega$ |
|                 |   |  | 10 V              | 50  | 160  | $\Omega$ |
|                 |   |  | 15 V              | 40  | 115  | $\Omega$ |
|                 |   | $V_I = V_{DD} - V_{EE}$ ;<br>see <a href="#">Figure 11</a> and <a href="#">Figure 12</a>               | 5 V               | 120 | 365  | $\Omega$ |
|                 |   |  | 10 V              | 65  | 200  | $\Omega$ |
|                 |   |  | 15 V              | 50  | 155  | $\Omega$ |
| $\Delta R_{ON}$ | ON resistance mismatch between channels | $V_I = 0\text{ V to }V_{DD} - V_{EE}$ ; see <a href="#">Figure 11</a>                                  | 5 V               | 25  | -    | $\Omega$ |
|                 |   |  | 10 V              | 10  | -    | $\Omega$ |
|                 |   |  | 15 V              | 5   | -    | $\Omega$ |

10.2.1 On resistance waveform and test circuit



$R_{ON} = V_{SW} / I_{SW}$ .

Fig 11. Test circuit for measuring  $R_{ON}$




Fig 12. Typical  $R_{ON}$  as a function of input voltage

## 11. Dynamic characteristics

Table 8. Dynamic characteristics



$T_{amb} = 25\text{ }^{\circ}\text{C}$ ;  $V_{SS} = V_{EE} = 0\text{ V}$ ; for test circuit see [Figure 16](#).

| Symbol           | Parameter                           | Conditions  | V <sub>DD</sub> |      | Typ | Max | Unit |
|------------------|-------------------------------------|---|-----------------|------|-----|-----|------|
|                  |                                     |   | 5 V             | 10 V |     |     |      |
| t <sub>PHL</sub> | HIGH to LOW propagation delay       | nYn, nZ to nZ, nYn; see <a href="#">Figure 13</a>   | 5 V             | 10   | 20  | ns  |      |
|                  |                                     |   | 10 V            | 5    | 10  | ns  |      |
|                  |                                     |   | 15 V            | 5    | 10  | ns  |      |
|                  |                                     | Sn to nYn, nZ; see <a href="#">Figure 14</a>        | 5 V             | 150  | 305 | ns  |      |
|                  |                                     |   | 10 V            | 65   | 135 | ns  |      |
|                  |                                     |   | 15 V            | 50   | 100 | ns  |      |
| t <sub>PLH</sub> | LOW to HIGH propagation delay       | Yn, nZ to nZ, nYn; see <a href="#">Figure 13</a>    | 5 V             | 10   | 20  | ns  |      |
|                  |                                     |   | 10 V            | 5    | 10  | ns  |      |
|                  |                                     |   | 15 V            | 5    | 10  | ns  |      |
|                  |                                     | Sn to nYn, nZ; see <a href="#">Figure 14</a>        | 5 V             | 150  | 300 | ns  |      |
|                  |                                     |   | 10 V            | 75   | 150 | ns  |      |
|                  |                                     |   | 15 V            | 50   | 100 | ns  |      |
| t <sub>PHZ</sub> | HIGH to OFF-state propagation delay | $\bar{E}$ to nYn, nZ; see <a href="#">Figure 15</a> | 5 V             | 95   | 190 | ns  |      |
|                  |                                     |   | 10 V            | 90   | 180 | ns  |      |
|                  |                                     |   | 15 V            | 85   | 180 | ns  |      |
| t <sub>PZH</sub> | OFF-state to HIGH propagation delay | $\bar{E}$ to nYn, nZ; see <a href="#">Figure 15</a> | 5 V             | 130  | 260 | ns  |      |
|                  |                                     |   | 10 V            | 55   | 115 | ns  |      |
|                  |                                     |   | 15 V            | 45   | 85  | ns  |      |
| t <sub>PLZ</sub> | LOW to OFF-state propagation delay  | $\bar{E}$ to nYn, nZ; see <a href="#">Figure 15</a> | 5 V             | 100  | 205 | ns  |      |
|                  |                                     |   | 10 V            | 90   | 180 | ns  |      |
|                  |                                     |   | 15 V            | 90   | 180 | ns  |      |

**Table 8. Dynamic characteristics ...continued**  
 $T_{amb} = 25\text{ }^{\circ}\text{C}$ ;  $V_{SS} = V_{EE} = 0\text{ V}$ ; for test circuit see [Figure 16](#).


| Symbol           | Parameter                          | Conditions  | $V_{DD}$ | Typ | Max | Unit |
|------------------|------------------------------------|---|----------|-----|-----|------|
| t <sub>PZL</sub> | OFF-state to LOW propagation delay | $\bar{E}$ to nYn, nZ; see <a href="#">Figure 15</a> | 5 V      | 120 | 240 | ns   |
|                  |                                    |   | 10 V     | 50  | 100 | ns   |
|                  |                                    |   | 15 V     | 35  | 75  | ns   |

**11.1 Waveforms and test circuit**



**Table 9. Measurement points**

| Supply voltage | Input       | Output      |
|----------------|-------------|-------------|
| $V_{DD}$       | $V_M$       | $V_M$       |
| 5 V to 15 V    | $0.5V_{DD}$ | $0.5V_{DD}$ |



Test data is given in [Table 10](#).

Definitions:

DUT = Device Under Test.

$R_T$  = Termination resistance should be equal to output impedance  $Z_o$  of the pulse generator.

$C_L$  = Load capacitance including test jig and probe.

$R_L$  = Load resistance.

Fig 16. Test circuit for measuring switching times

Table 10. Test data

| Input                |                      |              |             | Load  |               | S1 position              |           |                    |                    |          |
|----------------------|----------------------|--------------|-------------|-------|---------------|--------------------------|-----------|--------------------|--------------------|----------|
| nYn, nZ              | Sn and $\bar{E}$     | $t_r, t_f$   | $V_M$       | $C_L$ | $R_L$         | $t_{PHL}$ <sup>[1]</sup> | $t_{PLH}$ | $t_{PZH}, t_{PHZ}$ | $t_{PZL}, t_{PLZ}$ | other    |
| $V_{DD}$ or $V_{EE}$ | $V_{DD}$ or $V_{SS}$ | $\leq 20$ ns | $0.5V_{DD}$ | 50 pF | 10 k $\Omega$ | $V_{DD}$ or $V_{EE}$     | $V_{EE}$  | $V_{EE}$           | $V_{DD}$           | $V_{EE}$ |

[1] For nYn to nZ propagation delays use  $V_{EE}$ . For Sn to nYn or nZ propagation delays use  $V_{DD}$ .

11.2 Additional dynamic parameters

Table 11. Additional dynamic characteristics

$V_{SS} = V_{EE} = 0\text{ V}$ ;  $T_{amb} = 25\text{ }^{\circ}\text{C}$ .

| Symbol         | Parameter                 | Conditions  | $V_{DD}$ | Typ | Max  | Unit |     |
|----------------|---------------------------|---|----------|-----|------|------|-----|
| THD            | total harmonic distortion | see Figure 17; $R_L = 10\text{ k}\Omega$ ; $C_L = 15\text{ pF}$ ;<br>channel ON; $V_I = 0.5V_{DD}$ (p-p);<br>$f_i = 1\text{ kHz}$     | 5 V      | [1] | 0.25 | -    | %   |
|                |                           |   | 10 V     | [1] | 0.04 | -    | %   |
|                |                           |   | 15 V     | [1] | 0.04 | -    | %   |
| $f_{(-3dB)}$   | -3 dB frequency response  | see Figure 18; $R_L = 1\text{ k}\Omega$ ; $C_L = 5\text{ pF}$ ;<br>channel ON; $V_I = 0.5V_{DD}$ (p-p)                                | 5 V      | [1] | 13   | -    | MHz |
|                |                           |   | 10 V     | [1] | 40   | -    | MHz |
|                |                           |   | 15 V     | [1] | 70   | -    | MHz |
| $\alpha_{iso}$ | isolation (OFF-state)     | see Figure 19; $f_i = 1\text{ MHz}$ ; $R_L = 1\text{ k}\Omega$ ;<br>$C_L = 5\text{ pF}$ ; channel OFF;<br>$V_I = 0.5V_{DD}$ (p-p)     | 10 V     | [1] | -50  | -    | dB  |
| $V_{ct}$       | crosstalk voltage         | digital inputs to switch; see Figure 20;<br>$R_L = 10\text{ k}\Omega$ ; $C_L = 15\text{ pF}$ ;<br>$E$ or $S_n = V_{DD}$ (square-wave) | 10 V     |     | 50   | -    | mV  |
| Xtalk          | crosstalk                 | between switches; see Figure 21;<br>$f_i = 1\text{ MHz}$ ; $R_L = 1\text{ k}\Omega$ ;<br>$V_I = 0.5V_{DD}$ (p-p)                      | 10 V     | [1] | -50  | -    | dB  |

[1]  $f_i$  is biased at  $0.5 V_{DD}$ ;  $V_I = 0.5V_{DD}$  (p-p).

Table 12. Dynamic power dissipation  $P_D$

$P_D$  can be calculated from the formulas shown;  $V_{EE} = V_{SS} = 0\text{ V}$ ;  $t_r = t_f \leq 20\text{ ns}$ ;  $T_{amb} = 25\text{ }^{\circ}\text{C}$ .

| Symbol | Parameter                 | $V_{DD}$ | Typical formula for $P_D$ ( $\mu\text{W}$ )                       | where:   |
|--------|---------------------------|----------|---|--|
| $P_D$  | dynamic power dissipation | 5 V      | $P_D = 1300 \times f_i + \Sigma(f_o \times C_L) \times V_{DD}^2$  | $f_i$ = input frequency in MHz;<br>$f_o$ = output frequency in MHz;<br>$C_L$ = output load capacitance in pF;<br>$V_{DD}$ = supply voltage in V;<br>$\Sigma(C_L \times f_o)$ = sum of the outputs. |
|        |                           | 10 V     | $P_D = 6100 \times f_i + \Sigma(f_o \times C_L) \times V_{DD}^2$  |  |
|        |                           | 15 V     | $P_D = 15600 \times f_i + \Sigma(f_o \times C_L) \times V_{DD}^2$ |  |

11.2.1 Test circuits

001aak638

**Fig 17. Test circuit for measuring total harmonic distortion**

001aak639

**Fig 18. Test circuit for measuring frequency response**






Fig 19. Test circuit for measuring isolation (OFF-state)




a. Test circuit




b. Input and output pulse definitions

Fig 20. Test circuit for measuring crosstalk voltage between digital inputs and switch



a. Switch closed condition



b. Switch open condition

Fig 21. Test circuit for measuring crosstalk between switches

12. Package outline

DIP16: plastic dual in-line package; 16 leads (300 mil)

SOT38-4




Fig 22. Package outline SOT38-4 (DIP16)



SO16: plastic small outline package; 16 leads; body width 3.9 mm

SOT109-1




Fig 23. Package outline SOT109-1 (SO16)

TSSOP16: plastic thin shrink small outline package; 16 leads; body width 4.4 mm

SOT403-1




Fig 24. Package outline SOT403-1 (TSSOP16)

## 13. Abbreviations

Table 13. Abbreviations

| Acronym | Description       |
|---------|-------------------|
| DUT     | Device Under Test |

## 14. Revision history

Table 14. Revision history

| Document ID      | Release date  | Data sheet status     | Change notice | Supersedes       |
|------------------|---|-----------------------|---------------|------------------|
| HEF4052B v.9     | 20140911  | Product data sheet    | -             | HEF4052B v.8     |
| Modifications:   | <ul style="list-style-type: none"> <li>• <a href="#">Figure 20</a>: Test circuit modified</li> </ul>  |                       |               |                  |
| HEF4052B v.8     | 20111117  | Product data sheet    | -             | HEF4052B v.7     |
| Modifications:   | <ul style="list-style-type: none"> <li>• Legal pages updated.</li> <li>• Changes in “General description”, “Features and benefits” and “Applications”.</li> </ul> |                       |               |                  |
| HEF4052B v.7     | 20100326  | Product data sheet    | -             | HEF4052B v.6     |
| HEF4052B v.6     | 20100308  | Product data sheet    | -             | HEF4052B v.5     |
| HEF4052B v.5     | 20091127  | Product data sheet    | -             | HEF4052B v.4     |
| HEF4052B v.4     | 20090924  | Product data sheet    | -             | HEF4052B_CNV v.3 |
| HEF4052B_CNV v.3 | 19950101  | Product specification | -             | HEF4052B_CNV v.2 |
| HEF4052B_CNV v.2 | 19950101  | Product specification | -             | -                |

## 15. Legal information

### 15.1 Data sheet status

| Document status <sup>[1][2]</sup> | Product status <sup>[3]</sup> | Definition  |
|-----------------------------------|-------------------------------|---|
| Objective [short] data sheet      | Development                   | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet    | Qualification                 | This document contains data from the preliminary specification.                       |
| Product [short] data sheet        | Production                    | This document contains the product specification.                                     |

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nxp.com>.

### 15.2 Definitions

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

**Short data sheet** — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

### 15.3 Disclaimers

**Limited warranty and liability** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

**Limiting values** — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

**Terms and conditions of commercial sale** — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nxp.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

**Non-automotive qualified products** — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond

NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

## 15.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

## 16. Contact information

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: [salesaddresses@nxp.com](mailto:salesaddresses@nxp.com)

## 17. Contents

|           |   |           |
|-----------|---|-----------|
| <b>1</b>  | <b>General description</b> .....              | <b>1</b>  |
| <b>2</b>  | <b>Features and benefits</b> .....            | <b>1</b>  |
| <b>3</b>  | <b>Applications</b> .....                     | <b>1</b>  |
| <b>4</b>  | <b>Ordering information</b> .....             | <b>2</b>  |
| <b>5</b>  | <b>Functional diagram</b> .....               | <b>2</b>  |
| <b>6</b>  | <b>Pinning information</b> .....              | <b>5</b>  |
| 6.1       | Pinning .....                                 | 5         |
| 6.2       | Pin description .....                         | 5         |
| <b>7</b>  | <b>Functional description</b> .....           | <b>6</b>  |
| 7.1       | Function table .....                          | 6         |
| <b>8</b>  | <b>Limiting values</b> .....                  | <b>6</b>  |
| <b>9</b>  | <b>Recommended operating conditions</b> ..... | <b>7</b>  |
| <b>10</b> | <b>Static characteristics</b> .....           | <b>7</b>  |
| 10.1      | Test circuits .....                           | 8         |
| 10.2      | On resistance .....                           | 9         |
| 10.2.1    | On resistance waveform and test circuit ..... | 9         |
| <b>11</b> | <b>Dynamic characteristics</b> .....          | <b>10</b> |
| 11.1      | Waveforms and test circuit .....              | 11        |
| 11.2      | Additional dynamic parameters .....           | 13        |
| 11.2.1    | Test circuits .....                           | 13        |
| <b>12</b> | <b>Package outline</b> .....                  | <b>16</b> |
| <b>13</b> | <b>Abbreviations</b> .....                    | <b>19</b> |
| <b>14</b> | <b>Revision history</b> .....                 | <b>19</b> |
| <b>15</b> | <b>Legal information</b> .....                | <b>20</b> |
| 15.1      | Data sheet status .....                       | 20        |
| 15.2      | Definitions .....                             | 20        |
| 15.3      | Disclaimers .....                             | 20        |
| 15.4      | Trademarks .....                              | 21        |
| <b>16</b> | <b>Contact information</b> .....              | <b>21</b> |
| <b>17</b> | <b>Contents</b> .....                         | <b>22</b> |

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP Semiconductors N.V. 2014.

All rights reserved.

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: [salesaddresses@nxp.com](mailto:salesaddresses@nxp.com)

Date of release: 11 September 2014

Document identifier: HEF4052B