



DLPlus mini-trunking 20 x 12.5 and 32 x 12.5 profiles and finishing accessories



Selection chart **p. 782-783**
Wiring capacity chart **p. 788**

Pack	Cat.Nos		Mini-trunking
	20 x 12.5	32 x 12.5	EN 50085-2-1 approved
			Without central partition
			Mini-trunking with cable grip
			Equipped with an integrated device
			for holding cables in place
120 180	0 300 08 ¹	0 300 15 ¹	Length 2.10 m
			With central partition
120 180	0 300 07 ¹	0 300 14 ¹	Length 2.10 m



Pack	Cat.Nos		Finishing accessories
20	20 x 12.5 0 312 02	32 x 12.5 0 312 03	End cap
10	0 302 21	0 302 51	Changeable internal-external angle
10	0 302 23	0 302 53	Changeable flat angle
20	0 336 02	0 336 03	Cover joint
10	0 302 24	0 302 54	Flat T-junction

Pack	Cat.Nos	Special frames
		Supplied with end cap and divider for separation of currents
		Installation alongside the mini-trunking
		For vertical or horizontal mounting of surface mounting wiring accessories (p. 793)
10	0 314 04	1 gang
5	0 314 14	2 gang

Pack	Cat.Nos	Adaptors
		Adaptor for mounting Mosaic frames at end of the mini-trunking
10	0 316 40	For 20 x 12.5 mini-trunking
10	0 316 41	For 32 x 12.5 mini-trunking
		Adaptor for mounting Mosaic frames alongside the mini-trunking
10	0 317 01	For Mosaic frames Cat.Nos 0 316 11 and 0 316 12
10	0 317 02	For Mosaic frames Cat.Nos 0 316 13 and 0 316 21
5	0 317 03	For Mosaic frames Cat.Nos 0 316 14 and 0 316 22

Connection of luminaires (p. 787)

Frames for wiring accessories (p. 787)

1: Number of metres in pack