

Fan - RFC DUAL-FAN - 2730239

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Fan module for Remote Field Controllers RFC 430 ETH-IB / RFC 450 ETH-IB

Your advantages

- Power supply via RFC 4xx
- Maintenance-free operation
- Easy mounting
- Optimum heat exchange for RFC 4xx controllers



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 818746
GTIN	4017918818746
Weight per Piece (excluding packing)	170.400 g
Weight per piece (including packing)	171.300 g
Custom tariff number	84145915
Country of origin	Germany

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Height	25 mm
Depth	126 mm
Width	85 mm

Ambient conditions

Fan - RFC DUAL-FAN - 2730239

Technical data

Ambient conditions

Ambient temperature (operation)	0 °C ... 55 °C
---------------------------------	----------------

General

Supply voltage	24 V DC
----------------	---------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	27242292
eCl@ss 11.0	27242292
eCl@ss 4.0	27360400
eCl@ss 4.1	27360400
eCl@ss 5.0	27242200
eCl@ss 5.1	27242200
eCl@ss 6.0	27249200
eCl@ss 7.0	27249290
eCl@ss 9.0	27242292

ETIM

ETIM 2.0	EC000313
ETIM 3.0	EC000313
ETIM 4.0	EC002584
ETIM 6.0	EC002584
ETIM 7.0	EC002584

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	39121311
UNSPSC 13.2	39121552
UNSPSC 18.0	32151601
UNSPSC 19.0	32151601
UNSPSC 20.0	32151601
UNSPSC 21.0	32151601

Fan - RFC DUAL-FAN - 2730239

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / EAC / cULus Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140324
EAC			EAC-Zulassung
EAC			RU*DE*08.B.01186/19
cULus Recognized			
