

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2079010100](#)  
**Status:** **Active**  
**Overview:** Antennas  
**Description:** 600MHz-6GHz Monopole Low-profile Flexible Antenna, 100.00mm Cable Length

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 2079010100-PK (PDF)</a>
<a href="#">Product Specification 2079010100-PS (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 2079010100-AS (PDF)</a>	<a href="#">Product Literature (PDF)</a>

**General**

Product Family	Antennas
Series	<a href="#">207901</a>
Component Type	Stand Alone Antenna with Cable
Mates With	<a href="#">73412-0110</a> Microcoaxial RF, 50 Ohm
Overview	<a href="#">Antennas</a>
Product Literature Order No	987651-7811
Product Name	600MHz-6GHz Flexible Antenna
Protocol	Cellular
Type	Cellular Antenna
UPC	191130043040

**Physical**

Cable Length	100.00mm
Length	147.00mm
Mounting Style	Adhesive
Net Weight	1.815/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.16mm
Width	25.00mm


**Electrical**

Band#1 F_End (MHz)	960
Band#1 F_Start (MHz)	600
Band#2 F_End (MHz)	3000
Band#2 F_Start (MHz)	1500
Band#3 F_End (MHz)	6000
Band#3 F_Start (MHz)	3000
Electrical Connectivity	Cable
Peak Gain (dBi)	2.6 @ 600 MHz, 4.9 @ 1500 MHz, 5.4 @ 3 GHz
Return Loss - S11 (dB)	< -3, < -5
Total Efficiency	65% @ 1500 MHz, 70% @ 3 GHz, 70% @ 600 MHz

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2079010100-AS
Packaging Specification	2079010100-PK
Product Specification	2079010100-PS
Sales Drawing	2079010100-SD



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[207901](#) Series