



2.54	[.100]	5.08	[.200]	2	12	8-534237-9
99.06	[3.900]	101.60	[4.000]	40	12	8-534237-8
96.52	[3.800]	99.06	[3.900]	39	12	8-534237-7
93.98	[3.700]	96.52	[3.800]	38	12	8-534237-6
91.44	[3.600]	93.98	[3.700]	37	12	8-534237-5
88.90	[3.500]	91.44	[3.600]	36	12	8-534237-4
86.36	[3.400]	88.90	[3.500]	35	12	8-534237-3
83.82	[3.300]	86.36	[3.400]	34	12	8-534237-2
81.28	[3.200]	83.82	[3.300]	33	12	8-534237-1
78.74	[3.100]	81.28	[3.200]	32	12	8-534237-0
76.20	[3.000]	78.74	[3.100]	31	12	7-534237-9
73.66	[2.900]	76.20	[3.000]	30	12	7-534237-8
71.12	[2.800]	73.66	[2.900]	29	12	7-534237-7
68.58	[2.700]	71.12	[2.800]	28	12	7-534237-6
66.04	[2.600]	68.58	[2.700]	27	12	7-534237-5
63.50	[2.500]	66.04	[2.600]	26	12	7-534237-4
60.96	[2.400]	63.50	[2.500]	25	12	7-534237-3
58.42	[2.300]	60.96	[2.400]	24	12	7-534237-2
55.88	[2.200]	58.42	[2.300]	23	12	7-534237-1
53.34	[2.100]	55.88	[2.200]	22	12	7-534237-0
50.80	[2.000]	53.34	[2.100]	21	12	6-534237-9
48.26	[1.900]	50.80	[2.000]	20	12	6-534237-8
45.72	[1.800]	48.26	[1.900]	19	12	6-534237-7
43.18	[1.700]	45.72	[1.800]	18	12	6-534237-6
40.64	[1.600]	43.18	[1.700]	17	12	6-534237-5
38.10	[1.500]	40.64	[1.600]	16	12	6-534237-4
35.56	[1.400]	38.10	[1.500]	15	12	6-534237-3
33.02	[1.300]	35.56	[1.400]	14	12	6-534237-2
30.48	[1.200]	33.02	[1.300]	13	12	6-534237-1
27.94	[1.100]	30.48	[1.200]	12	12	6-534237-0
25.40	[1.000]	27.94	[1.100]	11	12	5-534237-9
22.86	[.900]	25.40	[1.000]	10	12	5-534237-8
20.32	[.800]	22.86	[.900]	9	12	5-534237-7
17.78	[.700]	20.32	[.800]	8	12	5-534237-6
15.24	[.600]	17.78	[.700]	7	12	5-534237-5
12.70	[.500]	15.24	[.600]	6	12	5-534237-4
10.16	[.400]	12.70	[.500]	5	12	5-534237-3
7.62	[.300]	10.16	[.400]	4	12	5-534237-2
5.08	[.200]	7.62	[.300]	3	12	5-534237-1
B		A		NO OF POSN	PART NUMBER	

2.54	[.100]	5.08	[.200]	2	12	3-534237-9
99.06	[3.900]	101.60	[4.000]	40	12	3-534237-8
96.52	[3.800]	99.06	[3.900]	39	12	3-534237-7
93.98	[3.700]	96.52	[3.800]	38	12	3-534237-6
91.44	[3.600]	93.98	[3.700]	37	12	3-534237-5
88.90	[3.500]	91.44	[3.600]	36	12	3-534237-4
86.36	[3.400]	88.90	[3.500]	35	12	3-534237-3
83.82	[3.300]	86.36	[3.400]	34	12	3-534237-2
81.28	[3.200]	83.82	[3.300]	33	12	3-534237-1
78.74	[3.100]	81.28	[3.200]	32	12	3-534237-0
76.20	[3.000]	78.74	[3.100]	31	12	2-534237-9
73.66	[2.900]	76.20	[3.000]	30	12	2-534237-8
71.12	[2.800]	73.66	[2.900]	29	12	2-534237-7
68.58	[2.700]	71.12	[2.800]	28	12	2-534237-6
66.04	[2.600]	68.58	[2.700]	27	12	2-534237-5
63.50	[2.500]	66.04	[2.600]	26	12	2-534237-4
60.96	[2.400]	63.50	[2.500]	25	12	2-534237-3
58.42	[2.300]	60.96	[2.400]	24	12	2-534237-2
55.88	[2.200]	58.42	[2.300]	23	12	2-534237-1
53.34	[2.100]	55.88	[2.200]	22	12	2-534237-0
50.80	[2.000]	53.34	[2.100]	21	12	1-534237-9
48.26	[1.900]	50.80	[2.000]	20	12	1-534237-8
45.72	[1.800]	48.26	[1.900]	19	12	1-534237-7
43.18	[1.700]	45.72	[1.800]	18	12	1-534237-6
40.64	[1.600]	43.18	[1.700]	17	12	1-534237-5
38.10	[1.500]	40.64	[1.600]	16	12	1-534237-4
35.56	[1.400]	38.10	[1.500]	15	12	1-534237-3
33.02	[1.300]	35.56	[1.400]	14	12	1-534237-2
30.48	[1.200]	33.02	[1.300]	13	12	1-534237-1
27.94	[1.100]	30.48	[1.200]	12	12	1-534237-0
25.40	[1.000]	27.94	[1.100]	11	12	534237-9
22.86	[.900]	25.40	[1.000]	10	12	534237-8
20.32	[.800]	22.86	[.900]	9	12	534237-7
17.78	[.700]	20.32	[.800]	8	12	534237-6
15.24	[.600]	17.78	[.700]	7	12	534237-5
12.70	[.500]	15.24	[.600]	6	12	534237-4
10.16	[.400]	12.70	[.500]	5	12	534237-3
7.62	[.300]	10.16	[.400]	4	12	534237-2
5.08	[.200]	7.62	[.300]	3	12	534237-1
B		A		NO OF POSN	PART NUMBER	

- 1 HOUSING: FLAME RETARDANT, GLASS FILLED, POLYESTER, COLOR: BLACK. CONTACT: PHOSPHOR BRONZE
- 2 CONTACT: DUPLEX PLATED 0.76µm[.000030] GOLD IN CONTACT AREA, 3.81-7.62µm[.000150-.000300] BRIGHT TIN-LEAD ON LEADS ALL OVER 1.27µm[.000050] MIN NICKEL
- 3 THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY - NOT TO CONTACT LOCATIONS
- 4 PART NUMBER AND DATE CODE MARKED IN APPROXIMATE LOCATION SHOWN, EITHER SIDE.
- 5 TOLERANCE IS NON-CUMULATIVE.
- 6 2 POSITION DATE CODE IS MARKED OPPOSITE SIDE OF TE CONNECTIVITY LOGO.
- 7 POINT-OF-MEASUREMENT DIMENSION FOR PLATING THICKNESS (INSIDE CONTACT BEAM).
- 8 POINT-OF-MEASUREMENT DIMENSION.
- 9 NO PART NUMBER MARKING REQUIRED FOR THIS PART.
- 10 TE CONNECTIVITY LOGO AND CSA LOGO ARE MOLDED INTO HOUSING, THIS LOCATION.
- 11 CONTACT: DUPLEX PLATED 0.76µm[.000030] GOLD IN CONTACT AREA, 3.81-7.62µm[.000150-.000300] MATTE TIN ON LEADS ALL OVER 1.27µm[.000050] MIN NICKEL
- 12 ROHS 2002/95/EC COMPLIANT
- 13 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 14 OBSOLETE.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIN M. BINNER OSNOV02
 CHK J. JOLSON OSNOV02
 APVD J. JOLSON OSNOV02

TE Connectivity

RECT. ASSY, MOD IV, SINGLE ROW, .100CL, VERTICAL BOARD MOUNT, CLOSED, TOP ENTRY, SHORT PNT. OF CONTACT

108-25022
 APPLICATION SPEC
 114-25018

SIZE: A1
 CASE CODE: 00779
 DRAWING NO: 534237

RESTRICTED TO: -

CUSTOMER DRAWING SCALE: 4:1 SHEET: 1 OF 1 REV: R4