

KVASER U100-X3

EAN: 73-30130-01268-4

The Kvaser U100-X3 is a robust, single-channel CAN/CAN FD to USB interface with reinforced galvanic isolation that squarely addresses the needs of the evolving automotive development market. Fully compatible with J1939, CANopen, NMEA 2000[®] and DeviceNet, this is the first in a new range of interfaces that is also suited to rugged applications in marine, industrial, heavy duty vehicle and heavy industries.

Warranty

2-year warranty. See our General Conditions and Policies for details.

Support

Free support for all products by contacting support@kvaser.com.



Major Features

- Supports CAN FD, up to 8 Mbit/s (with correct physical layer implementation).
- Supports both 11-bit (CAN 2.0A) and 29-bit (CAN 2.0B active) identifiers.
- Lightweight, glass fibre reinforced polyamide housing, overmolded with TPE.
- OBD-II connector (other connectors available).
- Intelligent LED UI.
- Reinforced galvanic isolation, design validated with 5000 VAC rms applied for 60 seconds.
- 20000 msg/s, each timestamped with a resolution of 100 μs.
- Support for SocketCAN.
- Compatible with J1939, CANopen, NMEA 2000[®] and DeviceNet.
- Fully compatible with applications written for other Kvaser CAN hardware with Kvaser CANlib.

Software

Documentation, Kvaser CANlib SDK and drivers can be downloaded for free at www.kvaser.com/ downloads.

Kvaser CANIib SDK is a free resource that includes everything you need to develop software for the Kvaser CAN interfaces. Includes full documentation and many program samples, written in C, C++, C#, Delphi, Visual Basic, Python and t programming language.

Kvaser CAN hardware is built around the same common software API. Applications developed using one device type will run without modification on other device types



Technical Data

CAN Bit Rate	10 kbit/s to 1 Mbit/s
CAN FD	Yes
CAN FD Bit Rate	Up to 8 Mbit/s
CAN Channels	1
CAN Transceivers	ADM3055E
Casing Material	PA/TPE
Connector	OBD-II
Current Consumption	Typical 250 mA
Dimensions	38 x 128 x 26 mm
Galvanic Isolation	Yes, reinforced. Validated with 5000 VAC rms applied for 60 seconds.
IP Rating Housing	IP67
Operating Temperature Range	-40 °C to +85 °C
Timestamp Resolution	100 μs
Weight	167 g
Operating Systems	Windows, Linux



+46 31 886344