ACPP Precision Surface Mount Passivated Resistors



- Precision thin film technology
- Extended ohmic range 10R 1M5
- Precision to ±0.1% and 15ppm/°C
- Passivated range for superior humidity performance
- RoHS Compliant



Characteristics

Tolerance (Code): $\pm 0.1\%$ (B), $\pm 0.25\%$ (C) Operating temperature: -55° C to $+155^{\circ}$ C

Temperature coefficient: ±15ppm/°C (A), ±25ppm/°C (E), ±50ppm/°C (F)

Overload: ≤±0.2%, ≤±0.1% (ACPP0402), RCWV*2.5 or maximum overload voltage (whichever is lowest) for 2 seconds

Thermal shock: $\leq \pm 0.02\%$, $\leq \pm 0.1\%$ (ACPP0402), -55°C +150°C 100 cycles

Endurance: $\leq \pm 0.05\%$, $\leq \pm 0.25\%$ (ACPP0402), $70 \pm 2^{\circ}$ C, RCWV for 1000 hours with 1.5 hours on and 0.5 hours off Humidity: $\leq \pm 0.05\%$, $\leq \pm 0.5\%$ (ACPP0402), 1000 hours at $40 \pm 2^{\circ}$ C, 90 - 95% R.H with 1.5 hours on and 0.5 hours off

Electrical Specifications

Туре	Wattage	Maximum operating voltage	Maximum overload voltage	TCR ppm/°C	Ohmic value range	
ACPP0402	0.0625	25V	50V	±15	49R9 - 12K	
			507	±25	24R9 - 24K9	
ACPP0603	0.0625	50V	100V	±15	24R9 - 332K	
				±25		
				±50		
ACPP0805	0.1	100V	200V	±15	10R - 1M	
				±25		
				±50		
ACPP1206	0.125	150V	300V	±15	10R - 1M	
				±25		
				±50		
ACPP2010	0.25	150V	300V	±15	24R9 - 1M	
				±25	10R - 1M5	
				±50		
ACPP2512	0.5	150V	300V	±15	24R9 - 1M	
				±25	10R - 1M5	
				±50	1011 - 11013	

ARCOL UK Limited,

Threemilestone Ind. Estate, Truro, Cornwall, TR4 9LG, UK.

T +44 (0) 1872 277431

F +44 (0) 1872 222002

E sales@arcolresistors.com

www.arcolresistors.com

The information contained herein does not form part of a contract and is subject to change without notice. ARCOL operate a policy of continual product development, therefore, specifications may change.

It is the responsibility of the customer to ensure that the component selected from our range is suitable for the intended application. If in doubt please ask ARCOL.


Page 1 of 2 5/15.34

ACPP Precision Surface Mount Passivated Resistors




Dimensions (mm)

Series	L	W	Т	D1	D2
ACPP0402	1.00 ± 0.05	0.50 ± 0.05	0.30 ± 0.05	0.20 ± 0.10	0.20 ± 0.10
ACPP0603	1.55 ± 0.10	0.80 ± 0.10	0.45 ± 0.10	0.30 ± 0.20	0.30 ± 0.20
ACPP0805	2.00 ± 0.15	1.25 ± 0.15	0.55 ± 0.10	0.30 ± 0.20	0.40 ± 0.20
ACPP1206	3.05 ± 0.15	1.55 ± 0.15	0.55 ± 0.10	0.42 ± 0.20	0.35 ± 0.20
ACPP2010	4.90 ± 0.15	2.40 ± 0.15	0.55 ± 0.10	0.60 ± 0.30	0.50 ± 0.20
ACPP2512	6.30 ± 0.15	3.10 ± 0.15	0.55 ± 0.10	0.60 ± 0.30	0.50 ± 0.20



Derating Curve 100 80 40 40 20 0 20 40 60 80 100 120 140 160 Ambient Temperature (*C)




ARCOL Ordering Procedure

<u>Standard Resistor:</u> Series, Size, Resistance Value, Tolerance, TCR

eg: ACPP0603 100K B 15PPM

Ohmite Ordering Procedure

<u>Standard Resistor:</u> Series, Size, Resistance Value, Tolerance, TCR Code, RoHS compliant



ARCOL UK Limited,

Threemilestone Ind. Estate,

Truro, Cornwall, TR4 9LG, UK.

T +44 (0) 1872 277431

F +44 (0) 1872 222002

E sales@arcolresistors.com

www.arcolresistors.com

The information contained herein does not form part of a contract and is subject to change without notice. ARCOL operate a policy of continual product development, therefore, specifications may change.

It is the responsibility of the customer to ensure that the component selected from our range is suitable for the intended application. If in doubt please ask ARCOL.

Page 2 of 2 5/15.34