

Specifications	Range		Best Accuracy	
	Model	SCAN Mode	AUTO Mode	UT118A
DC Voltage (V)	3V/30V/300V	3V/30V/300V	±(1%+3)	±(1%+3)
AC Voltage (V)	3V/30V/300V	3V/30V/300V	±(1%+4)	±(1%+4)
Resistance (Ω)	300Ω/3kΩ/30kΩ/300kΩ/3MΩ	300Ω/3kΩ/30kΩ/300kΩ/3MΩ/30MΩ	±(1%+3)	±(1%+3)
Capacitance (F)	3nF/30nF/300nF/3μF/30μF/300μF	3nF/30nF/300nF/3μF/30μF/300μF/3mF	±(3%+5)	±(3%+5)
<b>Features</b>				
Display Count			3000	3000
Auto Range			√	√
EF Function				√
Diode			√	√
Auto Power Off	around 10 minutes		√	√
Continuity Buzzer			√	√
Low Battery Indication			√	√
Data Hold			√	√
MAX Mode			√	√
MIN Mode			√	√
LCD Backlight			√	√
Penlight			√	√
Input Impedance for DCV	≥10MΩ		√	√
<b>General Characteristics</b>				
Power	3V Li-MnO <sub>2</sub> Cion cell battery			
LCD Size	28mm × 14mm			
Product Color	Red and grey			
Product Net Weight	90g			
Product Size	20mm × 27mm × 182mm			
Standard Accessories	Battery, test lead			
Standard Individual Packing	Blister, English manual			