




3189
OSCILLATING COMPACT ELBOW
BSP AND METRIC STUD

3189

maximum working pressure	bar 20	MPa 2,0	psi 290
working temperature	°C (Celsius) From -20 to 80	F (Fahrenheit) From -4 to 176	K (Kelvin) From 253 to 353
vacuum capability	mm Hg vacuum level of 755,000		
body	engineering grade polymer		
sub-base	nickel-plated brass		
'O'-rings	nitrile		
gripping ring	stainless steel		



	legris connectic	ØD (mm)	C	E (mm)	F (mm)	ØG (mm)	H (mm)	K (mm)	L (mm)	(kg)
3189 04 10		4	G1/8	5,0	13,0	11,0	23,0	14,0	17,5	0,013
3189 04 19		4	M5x0,8	3,0	12,0	11,0	24,5	13,0	17,5	0,011
3189 06 10		6	G1/8	5,0	14,0	14,0	27,0	15,0	20,5	0,019
3189 06 13		6	G1/4	5,5	16,0	14,0	25,5	17,5	20,5	0,023
3189 06 19		6	M5x0,8	3,0	12,0	14,0	27,5	13,0	20,5	0,017
3189 08 10		8	G1/8	5,0	17,0	16,0	33,5	18,5	23,5	0,034
3189 08 13		8	G1/4	5,5	17,0	16,0	31,0	18,5	23,5	0,034
3189 08 17		8	G3/8	5,5	20,0	16,0	29,5	22,0	23,5	0,042
3189 10 13		10	G1/4	5,5	19,0	19,5	39,0	21,0	29,0	0,058
3189 10 17		10	G3/8	5,5	20,0	19,5	37,0	22,0	29,0	0,055
3189 12 13		12	G1/4	5,5	21,0	22,0	46,5	23,0	33,5	0,014
3189 12 17		12	G3/8	5,5	21,0	22,0	45,5	23,0	33,5	0,020