

# APPROVAL SHEET

# **WR02X(W)**

±5%, ±1%

Thick Film General purpose chip resistors

Size 0201

\*Contents in this sheet are subject to change without prior notice.



#### **FEATURE**

- 1. Small size and light weight
- 2. High reliability and stability
- 3. Reduced size of final equipment
- 4. Suitable for high density print circuit board assembly
- 5. Higher component and equipment reliability
- Lead free product

#### **APPLICATION**

- Mobile phone
- PDA
- Camcorders
- Palmtop computers
- Hybrid module

#### **DESCRIPTION**

The resistors are constructed in a high grade ceramic body (aluminum oxide). Internal metal electrodes are added at each end and connected by a resistive paste that is applied to the top surface of the substrate. The composition of the paste is adjusted to give the approximate resistance required and the value is trimmed to nominated value within tolerance which controlled by laser trimming of this resistive layer.

The resistive layer is covered with a protective coat. Finally, the two external end terminations are added. For ease of soldering the outer layer of these end terminations is a pure Tin.




Fig 1. Construction of Chip-R WR02X



#### **QUICK REFERENCE DATA**


Item	General Specification		
Series No.	WR02X(W)		
Size code	02	201(0603)	
Resistance Range	1Ω~10MΩ ( $\pm 5\%$ tolerance ), Jumper		
	1Ω~ 10MΩ ( $\pm$ 1% tolerance )		
Resistance Tolerance	±1%	±5%	
	E96/E24	E24	
TCR (ppm/°C)	10Ω - 10MΩ, ≤±200		
	1 - 9.76Ω, +600~-200		
Max. dissipation @ T <sub>amb</sub> =70°C	1/20 W		
Max. Operation Voltage (DC or RMS)	25V		
Max. Overload Voltage (DC or RMS)	50V		
Operation temperature	-55 ~ +125'C		

#### Note:

- 1. This is the maximum voltage that may be continuously supplied to the resistor element, see "IEC publication 60115-8"
- 2. Max. Operation Voltage : So called RCWV (Rated Continuous Working Voltage) is determined by  $RCWV = \sqrt{RatedPower \times Resistance Value} \text{ or Max. RCWV listed above, whichever is lower.}$

## **DIMENSION(unit: mm)**

	WR02X(W)	
L	$0.60 \pm 0.03$	
W	$0.30 \pm 0.03$	
Т	$0.23 \pm 0.03$	
Tb	0.15 ± 0.05	
Tt	$0.10 \pm 0.05$	



#### **MARKING**

WR02X(W) has no marking.



#### **FUNCTIONAL DESCRIPTION**

#### **Product characterization**

Standard values of nominal resistance are taken from the E24/E96 series for resistors with a tolerance of  $\pm 5\%$  &  $\pm 1\%$ . The values of the E24/E96 series are in accordance with "IEC publication 60063"

#### Derating

The power that the resistor can dissipate depends on the operating temperature; see Fig.2




Figure 2. Maximum dissipation in percentage of rated power

As a function of the ambient temperature

#### **MOUNTING**

Due to their rectangular shapes and small tolerances, Surface Mountable Resistors are suitable for handling by automatic placement systems.

Chip placement can be on ceramic substrates and printed-circuit boards (PCBs).

Electrical connection to the circuit is by individual soldering condition.

The end terminations guarantee a reliable contact.

#### **SOLDERING CONDITION**

The robust construction of chip resistors allows them to be completely immersed in a solder bath of 260°C for 10 seconds. Therefore, it is possible to mount Surface Mount Resistors on one side of a PCB and other discrete components on the reverse (mixed PCBs).

Surface Mount Resistors are tested for solderability at 235°C during 2 seconds. The test condition for no leaching is 260°C for 30 seconds. Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 3.




Fig 3. Infrared soldering profile for Chip Resistors WR02X(W)



#### **CATALOGUE NUMBERS**

The resistors have a catalogue number starting with:

WR02	X	472_	J	Α	L
Size code	Type code	Resistance code	Tolerance	Packaging code	Termination code
WR02 : 0201	X : Normal W: 1% For <10Ω and >1MΩ	$5\%$ , E24: 2 significant digits followed by no. of zeros and a blank $4.7\Omega = 4R7$ $100\Omega = 101$ $10K\Omega = 103$ $1\%$ , E24+E96: 3 significant digits followed by no. of zeros $100\Omega = 1000$ $37.4K\Omega = 3742$	J:±5% F:±1% P:Jumper	A: 7" Reeled taping (15Kpcs/Reel)  T: 7" Reeled taping (10Kpcs/Reel)  D: 7" Reeled taping (20Kpcs/Reel)  H: 13" Reeled taping (50Kpcs/Reel)  G: 13" Reeled taping (70Kpcs/Reel)	L = Sn base (lead free)

## TEST CONDITION FOR JUMPER (0 $\Omega$ )

	• •
Item	WR02
Power Rating At 70°C	1/20W
Resistance	MAX.50m $Ω$
Rated Current	1A
Peak Current within 5 sec	2.5A
Operating Temperature	-55 ~ +125°C




# **TEST AND REQUIREMENTS (JIS C 5201-1: 1998)**

TEST	DDOCEDURE / TEST METHOD	REQUIREMENT		
TEST	PROCEDURE / TEST METHOD	Resistor	0Ω	
Electrical Characteristics	- DC resistance values measurement - Temperature Coefficient of Resistance (T.C.R)	Within the specified tolerance Refer to "QUICK		
JISC5201-1: 1998 Clause 4.8	Natural resistance change per change in degree centigrade.	REFERENCE DATA"		
	$\frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \text{ (ppm/°C)}  t_1 : 20\text{°C} + 5\text{°C} - 1\text{°C}$		<50mΩ	
	$R_1$ : Resistance at reference temperature (20°C+5°C/-1°C)			
	R₂: Resistance at test temperature (-55℃ or +125℃)			
Short time overload (S.T.O.L) Clause 4.13	Permanent resistance change after a 5second application of a voltage 2.5 times RCWV or the maximum overload voltage specified in the above list, whichever is less.	$\Delta$ R/R max. ±(2%+0.10 $\Omega$ )	<50mΩ	
Resistance to soldering heat(R.S.H)	Un-mounted chips completely immersed for 10±1second in a SAC solder bath at 260°C±5°C	$\Delta$ R/R max. $\pm$ (1%+0.05 $\Omega$ ) no visible damage	<50mΩ	
Clause 4.18		· ·		
Solderability Clause 4.17	Un-mounted chips completely immersed for 2±0.8second in a SAC solder bath at 235°C ±5°C	95% coverage min., good tinnii visible damage	ng and no	
Temperature cycling Clause 4.19	30 minutes at -55°C±3°C, 2~3 minutes at 20°C+5°C-1°C, 30 minutes at +125°C±3°C, 2~3 minutes at 20°C+5°C-1°C, total 5 continuous cycles	$\Delta$ R/R max. ±(1%+0.05 $\Omega$ )	< 50mΩ	
Damp Heat	1000 +48/-0 hours, loaded with RCWV or Vmax in	10Ω≤R<1MΩ :		
(Load life in humidity) Clause 4.24	humidity chamber controller at 40°C±2°C and 90~95% relative humidity, 1.5hours on and 0.5 hours off	$\Delta$ R/R max. ±(3%+0.10Ω) R<10Ω, R≥1MΩ : $\Delta$ R/R max. ±(5%+0.10Ω)	< 50mΩ	
Load Life (Endurance)	1000+48/-0 hours; loaded with RCWV or V <sub>max</sub> in chamber	Ditto.		
Clause 4.25	controller 70±2°C, 1.5 hours on and 0.5 hours off		r	
Bending strength	Resistors mounted on a 90mm glass epoxy resin	No visual damaged,	< 50mΩ	
Clause 4.33	PCB(FR4), bending once 5mm for 10sec.	$\Delta$ R/R max. $\pm$ (1%+0.05 $\Omega$ )	~ JUIII22	
Adhesion	Pressurizing force: 3N, Test time: 10±1sec.	No remarkable damage or remo	oval of the	
Clause 4.32		terminations		



#### **PACKAGING**


#### Paper Tape specifications (unit :mm)



Series No.	Α	В	W	F	E
WR02X	0.67±0.05	0.37±0.05	8.00±0.20	3.50±0.05	1.75±0.10

Series No.	P1	P0	ΦD	Т
WR02X	2.00±0.05	4.00±0.05	$\Phi$ 1.50 $^{+0.1}_{-0.0}$	0.45±0.05

#### **Reel dimensions**



Symbol	Α	В	С	D
7" Reel	Φ178.0±0.2	Φ60.0±1.0	13.0±0.2	9.0±0.5
10" Reel	Ф254.0±2.0	Φ100.0±1.0	13.0±0.2	9.0±0.5
13" Reel	Ф330.0±2.0	Φ100.0±1.0	13.0±0.2	9.0±0.5

#### **Taping quantity and Tape material**

- Chip resistors 10,000 / 15,000 / 20,000 pcs 7" Reel, Paper tape.
- Chip resistors 50,000 / 70,000 pcs 13" Reel, Paper tape.

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

#### Walsin:

```
WR02X6803FAL WR02W1804FAL WR02X203 JTL WR02X1003FTL WR02X560 JAL WR02X1500FAL
WR02X472 JTL WR02X3902FAL WR02X1001FTL WR02X101 JAL WR02X1000FTL WR02X1803FAL
WR02X27R0FAL WR02X2000FTL WR02X1001FAL WR02X1000FAL WR02X2000FAL WR02W1154FAL
WR02X1202FAL WR02X6041FAL WR02X222 JAL WR02X2492FAL WR02X7501FAL WR02X180 JAL
WR02X61R9FAL WR02X1503FAL WR02X4321FAL WR02X1471FAL WR02X30R0FAL WR02X4320FAL
WR02X30R1FAL WR02X2430FAL WR02X1870FAL WR02X24R3FAL WR02X1272FAL WR02X5623FAL
WR02X18R7FAL WR02X20R0FAL WR02X000 PAL WR02X8660FAL WR02X9091FAL WR02X76R8FAL
WR02X3901FAL WR02X2402FAL WR02X7680FAL WR02X201 JAL WR02X1502FAL WR02X4753FAL
WR02X68R1FAL WR02X82R0FAL WR02X3321FAL WR02X2202FAL WR02X3011FAL WR02X390 JAL
WR02X1962FAL WR02X8203FAL WR02X132 JAL WR02X4640FAL WR02X6650FAL WR02X754 JAL WR02X824
JAL WR02X1782FAL WR02X2743FAL WR02X3300FAL WR02X204 JAL WR02X4991FAL WR02X100 JAL
WR02X1963FAL WR02X5100FAL WR02X9093FAL WR02X681 JAL WR02X1473FAL WR02X104 JAL
WR02X46R4FAL WR02X2742FAL WR02X130 JAL WR02X6190FAL WR02X334 JAL WR02X6802FAL
WR02X17R8FAL WR02X1583FAL WR02X4641FAL WR02X181 JAL WR02X2700FAL WR02X7681FAL
WR02X4642FAL WR02X1691FAL WR02X7682FAL WR02X47R0FAL WR02X2201FAL WR02X7500FAL
WR02X153 JAL WR02X9103FAL WR02X1690FAL WR02X122 JAL WR02X1002FAL WR02X6801FAL
WR02X5620FAL WR02X1653FAL WR02X1871FAL
```