## Product data sheet Characteristics

### XACA04

Enclosure material

Enclosure type

Electrical circuit type

# empty pendant control station XAC-A - 4 vertical openings



# Main Range of product Harmony XAC Product or component type Pendant control station Control station name XACA Control station type Double insulated

Polypropylene

Control circuit

Empty enclosure

| Number of cut-out | 4 cut-outs   |  |  |
|-------------------|--|--|--|
| Cable entry       | Rubber sleeve with stepped entry, cable outer diameter: 826 mm |  |  |

Guard rail Without

Cutout in base of enclo- With

#### Complementary

| Control station colour           | Yellow         |  |  |
|----------------------------------|----------------|--|--|
| Vertical operator cut-out centre | 30 mm          |  |  |
| Mechanical durability            | 1000000 cycles |  |  |
| Product weight                   | 0.54 kg        |  |  |


#### Environment

| Standards                                  | CSA C22-2 No 14                                  |  |  |  |  |
|--|--|--|--|--|--|
| Clarida do                                 | EN/IEC 60204-32                                  |  |  |  |  |
|  | EN/IEC 60947-5-1                                 |  |  |  |  |
|  | UL 508   |  |  |  |  |
| Product certifications                     | CCC  |  |  |  |  |
|  | GOST   |  |  |  |  |
| Protective treatment                       | TH   |  |  |  |  |
| Ambient air temperature for operation      | -2570 °C   |  |  |  |  |
| Ambient air temperature for storage        | -4070 °C   |  |  |  |  |
| Vibration resistance                       | 15 gn (f = 10500 Hz) conforming to IEC 60068-2-6 |  |  |  |  |
| Shock resistance                           | 100 gn conforming to IEC 60068-2-27              |  |  |  |  |
| Class of protection against electric shock | Class II conforming to IEC 61140                 |  |  |  |  |
| IP degree of protection                    | IP65 conforming to IEC 60529                     |  |  |  |  |
| IK degree of protection                    | IK08 conforming to EN 50102                      |  |  |  |  |

#### **Dimensions**

Below drawing shows a product with 6 cut-outs. Select the number of cut-outs according to the product characteristics in order to get b, b1 and c dimensions.





- For 2 and 3-way XAC A stations.
- For 4 to 8-way XAC A stations.
- (2) (3) With trigger action Emergency stop head operator
- (4) Internal ø

#### Dimensions in mm

| Number of cut-outs | 2   | 3   | 4   | 5   | 6   | 8   | 12  |
|--------------------|-----|-----|-----|-----|-----|-----|-----|
| b                  | 314 | 314 | 440 | 440 | 500 | 560 | 680 |
| b1                 | 190 | 190 | 250 | 250 | 310 | 370 | 490 |
| С                  | 80  | 80  | 80  | 80  | 80  | 80  | 92  |

#### Dimensions in in.

| Number of cut-outs | 2     | 3     | 4     | 5     | 6     | 8     | 12    |
|--------------------|-------|-------|-------|-------|-------|-------|-------|
| b                  | 12.36 | 12.36 | 17.32 | 17.32 | 19.68 | 22.05 | 26.77 |
| b1                 | 7.48  | 7.48  | 9.84  | 9.84  | 12.20 | 14.57 | 19.29 |
| С                  | 3.15  | 3.15  | 3.15  | 3.15  | 3.15  | 3.15  | 3.62  |