


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

| | | | | | | | |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
| LOC | DIST | REVISIONS | | | | | |
| AD | 00 | P | LTR | DESCRIPTION | DATE | DWN | APVD |
| | | M2 | | REVISED PER ECO-11-004820 | 11MAR11 | RK | HMR |



- 1 CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS.
- 2 USE WITH #26-#30 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS.
- 3 THE DIMENSION APPLIES WITH THE FORWARD STOP IN CONTACT WITH THE HOUSING SURFACE
- 4 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 5. FOR INDIVIDUAL ASSEMBLIES SEE PART NUMBER 103640
- 6 ASSEMBLIES ARE JOINED BY THE CARRIER STRIP. ORDER QUANTITY REFLECTS TOTAL NUMBER OF INDIVIDUAL ASSEMBLIES REQUIRED. SEE TABLE FOR NUMBER OF ASSEMBLIES PER STRIP.
- 7 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)
- 8 MAXIMUM ALLOWABLE BOW OF ASSEMBLY NOT TO EXCEED .055.
- 9 .000015 GOLD IN THE CONTACT AREA. .000050-.000100 BRIGHT TIN-LEAD ON THE TERMINATION AREA, ALL OVER .000050 NICKEL.
- 10 .000015 GOLD IN THE CONTACT AREA. .000050-.000100 BRIGHT TIN ON THE TERMINATION AREA, ALL OVER .000050 NICKEL.
- 11 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 12 .000015 GOLD IN THE CONTACT AREA. .000050-.000100 MATTE TIN ON THE TERMINATION AREA, ALL OVER .000050 NICKEL.
- 13 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

| | | | | | | | | |
|---------|----------|----|----|------|-------|---------------------|------------|-------------------------------|
| 13 | OBSOLETE | 12 | 2 | 2.40 | 1.198 | 1-104257-1 | 12 | 6-103960-1 |
| 13 | OBSOLETE | 12 | 2 | 2.20 | 1.098 | 1-104257-0 | 11 | 6-103960-0 |
| | | 12 | 2 | 2.00 | .998 | 104257-9 | 10 | 5-103960-9 |
| 13 | OBSOLETE | 12 | 2 | 1.80 | .898 | 104257-8 | 9 | 5-103960-8 |
| | | 12 | 2 | 1.60 | .798 | 104257-7 | 8 | 5-103960-7 |
| | | 12 | 2 | 1.40 | .698 | 104257-6 | 7 | 5-103960-6 |
| | | 12 | 4 | 2.39 | .598 | 104257-5 | 6 | 5-103960-5 |
| | | 12 | 4 | 1.99 | .498 | 104257-4 | 5 | 5-103960-4 |
| | | 12 | 5 | 1.99 | .398 | 104257-3 | 4 | 5-103960-3 |
| | | 12 | 8 | 2.40 | .298 | 104257-2 | 3 | 5-103960-2 |
| | | 12 | 10 | 2.00 | .198 | 104257-1 | 2 | 5-103960-1 |
| | | 11 | 5 | 1.99 | .398 | 104257-3 | 4 | 1-103960-2 |
| 13 | OBSOLETE | 9 | 2 | 2.40 | 1.198 | 1-104257-1 | 12 | 1-103960-1 |
| | | 9 | 2 | 2.20 | 1.098 | 1-104257-0 | 11 | 1-103960-0 |
| | | 9 | 2 | 2.00 | .998 | 104257-9 | 10 | 103960-9 |
| | | 9 | 2 | 1.80 | .898 | 104257-8 | 9 | 103960-8 |
| | | 9 | 2 | 1.60 | .798 | 104257-7 | 8 | 103960-7 |
| | | 9 | 2 | 1.40 | .698 | 104257-6 | 7 | 103960-6 |
| | | 9 | 4 | 2.39 | .598 | 104257-5 | 6 | 103960-5 |
| | | 9 | 4 | 1.99 | .498 | 104257-4 | 5 | 103960-4 |
| | | 9 | 5 | 1.99 | .398 | 104257-3 | 4 | 103960-3 |
| | | 9 | 8 | 2.40 | .298 | 104257-2 | 3 | 103960-2 |
| | | 9 | 10 | 2.00 | .198 | 104257-1 | 2 | 103960-1 |
| PLATING | | 6 | B | A | | HOUSING PART NUMBER | NO OF POSN | ASSEMBLY PART NUMBER ON STRIP |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN L A MAYER 11-4-86
 CHK P de JONG 11-4-86
 APVD P de JONG 11-4-86

TE Connectivity

RCPT ASSY, AMPMODU MTE, SINGLE ROW, .100 C/L, LATCHED & POLARIZED FOR NO 26- NO 30 AWG WIRE SIZE, STRIP FORM

108-25034
 114-25026

SIZE A2 CAGE CODE 00779 DRAWING NO C=103960

WEIGHT -

CUSTOMER DRAWING SCALE 3:1 SHEET 1 of 1 REV M2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-103960-3](#)