

PCB TERMINAL BLOCKS

PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES


DIN RAIL
ENCLOSURES

BATTERIES


SOLAR
PANELS

TRANS-
FORMERS

7.62mm Pitch Standard Profile Rising Clamp Terminal Blocks

- 2 & 3 pole double interlocking mechanism for increased strength
- 4-12 pole pre-assembled
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 0.2-4.0mm² (30-12AWG) solid cable
- 0.2-2.5mm² (30-12AWG) stranded cable
- Guided pin alignment
-  approved


CTB0118




TYPE NO.	POLES	LENGTH
CTB0118/2	2	15.2mm
CTB0118/3	3	22.9mm
CTB0118/4	4	30.5mm
CTB0118/5	5	38.1mm
CTB0118/6	6	45.7mm
CTB0118/7	7	53.3mm
CTB0118/8	8	61mm
CTB0118/9	9	68.6mm
CTB0118/10	10	76.2mm
CTB0118/11	11	83.8mm
CTB0118/12	12	91.4mm

SPECIFICATION

Rating	24A/500V UL=14A/300V, VDE&IMQ=24A/750V
Dielectric strength	≥3kV
Impulse withstand voltage	6kV
Working temperature	110°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	Tinned, nickel plated brass
Rising clamp	Tinned, nickel plated brass
Screw/torque	M3 steel zinc plated, 0.5Nm
Recommended PCB hole size	ø1.5mm



7.62mm Pitch Standard Profile 90° Rising Clamp Terminal Blocks

- 2 & 3 pole double interlocking mechanism for increased strength
- 4-12 pole pre-assembled
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 0.2-4.0mm² (30-12AWG) solid cable
- 0.2-2.5mm² (30-12AWG) stranded cable
- Guided pin alignment
-  approved


CTB01HL



TYPE NO.	POLES	LENGTH
CTB01HL/2	2	15.2mm
CTB01HL/3	3	22.9mm
CTB01HL/4	4	30.5mm
CTB01HL/5	5	38.1mm
CTB01HL/6	6	45.7mm
CTB01HL/7	7	53.3mm
CTB01HL/8	8	61mm
CTB01HL/9	9	68.6mm
CTB01HL/10	10	76.2mm
CTB01HL/11	11	83.8mm
CTB01HL/12	12	91.4mm

SPECIFICATION

Rating	24A/500V UL=16A/300V, VDE&IMQ=24A/750V
Dielectric strength	≥3kV
Impulse withstand voltage	6kV
Working temperature	110°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	Tinned, nickel plated brass
Rising clamp	Tinned, nickel plated brass
Screw/torque	M3 steel zinc plated, 0.5Nm
Recommended PCB hole size	ø1.5mm



For other dimensions see CTB0118