

KAA-3528	KA-2734	KA-3022-4.5SF
----------	---------	---------------

Part No.	Emitting Color + Material	Wave-length (nm)	Lens Type	Iv (mcd) @20mA		Viewing Angle	Dimension
				Min.	Typ.		

KAA-3528ESGC	GaAsP/GaP	625	water clear	12	30	120°	<p>3.5mm x 2.8mm</p>	
	GaP	565		12	30			
KAA-3528SURKSGC	InGaAlP	640	water clear	80	200	120°		
	GaP	565		12	30			
KAA-3528EMBSGC (Full Color)	GaAsP/GaP	625	water clear	12	30	120°		
	GaP	565		12	30			
	GaN	430		5	20			

KA-2734ESGC	GaAsP/GaP	625	water clear	8	30	120°	<p>2.7mm x 3.4mm</p>
	GaP	565		8	30		
KA-2734SRSGC	GaAlAs	660	water clear	80	150	120°	
	GaP	565		8	30		

KA-3022HC-4.5SF	GaP	700	water clear	1	2.5	90°	<p>3.0mm x 2.2mm</p>
KA-3022HT-4.5SF	GaP	700	red transparent	1	2.5	90°	
KA-3022EC-4.5SF	GaAsP/GaP	625	water clear	8	40	90°	
KA-3022IT-4.5SF	GaAsP/GaP	625	red transparent	8	40	90°	
KA-3022YC-4.5SF	GaAsP/GaP	590	water clear	5	20	90°	
KA-3022YT-4.5SF	GaAsP/GaP	590	yellow transparent	5	20	90°	
KA-3022SRC-4.5SF	GaAlAs	660	water clear	70	150	90°	
KA-3022SRT-4.5SF	GaAlAs	660	red transparent	70	150	90°	
KA-3022SGC-4.5SF	GaP	565	water clear	8	30	90°	
KA-3022SGT-4.5SF	GaP	565	green transparent	8	30	90°	
KA-3022SYC-4.5SF	InGaAlP	590	water clear	70	150	90°	
KA-3022SYT-4.5SF	InGaAlP	590	yellow transparent	70	150	90°	

NOTES :

1. All dimensions are in millimeters (inches)
2. Tolerance is ±0.25mm(0.01") unless otherwise noted.