


# AP2N7002

## N-Channel Power MOSFET

- ▼ Simple Drive Requirement
- ▼ Small Package Outline
- ▼ Surface Mount Device
- ▼ RoHS Compliant & Halogen-Free




$BV_{DSS}$	60V
$R_{DS(ON)}$	2 $\Omega$
$I_D$	450mA

### Description

Advanced Power MOSFETs utilized advanced processing techniques to achieve the lowest possible on-resistance, extremely efficient and cost-effectiveness device.

The SOT-23 package is universally used for all commercial-industrial applications.



### Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
$V_{DS}$	Drain-Source Voltage	60	V
$V_{GS}$	Gate-Source Voltage	$\pm 20$	V
$I_D@T_A=25^\circ C$	Continuous Drain Current <sup>3</sup> , $V_{GS}$ @ 10V	450	mA
$I_D@T_A=70^\circ C$	Continuous Drain Current <sup>3</sup> , $V_{GS}$ @ 10V	360	mA
$I_{DM}$	Pulsed Drain Current <sup>1</sup>	950	mA
$P_D@T_A=25^\circ C$	Total Power Dissipation	0.7	W
	Linear Derating Factor	0.005	W/ $^\circ C$
$T_{STG}$	Storage Temperature Range	-55 to 150	$^\circ C$
$T_J$	Operating Junction Temperature Range	-55 to 150	$^\circ C$

### Thermal Data

Symbol	Parameter	Value	Unit
$R_{thj-a}$	Maximum Thermal Resistance, Junction-ambient <sup>3</sup>	180	$^\circ C/W$

**N-Channel Power MOSFET**

**Electrical Characteristics@T<sub>j</sub>=25°C(unless otherwise specified)**


Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	V <sub>GS</sub> =0V, I <sub>D</sub> =250uA	60	-	-	V
ΔBV <sub>DSS</sub> /ΔT <sub>j</sub>	Breakdown Voltage Temperature Coefficient	Reference to 25°C, I <sub>D</sub> =1mA	-	0.06	-	V/°C
R <sub>DS(on)</sub>	Static Drain-Source On-Resistance <sup>2</sup>	V <sub>GS</sub> =10V, I <sub>D</sub> =450mA	-	-	2	Ω
		V <sub>GS</sub> =4.5V, I <sub>D</sub> =200mA	-	-	4	Ω
V <sub>GS(th)</sub>	Gate Threshold Voltage	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250uA	1	-	2.5	V
g <sub>fs</sub>	Forward Transconductance	V <sub>DS</sub> =10V, I <sub>D</sub> =450mA	-	400	-	mS
I <sub>DSS</sub>	Drain-Source Leakage Current	V <sub>DS</sub> =60V, V <sub>GS</sub> =0V	-	-	10	uA
	Drain-Source Leakage Current (T <sub>j</sub> =70°C)	V <sub>DS</sub> =48V, V <sub>GS</sub> =0V	-	-	100	uA
I <sub>GSS</sub>	Gate-Source Leakage	V <sub>GS</sub> =±20V, V <sub>DS</sub> =0V	-	-	±30	uA
Q <sub>g</sub>	Total Gate Charge <sup>2</sup>	I <sub>D</sub> =450mA	-	1	1.6	nC
Q <sub>gs</sub>	Gate-Source Charge	V <sub>DS</sub> =50V	-	0.5	-	nC
Q <sub>gd</sub>	Gate-Drain ("Miller") Charge	V <sub>GS</sub> =4.5V	-	0.5	-	nC
t <sub>d(on)</sub>	Turn-on Delay Time <sup>2</sup>	V <sub>DS</sub> =30V	-	12	-	ns
t <sub>r</sub>	Rise Time	I <sub>D</sub> =450mA	-	10	-	ns
t <sub>d(off)</sub>	Turn-off Delay Time	R <sub>G</sub> =3.3Ω, V <sub>GS</sub> =10V	-	56	-	ns
t <sub>f</sub>	Fall Time	R <sub>D</sub> =52Ω	-	29	-	ns
C <sub>iss</sub>	Input Capacitance	V <sub>GS</sub> =0V	-	32	50	pF
C <sub>oss</sub>	Output Capacitance	V <sub>DS</sub> =25V	-	8	-	pF
C <sub>rss</sub>	Reverse Transfer Capacitance	f=1.0MHz	-	6	-	pF

**Source-Drain Diode**


Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
V <sub>SD</sub>	Forward On Voltage <sup>2</sup>	I <sub>S</sub> =450mA, V <sub>GS</sub> =0V	-	-	1.2	V

**Notes:**


- 1.Pulse width limited by Max. junction temperature.
- 2.Pulse test
- 3.Surface mounted on 1 in<sup>2</sup> copper pad of FR4 board t ≤ 10sec; 400°C/W when mounted on min. copper pad.




**Fig 1. Typical Output Characteristics**




**Fig 2. Typical Output Characteristics**




**Fig 3. On-Resistance v.s. Gate Voltage**



**Fig 4. Normalized On-Resistance v.s. Junction Temperature**




**Fig 5. Forward Characteristic of Reverse Diode**




**Fig 6. Gate Threshold Voltage v.s. Junction Temperature**


**AP2N7002**  
**N-Channel Power MOSFET**




**Fig 7. Gate Charge Characteristics**




**Fig 8. Typical Capacitance Characteristics**




**Fig 9. Maximum Safe Operating Area**



**Fig 10. Effective Transient Thermal Impedance**



**Fig 11. Transfer Characteristics**



**Fig 12. Gate Charge Waveform**