

## DCF850E2T-QW

### 18V XR Brushless Compact Impact Driver - 2 X POWERSTACK

Our smallest most powerful 18V XR impact driver giving you more comfort and better application speed. The DCF850 delivers 205Nm in a 100mm compact body perfect for a wide range of applications across construction, industrial and automotive environments. Other features include a 3 mode switch for enhanced control including Precision Drive which stops the material and fastener been damaged in smaller jobs and a LED ring light to deliver the best visibility in the toughest environments. POWERSTACK batteries deliver 50% more power\*\* with a 25% smaller\*\* footprint that works with all the 18V XR tools you already have. \*\* Regarding 50% more power: vs. DCB183 battery, not in application. Regarding 25% smaller pack and more compact: footprint vs. DCB183 battery.

#### Selling Propositions

- 3 luci LED ad anello per un illuminazione uniforme senz
- Application control is achieved through 3 motor speeds and torque settings including Precision Drive
- New compact brushless motor allows you to fit into tight spaces
- Compatible with all DEWALT 18V XR & Flex Volt battery packs
- High power Brushless motor outputting 205Nm of torque ensures heavy applications are completed effectively
- New and more efficient brushless motor, outputting 3250 Rpm no load speed allowing you to complete applications faster

#### Standard Equipment

#### Warranty specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Max. Torque	205.0 Nm
No. of Modes	3.0
No Load Speed	0-1000/2800/3250
Impacts per Minute	3800 ipm
Bit Holder	6.35mm
Battery Voltage	18
Battery Chemistry	Li-Ion
Weight	0.9 kg
Length	101.0 mm
Height	200.0 mm