
### STTH5L06



### Turbo 2 ultrafast high voltage rectifier

Datasheet - production data



### **Description**

The device is developed using ST's Turbo 2 600 V technology. It is well-suited as a boost diode, especially for use in continuous mode power factor corrections and hard switching conditions.

This device is also intended for use as a free wheeling diode in power supplies and other power switching applications.

**Table 1: Device summary** 

Symbol Value		
I <sub>F(AV)</sub>	5 A	
$V_{RRM}$	600 V	
I <sub>R</sub> (max)	125 μΑ / 150 μΑ	
T <sub>j</sub> (max)	175 °C	
V <sub>F</sub> (typ)	0.85 V	
t <sub>rr</sub> (typ)	65 ns	

### **Features**

- Ultrafast switching
- Low reverse recovery current
- Reduces switching losses
- Low thermal resistance
- Insulated package: TO-220FPAC
  - Insulation voltage: 2000 V<sub>RMS</sub> sine
- ECOPACK®2 compliant component for

DPAK on demand

Characteristics STTH5L06

### 1 Characteristics

Table 2: Absolute ratings (limiting values at 25 °C, unless otherwise specified)

Symbol		Parameter		Value	Unit
V <sub>RRM</sub>	Repetitive peak reverse voltage			600	V
I <sub>F(RMS)</sub>	TO-220F		TO-220AC TO-220FPAC DO-201AD	20	А
			DPAK	10	
		TO-220AC, DPAK	T <sub>C</sub> = 150 °C		
I <sub>F(AV)</sub>	Average forward current δ = 0.5, square wave	DO-201AD	T <sub>I</sub> = 50 °C 5		А
	o o.o, oquare wave	TO-220FPAC			
I <sub>FRM</sub>	Repetitive peak forward current	t <sub>P</sub> = 5 μs, F = 5 kHz squa	$t_P = 5 \mu s$ , $F = 5 kHz square$		Α
	Surge non repetitive	TO-220AC TO-220FPAC		90	
IFSM	forward current	t <sub>p</sub> = 10 ms sinusoidal	DO-201AD	110	Α
			DPAK	60	
T <sub>stg</sub>	T <sub>stg</sub> Storage temperature range			-65 to +175	°C
Tj	Maximum operating junction	on temperature		175	ů

**Table 3: Thermal parameter** 

Symbol	Pa	Max. value	Unit		
Б	lunction to coop	TO-220AC / DPAK	3.5	°C // //	
R <sub>th(j-c)</sub>	Junction to case	TO-220FPAC	6	°C/W	
R <sub>th(j-l)</sub>	Junction to lead	1 10 mm DO 201AD	20	°C // //	
R <sub>th(j-a)</sub>	Junction to ambient	L = 10 mm, DO-201AD	75	°C/W	

STTH5L06 Characteristics

**Table 4: Static electrical characteristics** 

Symbol	Parameter	Test conditions			Min.	Тур.	Max.	Unit
		T <sub>j</sub> = 25 °C	V <sub>R</sub> = 600 V		-		5	
I <sub>R</sub> <sup>(1)</sup>	Reverse leakage current	T <sub>j</sub> = 150 °C	V <sub>R</sub> = 600 V	TO-220AC TO-220FPAC DPAK	-	10	125	μA
				DO-201AD	-	25	150	
V <sub>F</sub> <sup>(2)</sup>	Forward	T <sub>j</sub> = 25 °C	I 5 A		-		1.30	V
VF(=)	voltage drop	T <sub>j</sub> = 150 °C	I <sub>F</sub> = 5 A		-	0.85	1.05	V

#### Notes:

 $^{(1)}$ Pulse test: t<sub>p</sub> = 5 ms,  $\delta$  < 2%

To evaluate the conduction losses, use the following equation:

 $P = 0.89 \text{ x } I_{F(AV)} + 0.033 \text{ x } I_{F^2(RMS)}$ 

**Table 5: Dynamic electrical characteristics** 

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
t <sub>rr</sub>	Reverse recovery time	T <sub>j</sub> = 25 °C	$I_F = 1 A$ $V_R = 30 V$ $dI_F/dt = -50 A/\mu s$	-	65	95	ns
t <sub>fr</sub>	Forward recovery time	T <sub>j</sub> = 25 °C	I <sub>F</sub> = 5 A V <sub>FR</sub> = 1.1 x V <sub>F</sub> max dI <sub>F</sub> /dt = 100 A/µs	-		150	ns
V <sub>FP</sub>	Forward recovery voltage		I <sub>F</sub> = 5 A dI <sub>F</sub> /dt = 100 A/μs	-		7	V

 $<sup>^{(2)}\</sup>text{Pulse}$  test:  $t_p$  = 380  $\mu\text{s},\,\delta$  < 2%

Characteristics STTH5L06

#### 1.1 **Characteristics (curves)**



current 100.0 T<sub>j</sub> = 150 °C (maximum values 10.0 1.0 0.0 0.5 1.0 1.5 V<sub>F</sub>(V) 2.0 3.0

Figure 2: Forward voltage drop versus forward

0.5 1.0 1.5 2.0 2.5 3.0 3.5 4.0 4.5 5.0  $I_{\mathsf{F}(\mathsf{AV})}(\mathsf{A})$ 


Figure 3: Relative variation of thermal impedance junction to case versus pulse duration (TO-220AC, DPAK)  $Z_{th(j-c)}/R_{th(j-c)}$ 1.0 0.9 0.8 0.7 0.6 0.5 0.4 0.3  $\delta = 0.1$ 0.2 Single 0.1 0.0  $t_p(s)$ 

Figure 4: Relative variation of thermal impedance junction to case versus pulse duration (TO-220FPAC)  $Z_{th(j-c)}/R_{th(j-c)}$ 0.9 0.8 0.7 0.6 0.5 0.4  $0.3 \ \bar{\delta} = 0.2$  $0.2 \ \delta = 0.1$ 0.1 ∰\_ δ =tp/T 0.0 1.E-03 1.E-02 1.E-01 1.E+00 1.E+01  $t_p(s)$ 

junction to ambient versus pulse duration (DO-201AD)  $Z_{th(j-a)}/R_{th(j-a)}$ 1.0 Epoxy FR4, L<sub>leads</sub> = 10 mm 0.9 0.8 0.7 0.6 0.5 0.2  $\delta = tp/T$ 1.E+01 1.E+03

 $t_p(s)$ 

Figure 5: Relative variation of thermal impedance



4/15 DocID8371 Rev 5 STTH5L06 Characteristics







Figure 8: Reverse recovery charges versus dl<sub>F</sub>/dt (typical values)  $Q_{rr}(nC)$ 500 V<sub>R</sub> = 400 V I<sub>F</sub> = 2 x I<sub>F(AV)</sub> 450 T = 125 °C 400  $I_F = I_{F(AV)}$ 350 le = 0.5 x le 300 250 200 150 100 50 0 10 20 100 30 40 90 dl<sub>F</sub>/dt(A/µs)


Figure 9: Softness factor versus dl<sub>F</sub>/dt (typical values) Sfactor 2.4 I<sub>F</sub> = I<sub>F(AV)</sub> V<sub>R</sub> = 400 V 2.2 T<sub>j</sub> = 125°C 2.0 1.8 1.6 1.4 1.2 1.0 0.8 0.6 0.4 0.2 10 20 30 50 60 70 80 90 100  $dI_F/dt(A/\mu s)$ 









**Characteristics** STTH5L06







DocID8371 Rev 5 6/15

### 2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: **www.st.com**. ECOPACK® is an ST trademark.

- Cooling method: by conduction (C)
- Epoxy meets UL 94,V0
- Recommended torque value: 0.55 N·m (for TO-220FPAC / TO-220AC)
- Maximum torque value: 0.7 N·m (for TO-220FPAC / TO-220AC)

### 2.1 TO-220AC package information

Figure 16: TO-220AC package outline

H2

A

C

C

L5

L7

L4

F

G

Table 6: TO-220AC package mechanical data

	Dimensions				
Ref.	Millim	neters	Inches		
	Min.	Min. Max.		Max.	
А	4.40	4.60	0.173	0.181	
С	1.23	1.32	0.048	0.051	
D	2.40	2.72	0.094	0.107	
Е	0.49	0.70	0.019	0.027	
F	0.61	0.88	0.024	0.034	
F1	1.14	1.70	0.044	0.066	
G	4.95	5.15	0.194	0.202	
H2	10.00	10.40	0.393	0.409	
L2	16.40	typ.	0.645 typ.		
L4	13.00	14.00	0.511	0.551	
L5	2.65	2.95	0.104	0.116	
L6	15.25	15.75	0.600	0.620	
L7	6.20	6.60	0.244	0.259	
L9	3.50	3.93	0.137	0.154	
М	2.6	typ.	0.102	2 typ.	
ØI	3.75	3.85	0.147	0.151	

# 2.2 TO-220FPAC package information

Figure 17: TO-220FPAC package outline




Table 7: TO-220FPAC package mechanical data

		Dimer	nsions		
Ref.	Millim	neters	Inches		
	Min.	Min. Max.		Max.	
А	4.40	4.60	0.173	0.181	
В	2.50	2.70	0.098	0.106	
D	2.50	2.75	0.098	0.108	
E	0.45	0.70	0.018	0.027	
F	0.75	1.00	0.030	0.039	
F1	1.15	1.70	0.045	0.067	
G	4.95	5.20	0.195	0.205	
G1	2.40	2.70	0.094	0.106	
Н	10.00	10.40	0.393	0.409	
L2	16.00	) typ.	0.630	O typ.	
L3	28.60	30.60	0.126	1.205	
L4	9.80	10.60	0.386	0.417	
L6	15.90	16.40	0.626	0.646	
L7	9.00	9.30	0.354	0.366	
Dia.	3.00	3.20	0.118	0.126	

### 2.3 DO-201AD package information

Figure 18: DO-201AD package outline





Table 8: DO-201AD package mechanical data

	Dimensions			
Ref.	Millim	eters	Inc	ches
	Min.	Max.	Min.	Max.
А		9.50		0.374
В	25.40		1.000	
ØC		5.30		0.209
ØD		1.30		0.051
E		1.25		0.049

Package information STTH5L06

# 2.4 DPAK package information

Figure 19: DPAK package outline






This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.

Downloaded from Arrow.com.

Table 9: DPAK package mechanical data

		Din	nensions	
Ref.	Milli	Millimeters		hes
	Min.	Max.	Min.	Max.
А	2.18	2.40	0.085	0.094
A1	0.90	1.10	0.035	0.043
A2	0.03	0.23	0.001	0.009
b	0.64	0.90	0.025	0.035
b4	4.95	5.46	0.194	0.215
С	0.46	0.61	0.018	0.024
c2	0.46	0.60	0.018	0.023
D	5.97	6.22	0.235	0.244
D1	4.95	5.60	0.194	0.220
Е	6.35	6.73	0.250	0.265
E1	4.32	5.50	0.170	0.216
е	2.2	86 typ.	0.09	0 typ.
e1	4.40	4.70	0.173	0.185
Н	9.35	10.40	0.368	0.409
L	1.0	1.78	0.039	0.070
L2		1.27		0.050
L4	0.60	1.02	0.023	0.040
V2	-8°	+8°	-8°	+8°

Figure 20: DPAK recommended footprint (dimensions in mm)





Ordering information STTH5L06

# 3 Ordering information

**Table 10: Ordering information** 

Order code	Marking	Package	Weight	Base qty	Delivery mode
STTH5L06	STTH5L06	DO-201AD	1 10 ~	600	Ammopack
STTH5L06RL	STTH5L06	DO-201AD	1.12 g	1900	Tape and reel
STTH5L06D	STTH5L06D	TO-220AC	1.9 g	50	Tube
STTH5L06B-TR	STTH5 L06B	DPAK	0.32 g	2500	Tape and reel
STTH5L06FP	STTH5L06FP	TO-220FPAC	1.9 g	50	Tube

# 4 Revision history

**Table 11: Document revision history** 

Date	Revision	Changes
16-Nov-2001	1	First issue.
31-Mar-2007	2	Merged with TO-220AC, TO-220FPAC and DPAK version.
26-Nov-2014	3	Updated DPAK and reformatted to current standard.
05-Dec-2014	4	Updated Features.
17-May-2017	5	Updated DPAK package information and reformatted to current standard.

#### **IMPORTANT NOTICE - PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2017 STMicroelectronics - All rights reserved

