

SPECIFICATIONS

Current rating : 3A AC,DC

Voltage rating : 250V AC,DC

Contact resistance : 20m Ω Max.




Insulation resistance : 1000M Ω Min.


Withstanding voltage : 800V AC/minute

Temperature range : -25°C to +85 °C

Material : Nylon 66, UL94V-0

Poles	Dimension mm (in.)		Part No.
	A	B	
2	2.50 (0.098)	5.70(0.224)	250G2-H02
3	5.00 (0.197)	8.20(0.323)	250G2-H03
4	7.50 (0.295)	10.70(0.421)	250G2-H04
5	10.00 (0.394)	13.20 (0.520)	250G2-H05
6	12.50 (0.492)	15.70(0.618)	250G2-H06
7	15.00 (0.591)	18.20(0.717)	250G2-H07
8	17.50 (0.689)	20.70(0.815)	250G2-H08
9	20.00 (0.787)	23.20(0.913)	250G2-H09
10	22.50 (0.886)	25.70(1.012)	250G2-H10
11	25.00 (0.984)	28.20(1.110)	250G2-H11
12	27.50 (1.802)	30.70(1.209)	250G2-H12
13	30.00 (1.181)	33.20(1.307)	250G2-H13
14	32.50 (1.280)	35.70(1.406)	250G2-H14
15	35.00 (1.378)	38.20(1.504)	250G2-H15
16	37.50 (1.476)	40.70(1.602)	250G2-H16
20	47.50 (1.870)	50.70(1.996)	250G2-H20



Rev	Description/Date	Drawn By: Storm.li	Customer:	Third angle projection			X.± .X±0.30 .XX±0.20 .XXX±0.10
△		Checked By: Simmon	Part No.: 250G2-HXX	General Dimension Tolerance			
△		Approved By: Tony	Title: Housing				
SGS Report No.: CE/2005/63004C							