









LM2586

SNVS121E - MAY 1996 - REVISED MAY 2019



LM2586 4-V to 40-V, 3-A Step-Up Wide V_{IN} Flyback Regulator

Features

- Requires Few External Components
- Family of Standard Inductors and Transformers
- NPN Output Switches 3 A, Can Stand Off 65 V
- Wide Input Voltage Range: 4 V to 40 V
- Adjustable Switching Frequency: 100 kHz to 200
- External Shutdown Capability
- Draws Less Than 60 µA When Shut Down
- Frequency Synchronization
- Current-mode Operation for Improved Transient Response, Line Regulation, and Current Limit
- Internal Soft-start Function Reduces In-rush Current During Start-up
- Output Transistor Protected by Current Limit, Undervoltage Lockout, and Thermal Shutdown
- System Output Voltage Tolerance of ±4% Maximum Over Line and Load Conditions
- Create a Custom Design Using the LM2586 With the WEBENCH® Power Designer

Typical Applications

- Flyback Regulator
- Forward Converter
- Multiple-output Regulator
- Simple Boost Regulator

3 Description

The LM2586 series of regulators are monolithic integrated circuits specifically designed for flyback, step-up (boost), and forward converter applications. The device is available in 4 different output voltage versions: 3.3 V, 5 V, 12 V, and adjustable.

minimum number components, these regulators are cost effective, and simple to use. Included in the datasheet are typical circuits of boost and flyback regulators. Also listed are selector guides for diodes and capacitors and a family of standard inductors and flyback transformers designed to work with these switching regulators.

The power switch is a 3-A NPN device that can stand-off 65 V. Protecting the power switch are current and thermal limiting circuits, and undervoltage lockout circuit. This IC contains an adjustable frequency oscillator that programmed up to 200 kHz. The oscillator can also be synchronized with other devices, so that multiple devices can operate at the same switching frequency.

Other features include soft start mode to reduce inrush current during start up, and current mode control for improved rejection of input voltage and output load transients and cycle-by-cycle current limiting. The device also has a shutdown pin, so that it can be turned off externally. An output voltage tolerance of ±4%, within specified input voltages and output load conditions, is ensured for the power supply system.

Device Information⁽¹⁾

| PART NUMBER | PACKAGE | BODY SIZE (NOM) | | |
|-------------|-------------------|----------------------|--|--|
| 1.840500 | TO-220 (7) | 10.1 mm × 8.89 mm | | |
| LM2586 | DDPAK /TO-263 (7) | 14.986 mm × 10.16 mm | | |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

Block Diagram






Table of Contents

| Features 1 | | 7.3 Feature Description | 13 |
|---|---|---|---|
| | 8 | Application and Implementation | 20 |
| | | 8.1 Application Information | 20 |
| | | 8.2 Typical Applications | 20 |
| • | | 8.3 System Examples | 31 |
| | 9 | Layout | 33 |
| • | | 9.1 Layout Guidelines | 33 |
| G . | | 9.2 Layout Example | 33 |
| <u> </u> | | 9.3 Heat Sink/Thermal Considerations | 33 |
| | 10 | Device and Documentation Support | 35 |
| | | 10.1 Device Support | 35 |
| 6.6 Electrical Characteristics: 5 V | | 10.2 Receiving Notification of Documentation Updates | 35 |
| 6.7 Electrical Characteristics: 12 V | | 10.3 Community Resources | 35 |
| 6.8 Electrical Characteristics: Adjustable | | 10.4 Trademarks | 35 |
| 6.9 Typical Characteristics | | 10.5 Electrostatic Discharge Caution | 36 |
| ** | | 10.6 Glossary | 36 |
| 7.1 Overview 13 7.2 Functional Block Diagram 13 | 11 | Mechanical, Packaging, and Orderable Information | 36 |
| | 6.5 Electrical Characteristics: 3.3 V | Typical Applications 1 8 Description 1 1 Revision History 2 2 Pin Configurations 3 3 Specifications 4 6 6.1 Absolute Maximum Ratings 4 6.2 ESD Ratings 4 6.3 Recommended Operating Ratings 4 6.4 Thermal Information 5 6.5 Electrical Characteristics: 3.3 V 5 6.6 Electrical Characteristics: 12 V 7 6.8 Electrical Characteristics: Adjustable 8 6.9 Typical Characteristics 10 Detailed Description 13 7.1 Overview 13 | Typical Applications 1 8 Application and Implementation 8.1 Application Information 8.1 Application Information 8.2 Typical Applications 8.3 System Examples 8.3 System Examples 9 Layout 9.1 Layout Guidelines 9.2 Layout Example 9.3 Heat Sink/Thermal Considerations 9.3 Heat Sink/Thermal Considerations 9.3 Heat Sink/Thermal Considerations 9.3 Heat Sink/Thermal Considerations 9.4 Layout Example 9.3 Heat Sink/Thermal Considerations 9.5 Lectrical Characteristics: 3.3 V 5 10.1 Device and Documentation Support 10.2 Receiving Notification of Documentation Updates 10.4 Trademarks 10.5 Electrosatic Discharge Caution 10.6 Glossary 10.6 |

4 Revision History


NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| Changes from Revision D (April 2013) to Revision E | Page |
|--|------|
| Editorial changes only, no technical revisions | 1 |
| Changes from Revision C (April 2013) to Revision D | Page |
| Changed layout of National Semiconductor data sheet to TI format | |




5 Pin Configurations

NDZ Package 7-Pin TO-220 Top View, Bent, Staggered Leads



KTW Package 7-Pin DDPAK/TO-263 Top View



NDZ Package 7-Pin TO-220 Side View; Bent, Staggered Leads



KTW Package 7-Pin DDPAK/TO-263 Side View



Copyright © 1996–2019, Texas Instruments Incorporated



6 Specifications

6.1 Absolute Maximum Ratings (1)(2)

| <u> </u> | |
|---------------------------------------|--|
| Input Voltage | $-0.4V \le V_{IN} \le 45V$ |
| Switch Voltage | -0.4V ≤ V _{SW} ≤ 65V |
| Switch Current (3) | Internally Limited |
| Compensation Pin Voltage | $-0.4V \le V_{COMP} \le 2.4V$ |
| Feedback Pin Voltage | -0.4V ≤ V _{FB} ≤ 2 V _{OUT} |
| ON /OFF Pin Voltage | -0.4V ≤ V _{SH} ≤ 6V |
| Sync Pin Voltage | $-0.4V \le V_{SYNC} \le 2V$ |
| Power Dissipation (4) | Internally Limited |
| Storage Temperature Range | −65°C to +150°C |
| Lead Temperature (Soldering, 10 sec.) | 260°C |
| Maximum Junction Temperature (4) | 150°C |
| | |

- If Military/Aerospace specified devices are required, contact the Texas Instruments Sales Office/ Distributors for availability and specifications.
- (2) Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. These ratings apply when the current is limited to less than 1.2 mA for pins 1, 2, 3, and 6. Operating ratings indicate conditions for which the device is intended to be functional, but device parameter specifications may not be ensured under these conditions. For ensured specifications and test conditions, see the *Electrical Characteristics*.
- (3) Note that switch current and output current are not identical in a step-up regulator. Output current cannot be internally limited when the LM2586 is used as a step-up regulator. To prevent damage to the switch, the output current must be externally limited to 3A. However, output current is internally limited when the LM2586 is used as a flyback regulator (see the section for more information).
- (4) The junction temperature of the device (T_J) is a function of the ambient temperature (T_A), the junction-to-ambient thermal resistance (θ_{JA}), and the power dissipation of the device (P_D). A thermal shutdown will occur if the temperature exceeds the maximum junction temperature of the device: P_D × θ_{JA} + T_{A(MAX)} ≥ T_{J(MAX)}. For a safe thermal design, check that the maximum power dissipated by the device is less than: P_D ≤ [T_{J(MAX)} − T_{A(MAX)}]/θ_{JA}. When calculating the maximum allowable power dissipation, derate the maximum junction temperature—this ensures a margin of safety in the thermal design.

6.2 ESD Ratings

| | | | VALUE | UNIT |
|--------------------|-----------------------------------|---|-------|------|
| V _(ESD) | Electrostatic discharge (minimum) | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 $^{(1)}$ (C = 100 pF, R = 1.5 k Ω) | 2000 | V |

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Ratings

| Supply Voltage | $4V \le V_{ N} \le 40V$ |
|-----------------------|---------------------------------|
| Output Switch Voltage | 0V ≤ V _{SW} ≤ 60V |
| Output Switch Current | I _{SW} ≤ 3A |
| Junction Temp. Range | -40°C ≤ T _J ≤ +125°C |

Product Folder Links: LM2586



6.4 Thermal Information

| | | | LM2585 | | |
|-------------------------------|--|-------------------|-------------------|------|--|
| THERMAL METRIC ⁽¹⁾ | | KTW (DDPAK/TO-263 | NDZ (TO-220) | UNIT | |
| | | 7 PINS | 7 PINS | | |
| | | 56 ⁽²⁾ | 65 ⁽³⁾ | | |
| $R_{\theta JA}$ | Junction-to-ambient thermal resistance | 35 ⁽⁴⁾ | 45 ⁽⁵⁾ | °C/W | |
| | | 26 ⁽⁶⁾ | _ | | |
| $R_{\theta JC}$ | Junction-to-case thermal resistance | 2 | 2 | °C/W | |

- For more information about traditional and new thermal metrics, see the Semiconductor and IC package thermal metrics application report.
- (2) Junction-to-ambient thermal resistance for the 7-lead TO-263 mounted horizontally against a PC board area of 0.136 square inches (the same size as the DDPAK/TO-263 package) of 1 oz. (0.0014 in. thick) copper.
- (3) Junction-to-ambient thermal resistance (no external heat sink) for the 7-lead TO-220 package mounted vertically, with ½ inch leads in a socket, or on a PC board with minimum copper area.
- (4) Junction-to-ambient thermal resistance for the 7-lead TO-263 mounted horizontally against a PC board area of 0.4896 square inches (3.6 times the area of the DDPAK/TO-263 package) of 1 oz. (0.0014 in. thick) copper.
- (5) Junction-to-ambient thermal resistance (no external heat sink) for the 7-lead TO-220 package mounted vertically, with ½ inch leads soldered to a PC board containing approximately 4 square inches of (1 oz.) copper area surrounding the leads.
- (6) Junction-to-ambient thermal resistance for the 7-lead TO-263 mounted horizontally against a PC board copper area of 1.0064 square inches (7.4 times the area of the DDPAK/TO-2633 package) of 1 oz. (0.0014 in. thick) copper. Additional copper area reduces thermal resistance further.

6.5 Electrical Characteristics: 3.3 V

Specifications with standard type face are for $T_J = 25^{\circ}C$, and those in **bold type face** apply over full **Operating Temperature Range.** Unless otherwise specified, $V_{IN} = 5V$.

| | PARAMETER | TEST CONDITIONS | TYP | MIN | MAX | UNIT |
|-------------------------------------|--------------------------------------|---|-------|---------------------|---------------------|------|
| SYSTEM | PARAMETERS Test Circu | it of Figure 54 ⁽¹⁾ | | | | |
| V _{OUT} | Output Voltage | $V_{IN} = 4V$ to 12V $I_{LOAD} = 0.3$ to 1.2A | 3.3 | 3.17/ 3.14 | 3.43/ 3.46 | V |
| $\Delta V_{OUT} / \Delta V_{IN}$ | Line Regulation | V _{IN} = 4V to 12V I _{LOAD} = 0.3A | 20 | | 50/100 | mV |
| $\Delta V_{OUT}/$ ΔI_{LOAD} | Load Regulation | V _{IN} = 12V I _{LOAD} = 0.3A to 1.2A | 20 | | 50/100 | mV |
| η | Efficiency | $V_{IN} = 5V, I_{LOAD} = 0.3A$ | 76% | | | |
| UNIQUE | DEVICE PARAMETERS (2 | | | | | |
| V _{REF} | Output Reference Voltage | Measured at Feedback Pin V = 1.0V | 3.3 | 3.242/ 3.234 | 3.358/ 3.366 | V |
| ΔV_{REF} | Reference Voltage Line Regulation | V _{IN} = 4V to 40V | 2 | | | mV |
| G _M | Error Amp Transconductance | I_{COMP} = -30 μA to +30 μA V_{COMP} = 1V | 1.193 | 0.678 | 2.259 | mmho |
| A _{VOL} | Error Amp Voltage Gain | $V_{COMP} = 0.5V$ to 1.6V $R_{COMP} = 1$ $M\Omega$ $^{(3)}$ | 260 | 151/ 75 | | V/V |

- (1) External components such as the diode, inductor, input and output capacitors can affect switching regulator performance. When the LM2586 is used as shown in Figure 54 and Figure 55, system performance will be as specified by the system parameters.
- (2) All room temperature limits are 100% production tested, and all limits at temperature extremes are specified via correlation using standard Statistical Quality Control (SQC) methods.
- (3) A 1.0 M Ω resistor is connected to the compensation pin (which is the error amplifier output) to ensure accuracy in measuring A_{VOL}.

Product Folder Links: LM2586



6.6 Electrical Characteristics: 5 V

| | PARAMETER | TEST CONDITIONS | TYP | MIN | MAX | UNIT |
|-------------------------------------|--------------------------------------|--|-------|---------------------|---------------------|------|
| SYSTEM I | PARAMETERS Test Circu | uit of _{COMP} Figure 54 ⁽¹⁾ | | | | |
| V_{OUT} | Output Voltage | V _{IN} = 4V to 12V I _{LOAD} = 0.3A to 1.1A | 5.0 | 4.80/ 4.75 | 5.20/ 5.25 | V |
| $\Delta V_{OUT}/$ ΔV_{IN} | Line Regulation | V _{IN} = 4V to 12V I _{LOAD} = 0.3A | 20 | | 50/ 100 | mV |
| $\Delta V_{OUT}/$ ΔI_{LOAD} | Load Regulation | V _{IN} = 12V I _{LOAD} = 0.3A to 1.1A | 20 | | 50/ 100 | mV |
| η | Efficiency | V _{IN} = 12V, I _{LOAD} = 0.6A | 80% | | | |
| UNIQUE D | DEVICE PARAMETERS (2 | 2) | | | | |
| V_{REF} | Output Reference Voltage | Measured at Feedback Pin V _{COMP} = 1 V | 5.0 | 4.913/ 4.900 | 5.088/ 5.100 | V |
| ΔV_{REF} | Reference Voltage Line Regulation | V _{IN} = 4V to 40V | 3.3 | | | mV |
| G _M | Error Amp Transconductance | I_{COMP} = -30 μA to +30 μA V_{COMP} = 1 V | 0.750 | 0.447 | 1.491 | mmho |
| A _{VOL} | Error Amp Voltage Gain | $V_{COMP} = 0.5V \text{ to } 1.6V$ $R_{COMP} = 1 \text{ M}\Omega^{(3)}$ | 165 | 99/ 49 | | V/V |

External components such as the diode, inductor, input and output capacitors can affect switching regulator performance. When the

Submit Documentation Feedback

Copyright © 1996-2019, Texas Instruments Incorporated

LM2586 is used as shown in Figure 54 and Figure 55, system performance will be as specified by the system parameters.

All room temperature limits are 100% production tested, and all limits at temperature extremes are specified via correlation using standard Statistical Quality Control (SQC) methods.

⁽³⁾ A 1.0 M Ω resistor is connected to the compensation pin (which is the error amplifier output) to ensure accuracy in measuring A_{VOL}.



6.7 Electrical Characteristics: 12 V

| | PARAMETER | TEST CONDITIONS | TYP | MIN | MAX | UNIT |
|---|--------------------------------------|--|-------|---------------------|---------------------|------|
| SYSTEM | PARAMETERS Test Circu | uit of Figure 55 ⁽¹⁾ | | | , | • |
| V _{OUT} | Output Voltage | V _{IN} = 4V to 10V I _{LOAD} = 0.2A to 0.8A | 12 | 11.52/ 11.40 | 12.48/ 12.60 | V |
| $\Delta V_{OUT}/$ ΔV_{IN} | Line Regulation | $V_{IN} = 4V$ to 10V $I_{LOAD} = 0.2A$ | 20 | | 100/ 200 | mV |
| ΔV _{OUT} / ΔI _{LOAD} | Load Regulation | $V_{IN} = 10V$ $I_{LOAD} = 0.2A \text{ to } 0.8A$ | 20 | | 100/ 200 | mV |
| η | Efficiency | V _{IN} = 10V, I _{LOAD} = 0.6A | 93% | | | |
| UNIQUE | DEVICE PARAMETERS (| 2) | | | | |
| V_{REF} | Output Reference Voltage | Measured at Feedback Pin V _{COMP} = 1.0V | 12 | 11.79/ 11.76 | 12.21/ 12.24 | V |
| ΔV_{REF} | Reference Voltage Line Regulation | V _{IN} = 4V to 40V | 7.8 | | | mV |
| G _M | Error Amp Transconductance | I_{COMP} = -30 μ A to +30 μ A V_{COMP} = 1.0V | 0.328 | 0.186 | 0.621 | mmho |
| A _{VOL} | Error Amp Voltage Gain | $V_{COMP} = 0.5V \text{ to } 1.6V$ $R_{COMP} = 1.0 \text{ M}\Omega^{(3)}$ | 70 | 41/ 21 | | V/V |

External components such as the diode, inductor, input and output capacitors can affect switching regulator performance. When the

LM2586 is used as shown in Figure 54 and Figure 55, system performance will be as specified by the system parameters.

All room temperature limits are 100% production tested, and all limits at temperature extremes are specified via correlation using standard Statistical Quality Control (SQC) methods.

⁽³⁾ A 1.0 M Ω resistor is connected to the compensation pin (which is the error amplifier output) to ensure accuracy in measuring A_{VOL}.



6.8 Electrical Characteristics: Adjustable

| | PARAMETER | TEST CONDITIONS | TYP | MIN | MAX | UNIT |
|---|---|--|-------|---------------------|---------------------|------|
| SYSTEM | PARAMETERS Test Circuit of | Figure 55 ⁽¹⁾ | - | | | |
| V _{OUT} | Output Voltage | V _{IN} = 4V to 10V I _{LOAD} = 0.2A to 0.8A | 12.0 | 11.52/ 11.40 | 12.48/ 12.60 | V |
| ∆V _{OUT} / ∆V _{IN} | Line Regulation | $V_{IN} = 4V$ to 10V $I_{LOAD} = 0.2A$ | 20 | | 100/ 200 | mV |
| ∆V _{OUT} / ∆I _{LOAD} | Load Regulation | $V_{IN} = 10V$ $I_{LOAD} = 0.2A$ to 0.8A | 20 | | 100/ 200 | mV |
| 1 | Efficiency | $V_{IN} = 10V, I_{LOAD} = 0.6A$ | 93 | | | % |
| UNIQUE | DEVICE PARAMETERS (2) | | | , | | |
| V_{REF} | Output Reference Voltage | Measured at Feedback Pin V _{COMP} = 1.0V | 1.230 | 1.208/ 1.205 | 1.252/ 1.255 | V |
| ΔV_{REF} | Reference Voltage Line Regulation | $V_{IN} = 4V$ to $40V$ | 1.5 | | | mV |
| G _M | Error Amp Transconductance | I_{COMP} = -30 μA to +30 μA V_{COMP} = 1.0V | 3.200 | 1.800 | 6.000 | mmho |
| A _{VOL} | Error Amp Voltage Gain | $V_{COMP} = 0.5V$ to 1.6V, $R_{COMP} = 1.0 \ M\Omega$ ⁽³⁾ | 670 | 400/ 200 | | V/V |
| В | Error Amp Input Bias Current | $V_{COMP} = 1.0V$ | 125 | | 425/ 600 | nA |
| СОММО | N DEVICE PARAMETERS for a | III versions (2) | " | | • | |
| ls | Input Supply Current | Switch Off ⁽⁴⁾ | 11 | | 15.5/ 16.5 | mA |
| | | I _{SWITCH} = 1.8A | 50 | | 100/ 115 | mA |
| I _{S/D} | Shutdown Input Supply Current | $V_{SH} = 3V$ | 16 | | 100/ 300 | μΑ |
| V_{UV} | Input Supply Undervoltage Lockout | $R_{LOAD} = 100\Omega$ | 3.30 | 3.05 | 3.75 | V |
| fo | Oscillator Frequency | $\begin{array}{l} \text{Measured at Switch Pin} \\ \text{R}_{\text{LOAD}} = 100\Omega, \ \text{V}_{\text{COMP}} = 1.0\text{V} \\ \text{Freq. Adj. Pin Open (Pin 1)} \end{array}$ | 100 | 85/ 75 | 115/ 125 | kHz |
| | | $R_{SET} = 22 \text{ k}\Omega$ | 200 | | | kHz |
| fsc | Short-Circuit Frequency | Measured at Switch Pin $R_{LOAD} = 100\Omega$ $V_{FEEDBACK} = 1.15V$ | 25 | | | kHz |
| V _{EAO} | Error Amplifier | Upper Limit (5) | 2.8 | 2.6/ 2.4 | | V |
| | Output Swing | Lower Limit (4) | 0.25 | | 0.40/ 0.55 | V |
| EAO | Error Amp Output Current (Source or Sink) | See ⁽⁶⁾ | 165 | 110/ 70 | 260/ 320 | μА |
| ss | Soft Start Current | V _{FEEDBACK} = 0.92V V _{COMP} = 1.0V | 11.0 | 8.0/ 7.0 | 17.0/ 19.0 | μΑ |
| D _{MAX} | Maximum Duty Cycle | $R_{LOAD} = 100\Omega$ ⁽⁵⁾ | 98% | 93%/ 90% | | |
| lL | Switch Leakage Current | Switch Off V _{SWITCH} = 60V | 15 | | 300/ 600 | μΑ |
| V _{SUS} | Switch Sustaining Voltage | dV/dT = 1.5V/ns | | 65 | | V |
| V _{SAT} | Switch Saturation Voltage | I _{SWITCH} = 3.0A | 0.45 | | 0.65/ 0.9 | V |

⁽¹⁾ External components such as the diode, inductor, input and output capacitors can affect switching regulator performance. When the LM2586 is used as shown in Figure 54 and Figure 55, system performance will be as specified by the system parameters.

⁽²⁾ All room temperature limits are 100% production tested, and all limits at temperature extremes are specified via correlation using standard Statistical Quality Control (SQC) methods.

⁽³⁾ A 1.0 MΩ resistor is connected to the compensation pin (which is the error amplifier output) to ensure accuracy in measuring A_{VOL}.

⁽⁴⁾ To measure this parameter, the feedback voltage is set to a high value, depending on the output version of the device, to force the error amplifier output low and the switch off.

⁽⁵⁾ To measure this parameter, the feedback voltage is set to a low value, depending on the output version of the device, to force the error amplifier output high and the switch on.

⁽⁶⁾ To measure the worst-case error amplifier output current, the LM2586 is tested with the feedback voltage set to its low value (Note 4) and at its high value (Note 5).




Electrical Characteristics: Adjustable (continued)


| | PARAMETER | TEST CONDITIONS | TYP | MIN | MAX | UNIT |
|-------------------|---|--|------|--------------------|--------------------|------|
| I _{CL} | NPN Switch Current Limit | | 4.0 | 3.0 | 7.0 | Α |
| V _{STH} | Synchronization Threshold Voltage | $F_{SYNC} = 200 \text{ kHz}$ $V_{COMP} = 1V, V_{IN} = 5V$ | 0.75 | 0.625/ 0.40 | 0.875/ 1.00 | V |
| I _{SYNC} | Synchronization Pin Current | $V_{IN} = 5V$ $V_{COMP} = 1V$, $V_{SYNC} = V_{STH}$ | 100 | | 200 | μА |
| V _{SHTH} | ON/OFF Pin (Pin 1) Threshold Voltage | V _{COMP} = 1V | 1.6 | 1.0/ 0.8 | 2.2/ 2.4 | V |
| I _{SH} | ON/OFF Pin (Pin 1) Current | $V_{COMP} = 1V$ $V_{SH} = V_{SHTH}$ | 40 | 15/ 10 | 65/ 75 | μА |

⁽⁷⁾ When testing the minimum value, do not sink current from this pin—isolate it with a diode. If current is drawn from this pin, the frequency adjust circuit will begin operation (Figure 25).

STRUMENTS

6.9 Typical Characteristics











Figure 2. Reference Voltage vs Temperature 120






Figure 3. Δreference Voltage vs Supply Voltage






Figure 5. Current Limit vs Temperature





Figure 6. Feedback Pin Bias Current vs Temperature

Submit Documentation Feedback

Copyright © 1996-2019, Texas Instruments Incorporated



Typical Characteristics (continued)








Figure 8. Switch Transconductance vs Temperature




Figure 9. Oscillator Frequency vs Temperature




Figure 10. Error Amp Transconductance vs Temperature




Figure 11. Error Amp Voltage Gain vs Temperature






Figure 12. Short Circuit Frequency vs Temperature



Typical Characteristics (continued)










Figure 15. Oscillator Frequency vs Resistance




7 Detailed Description

Overview

The LM2586 series of regulators are monolithic integrated circuits specifically designed for flyback, step-up (boost), and forward converter applications. The device is available in 4 different output voltage versions: 3.3 V. 5 V, 12 V, and adjustable. Requiring a minimum number of external components, these regulators are cost effective, and simple to use. Included in the datasheet are typical circuits of boost and flyback regulators. Also listed are selector guides for diodes and capacitors and a family of standard inductors and flyback transformers designed to work with these switching regulators.

7.2 Functional Block Diagram



For Fixed Versions 3.3V, R1 = 3.4k, R2 = 2k5V, R1 = 6.15k, R2 = 2k12V, R1 = 8.73k, R2 = 1k For Adj. Version R1 = Short (0Ω) , R2 = Open

7.3 Feature Description

7.3.1 Flyback Regulator Operation


The LM2586 is ideally suited for use in the flyback regulator topology. The flyback regulator can produce a single output voltage, such as the one shown in Figure 16, or multiple output voltages. In Figure 16, the flyback regulator generates an output voltage that is inside the range of the input voltage. This feature is unique to flyback regulators and cannot be duplicated with buck or boost regulators.

The operation of a flyback regulator is as follows (refer to Figure 16): when the switch is on, current flows through the primary winding of the transformer, T1, storing energy in the magnetic field of the transformer. Note that the primary and secondary windings are out of phase, so no current flows through the secondary when current flows through the primary. When the switch turns off, the magnetic field collapses, reversing the voltage polarity of the primary and secondary windings. Now rectifier D1 is forward biased and current flows through it, releasing the energy stored in the transformer. This produces voltage at the output.

Copyright © 1996-2019, Texas Instruments Incorporated Submit Documentation Feedback



The output voltage is controlled by modulating the peak switch current. This is done by feeding back a portion of the output voltage to the error amp, which amplifies the difference between the feedback voltage and a 1.230V reference. The error amp output voltage is compared to a ramp voltage proportional to the switch current (in other words, inductor current during the switch on time). The comparator terminates the switch on time when the two voltages are equal, thereby controlling the peak switch current to maintain a constant output voltage.



As shown in Figure 16, the LM2586 can be used as a flyback regulator by using a minimum number of external components. The switching waveforms of this regulator are shown in . Typical performance characteristics observed during the operation of this circuit are shown in .

Figure 16. 12-V Flyback Regulator Design Example






Figure 17. 12-V Flyback Regulator Design Example





(1) As shown in Figure 17, the LM2585 can be used as a flyback regulator by using a minimum number of external components. The switching waveforms of this regulator are shown in Figure 18. Typical characteristics observed during the operation of this circuit are shown in Figure 19.





7.3.2 Step-Up (Boost) Regulator Operation

Figure 20 shows the LM2586 used as a step-up (boost) regulator. This is a switching regulator that produces an output voltage greater than the input supply voltage.

A brief explanation of how the LM2586 boost regulator works is as follows (refer to Figure 20). When the NPN switch turns on, the inductor current ramps up at the rate of V_{IN}/L , storing energy in the inductor. When the switch turns off, the lower end of the inductor flies above V_{IN} , discharging its current through diode (D) into the output capacitor (C_{OUT}) at a rate of ($V_{OUT} - V_{IN}/L$). Thus, energy stored in the inductor during the switch on time is transferred to the output during the switch off time. The output voltage is controlled by adjusting the peak switch current, as described in .





Figure 20. 12-V Boost Regulator

By adding a small number of external components (as shown in Figure 20), the LM2586 can be used to produce a regulated output voltage that is greater than the applied input voltage. The switching waveforms observed during the operation of this circuit are shown in Figure 21. Typical performance of this regulator is shown in Figure 22.



Submit Documentation Feedback

Copyright © 1996–2019, Texas Instruments Incorporated



7.3.3 Programming Output Voltage (Selecting R1 And R2)

Referring to the adjustable regulator in Figure 26, the output voltage is programmed by the resistors R1 and R2 by the following formula:

$$V_{OUT} = V_{REF} (1 + R1/R2)$$

where

Resistors R1 and R2 divide the output voltage down so that it can be compared with the 1.23V internal reference. With R2 between 1k and 5k, R1 is:

$$R1 = R2 (V_{OUT}/V_{REF} - 1)$$

where

•
$$V_{RFF} = 1.23V$$
 (2)

For best temperature coefficient and stability with time, use 1% metal film resistors.

7.3.4 Shutdown Control

A feature of the LM2586 is its ability to be shut down using the \overline{ON} /OFF pin (pin 1). This feature conserves input power by turning off the device when it is not in use. For proper operation, an isolation diode is required (as shown in Figure 23).

The device will shut down when 3V or greater is applied on the \overline{ON} /OFF pin, sourcing current into pin 1. In shut down mode, the device will draw typically 56 μ A of supply current (16 μ A to V_{IN} and 40 μ A to the \overline{ON} /OFF pin). To turn the device back on, leave pin 1 floating, using an (isolation) diode, as shown in Figure 23 (for normal operation, do not source or sink current to or from this pin—see the next section).




Figure 23. Shutdown Operation

7.3.5 Frequency Adjustment

The switching frequency of the LM2586 can be adjusted with the use of an external resistor. This feature allows the user to optimize the size of the magnetics and the output capacitor(s) by tailoring the operating frequency. A resistor connected from pin 1 (the Freq. Adj. pin) to ground will set the switching frequency from 100 kHz to 200 kHz (maximum). As shown in Figure 23, the pin can be used to adjust the frequency while still providing the shutdown function. A curve in *Typical Characteristics* the resistor value to the corresponding switching frequency. Table 1 shows resistor values corresponding to commonly used frequencies.

However, changing the LM2586 operating frequency from its nominal value of 100 kHz changes the magnetics selection and compensation component values.

Table 1. Frequency Setting Resistor Guide

| R _{SET} (kΩ) | Frequency (kHz) |
|-----------------------|-----------------|
| Open | 100 |
| 200 | 125 |
| 47 | 150 |
| 33 | 175 |



Table 1. Frequency Setting Resistor Guide (continued)

| R _{SET} (kΩ) | Frequency (kHz) |
|-----------------------|-----------------|
| 22 | 200 |

7.3.6 Frequency Synchronization

Another feature of the LM2586 is the ability to synchronize the switching frequency to an external source, using the sync pin (pin 6). This feature allows the user to parallel multiple devices to deliver more output power.

A negative falling pulse applied to the sync pin will synchronize the LM2586 to an external oscillator (see Figure 24 and Figure 25).

Use of this feature enables the LM2586 to be synchronized to an external oscillator, such as a system clock. This operation allows multiple power supplies to operate at the same frequency, thus eliminating frequency-related noise problems.




Figure 24. Frequency Synchronization




Figure 25. Waveforms of a Synchronized 12-V Boost Regulator

The scope photo in Figure 25 shows a LM2586 12-V boost regulator synchronized to a 200-kHz signal. There is a 700-ns delay between the falling edge of the sync signal and the turning on of the switch.

Product Folder Links: LM2586






Figure 26. Boost Regulator



8 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

8.1 Application Information

The LM2586 series of regulators are monolithic integrated circuits specifically designed for flyback, step-up (boost), and forward converter applications. Requiring a minimum number of external components, these regulators are cost effective, and simple to use. Included in the datasheet are typical circuits of boost and flyback regulators. Also listed are selector guides for diodes and capacitors and a family of standard inductors and flyback transformers designed to work with these switching regulators.

8.2 Typical Applications

8.2.1 Typical Flyback Regulator Applications

Figure 27 through Figure 32 show six typical flyback applications, varying from single output to triple output. Each drawing contains the part number(s) and manufacturer(s) for every component except the transformer. For the transformer part numbers and manufacturers' names, see Table 2. For applications with different output voltages—requiring the LM2586-ADJ—or different output configurations that do not match the standard configurations, refer to the **Switchers Made Simple** software.




Figure 27. Single-Output Flyback Regulator






Figure 28. Single-Output Flyback Regulator






Figure 29. Single-Output Flyback Regulator






Figure 30. Dual-Output Flyback Regulator




Figure 31. Dual-Output Flyback Regulator

Copyright © 1996–2019, Texas Instruments Incorporated




Figure 32. Triple-Output Flyback Regulator

8.2.1.1 Design Requirements

8.2.1.1.1 Transformer Selection (T)

Table 2 lists the standard transformers available for flyback regulator applications. Included in the table are the turns ratio(s) for each transformer, as well as the output voltages, input voltage ranges, and the maximum load currents for each circuit.

Table 2. Transformer Selection Table

| Applications | Figure 27 | Figure 28 | Figure 29 Figure 3 | | Figure 31 | Figure 32 |
|-------------------------|-----------|-----------|--------------------|-------|-----------|-----------|
| Transformers | T7 | T7 | T7 | T6 | T6 | T5 |
| V _{IN} | 4V-6V | 4V–6V | 8V-16V | 4V-6V | 18V-36V | 18V-36V |
| V _{OUT1} | 3.3V | 5V | 12V | 12V | 12V | 5V |
| I _{OUT1} (Max) | 1.4A | 1A | 0.8A | 0.15A | 0.6A | 1.8A |
| N ₁ | 1 | 1 | 1 | 1.2 | 1.2 | 0.5 |
| V _{OUT2} | | | | -12V | -12V | 12V |
| I _{OUT2} (Max) | | | | 0.15A | 0.6A | 0.25A |
| N ₂ | | | | 1.2 | 1.2 | 1.15 |
| V _{OUT3} | | | | | | -12V |
| I _{OUT3} (Max) | | | | | | 0.25A |
| N_3 | | _ | | | | 1.15 |



Table 3. Transformer Manufacturer Guide

| Transformer | Manufacturers' Part Numbers | | | | | | | | | | | |
|-------------|-----------------------------|---|----------|----------------------|-----------------------|----------|--|--|--|--|--|--|
| Туре | Coilcraft (1) | Coilcraft (1) Coilcraft (1) Pulse (2) Surface Mount Pulse (2) | | Renco ⁽³⁾ | Schott ⁽⁴⁾ | | | | | | | |
| T5 | Q4338-B | Q4437-B | PE-68413 | _ | RL-5532 | 67140890 | | | | | | |
| T6 | Q4339-B | Q4438-B | PE-68414 | _ | RL-5533 | 67140900 | | | | | | |
| T7 | S6000-A | S6057-A | _ | PE-68482 | RL-5751 | 26606 | | | | | | |

(1) Coilcraft Inc., Phone: (800) 322-2645

1102 Silver Lake Road, Cary, IL 60013 Fax: (708) 639-1469

European Headquarters, 21 Napier Place Phone: +44 1236 730 595 Wardpark North, Cumbernauld, Scotland G68 0LL Fax: +44 1236 730 627

(2) Pulse Engineering Inc., Phone: (619) 674-8100

12220 World Trade Drive, San Diego, CA 92128 Fax: (619) 674 -8262

European Headquarters, Dunmore Road Phone: +353 93 24 107 Tuam, Co. Galway, Ireland Fax: +353 93 24 459

(3) Renco Electronics Inc., Phone: (800) 645-5828


60 Jeffryn Blvd. East, Deer Park, NY 11729 Fax: (516) 586-5562

(4) Schott Corp., Phone: (612) 475-1173


1000 Parkers Lane Road, Wayzata, MN 55391 Fax: (612) 475-1786

8.2.1.1.2 Transformer Footprints

Figure 33 through Figure 47 show the footprints of each transformer, listed in Table 3.








Submit Documentation Feedback

Copyright © 1996–2019, Texas Instruments Incorporated





8.2.1.2 Detailed Design Procedure

8.2.1.2.1 Custom Design With WEBENCH® Tools

Click here to create a custom design using the LM2586 device with the WEBENCH® Power Designer.

- 1. Start by entering the input voltage (V_{IN}) , output voltage (V_{OUT}) , and output current (I_{OUT}) requirements.
- 2. Optimize the design for key parameters such as efficiency, footprint, and cost using the optimizer dial.
- 3. Compare the generated design with other possible solutions from Texas Instruments.

The WEBENCH Power Designer provides a customized schematic along with a list of materials with real-time pricing and component availability.

In most cases, these actions are available:

- Run electrical simulations to see important waveforms and circuit performance
- · Run thermal simulations to understand board thermal performance
- Export customized schematic and layout into popular CAD formats
- Print PDF reports for the design, and share the design with colleagues

Get more information about WEBENCH tools at www.ti.com/WEBENCH.

8.2.1.2.2 Flyback Regulator Input Capacitors

A flyback regulator draws discontinuous pulses of current from the input supply. Therefore, there are two input capacitors needed in a flyback regulator—one for energy storage and one for filtering (see Figure 48). Both are required due to the inherent operation of a flyback regulator. To keep a stable or constant voltage supply to the LM2586, a storage capacitor (≥100 μF) is required. If the input source is a rectified DC supply and/or the application has a wide temperature range, the required rms current rating of the capacitor might be very large. This means a larger value of capacitance or a higher voltage rating will be needed for the input capacitor. The storage capacitor will also attenuate noise which may interfere with other circuits connected to the same input supply voltage.






Figure 48. Flyback Regulator

In addition, a small bypass capacitor is required due to the noise generated by the input current pulses. To eliminate the noise, insert a 1- μ F ceramic capacitor between V_{IN} and ground as close as possible to the device.

8.2.1.2.3 Switch Voltage Limits

In a flyback regulator, the maximum steady-state voltage appearing at the switch, when it is off, is set by the transformer turns ratio, N, the output voltage, V_{OUT} , and the maximum input voltage, V_{IN} (maximum):

$$V_{SW(OFF)} = V_{IN} \text{ (maximum)} + (V_{OUT} + V_F)/N$$

where

 V_F is the forward biased voltage of the output diode, and is typically 0.5 V for Schottky diodes and 0.8 V for ultra-fast recovery diodes
 (3)

In certain circuits, there exists a voltage spike, V_{LL} , superimposed on top of the steady-state voltage (see , waveform A). Usually, this voltage spike is caused by the transformer leakage inductance and/or the output rectifier recovery time. To "clamp" the voltage at the switch from exceeding its maximum value, a transient suppressor in series with a diode is inserted across the transformer primary (as shown in the circuit in Figure 16 and other flyback regulator circuits throughout the datasheet). The schematic in Figure 48 shows another method of clamping the switch voltage. A single voltage transient suppressor (the SA51A) is inserted at the switch pin. This method clamps the total voltage across the switch, not just the voltage across the primary.

If poor circuit layout techniques are used (see the *Circuit Layout Guideline* section), negative voltage transients may appear on the Switch pin (pin 5). Applying a negative voltage (with respect to the IC's ground) to any monolithic IC pin causes erratic and unpredictable operation of that IC. This holds true for the LM2586 IC as well. When used in a flyback regulator, the voltage at the Switch pin (pin 5) can go negative when the switch turns on. The "ringing" voltage at the switch pin is caused by the output diode capacitance and the transformer leakage inductance forming a resonant circuit at the secondary(ies). The resonant circuit generates the "ringing" voltage, which gets reflected back through the transformer to the switch pin. There are two common methods to avoid this problem. One is to add an RC snubber around the output rectifier(s), as in Figure 48. The values of the resistor and the capacitor must be chosen so that the voltage at the Switch pin does not drop below -0.4 V. The resistor may range in value between 10Ω and 1 k Ω , and the capacitor will vary from 0.001 μF to 0.1 μF. Adding a snubber will (slightly) reduce the efficiency of the overall circuit.

The other method to reduce or eliminate the "ringing" is to insert a Schottky diode clamp between pins 5 and 4 (ground), also shown in Figure 48. This prevents the voltage at pin 5 from dropping below -0.4 V. The reverse voltage rating of the diode must be greater than the switch off voltage.






Figure 49. Input Line Filter

8.2.1.2.4 Output Voltage Limitations

The maximum output voltage of a boost regulator is the maximum switch voltage minus a diode drop. In a flyback regulator, the maximum output voltage is determined by the turns ratio, N, and the duty cycle, D, by the equation:

$$V_{OUT} \approx N \times V_{IN} \times D/(1 - D)$$
 (4)

The duty cycle of a flyback regulator is determined by Equation 5:

$$D = \frac{V_{OUT} + V_F}{N(V_{IN} - V_{SAT}) + V_{OUT} + V_F} \approx \frac{V_{OUT}}{N(V_{IN}) + V_{OUT}}$$
(5)

Theoretically, the maximum output voltage can be as large as desired—just keep increasing the turns ratio of the transformer. However, there exists some physical limitations that prevent the turns ratio, and thus the output voltage, from increasing to infinity. The physical limitations are capacitances and inductances in the LM2586 switch, the output diode(s), and the transformer—such as reverse recovery time of the output diode (mentioned above).

8.2.1.2.5 Noisy Input Line Condition

A small, low-pass RC filter should be used at the input pin of the LM2586 if the input voltage has an unusually large amount of transient noise, such as with an input switch that bounces. The circuit in Figure 49 demonstrates the layout of the filter, with the capacitor placed from the input pin to ground and the resistor placed between the input supply and the input pin. Note that the values of R_{IN} and C_{IN} shown in the schematic are good enough for most applications, but some readjusting might be required for a particular application. If efficiency is a major concern, replace the resistor with a small inductor (say 10 μ H and rated at 200 mA).

8.2.1.2.6 Stability

All current-mode controlled regulators can suffer from an instability, known as subharmonic oscillation, if they operate with a duty cycle above 50%. To eliminate subharmonic oscillations, a minimum value of inductance is required to ensure stability for all boost and flyback regulators. The minimum inductance is given by:

$$L(Min) = \frac{2.92 \left[(V_{IN}(Min) - V_{SAT}) \bullet (2D(Max) - 1) \right]}{1 - D(Max)} (\mu H)$$

where


V_{SAT} is the switch saturation voltage and can be found in the Characteristic Curves

(6)



8.2.2 Typical Boost Regulator Applications

Figure 50 through Figure 53 show four typical boost applications—one fixed and three using the adjustable version of the LM2586. Each drawing contains the part number(s) and manufacturer(s) for every component. For the fixed 12-V output application, the part numbers and manufacturers' names for the inductor are listed in Table 4. For applications with different output voltages, refer to the **Switchers Made Simple** software.



8.2.2.1 Design Requirements

Table 4 contains a list of standard inductors, by part number and corresponding manufacturer, for the fixed output regulator of Figure 50.

Table 4. Inductor Selection Table

| Coilcraft ⁽¹⁾ | Pulse ⁽²⁾ | Renco ⁽³⁾ | Schott ⁽⁴⁾ | Schott ⁽⁴⁾ (Surface Mount) |
|--------------------------|----------------------|----------------------|-----------------------|--|
| DO3316-153 | PE-53898 | RL-5471-7 | 67146510 | 67146540 |

(1) Coilcraft Inc., Phone: (800) 322-2645

1102 Silver Lake Road, Cary, IL 60013 Fax: (708) 639-1469

European Headquarters, 21 Napier Place Phone: +44 1236 730 595

Wardpark North, Cumbernauld, Scotland G68 0LL Fax: +44 1236 730 627
 Pulse Engineering Inc., Phone: (619) 674-8100
 12220 World Trade Drive, San Diego, CA 92128 Fax: (619) 674 -8262

European Headquarters, Dunmore Road Phone: +353 93 24 107 Tuam, Co. Galway, Ireland Fax: +353 93 24 459

Renco Electronics Inc., Phone: (800) 645-5828

60 Jeffryn Blvd. East, Deer Park, NY 11729 Fax: (516) 586-5562 (4) Schott Corp., Phone: (612) 475-1173

1000 Parkers Lane Road, Wayzata, MN 55391 Fax: (612) 475-1786




8.2.2.2 Detailed Design Procedure

See Detailed Design Procedure

8.3 System Examples

8.3.1 Test Circuits



 C_{IN1} —100 μF , 25V Aluminum Electrolytic

 C_{IN2} —0.1 μF Ceramic T—22 μH , 1:1 Schott #67141450

D-1N5820

 C_{OUT} —680 μF , 16V Aluminum Electrolytic

 $C_C\!\!-\!\!0.47~\mu\text{F}$ Ceramic


 R_C —2k

Figure 54. 3.3-V LM2586 and 5-V LM2586

Copyright © 1996-2019, Texas Instruments Incorporated



System Examples (continued)



 C_{IN1} —100 μF , 25V Aluminum Electrolytic

 C_{IN2} —0.1 μF Ceramic

L—15 μH, Renco #RL-5472-5

D-1N5820

 C_{OUT} —680 μF , 16V Aluminum Electrolytic

 C_{C} —0.47 μ F Ceramic R_{C} —2k For 12V Devices: R1 = Short (0 Ω) and 2 = Open

For ADJ Devices: R1 = 48.75k, $\pm 0.1\%$ and 2 = 5.62k, $\pm 0.1\%$

Figure 55. LM2586-12 and LM2586-ADJ



9 Layout

9.1 Layout Guidelines

As in any switching regulator, layout is very important. Rapidly switching currents associated with wiring inductance generate voltage transients which can cause problems. For minimal inductance and ground loops, keep the length of the leads and traces as short as possible. Use single point grounding or ground plane construction for best results. Separate the signal grounds from the power grounds (as indicated in Figure 56). When using the adjustable version, physically locate the programming resistors as close as possible to the regulator IC, to keep the sensitive feedback wiring short.

9.2 Layout Example




Figure 56. Circuit Board Layout

9.3 Heat Sink/Thermal Considerations

In many cases, a heat sink is not required to keep the LM2586 junction temperature within the allowed operating temperature range. For each application, to determine whether or not a heat sink will be required, the following must be identified:

- 1) Maximum ambient temperature (in the application).
- 2) Maximum regulator power dissipation (in the application).
- 3) Maximum allowed junction temperature (125°C for the LM2586). For a safe, conservative design, a temperature approximately 15°C cooler than the maximum junction temperature should be selected (110°C).
- 4) LM2586 package thermal resistances θ_{JA} and θ_{JC} (given in the Electrical Characteristics).

Total power dissipated (P_D) by the LM2586 can be estimated as follows:

Boost:

$$\begin{split} P_D &= 0.15\Omega \bullet \left(\frac{I_{LOAD}}{1-D}\right)^2 \bullet D + \frac{I_{LOAD}}{50 \bullet (1-D)} \bullet D \bullet V_{IN} \end{split}$$
 Flyback:
$$\begin{split} P_D &= 0.15\Omega \bullet \left(\frac{N \bullet \Sigma I_{LOAD}}{1-D}\right)^2 \bullet D \\ &+ \frac{N \bullet \Sigma I_{LOAD}}{50 \bullet (1-D)} \bullet D \bullet V_{IN} \end{split}$$

where

- V_{IN} is the minimum input voltage
- V_{OUT} is the output voltage
- N is the transformer turns ratio, D is the duty cycle
- I_{LOAD} is the maximum load current (and $\sum I_{LOAD}$ is the sum of the maximum load currents for multiple-output flyback regulators)

The duty cycle is given by:

Submit Documentation Feedback

(7)



Heat Sink/Thermal Considerations (continued)

Boost:

$$D = \frac{V_{OUT} + V_F - V_{IN}}{V_{OUT} + V_F - V_{SAT}} \approx \frac{V_{OUT} - V_{IN}}{V_{OUT}}$$

Flyback:

$$D = \frac{V_{OUT} + V_F}{N(V_{IN} - V_{SAT}) + V_{OUT} + V_F} \approx \frac{V_{OUT}}{N(V_{IN}) + V_{OUT}}$$

where

- V_F is the forward biased voltage of the diode and is typically 0.5 V for Schottky diodes and 0.8 V for fast recovery diodes
- V_{SAT} is the switch saturation voltage and can be found in the Characteristic Curves (8)

When no heat sink is used, the junction temperature rise is:

$$\Delta T_{J} = P_{D} \bullet \theta_{JA}. \tag{9}$$

Adding the junction temperature rise to the maximum ambient temperature gives the actual operating junction temperature:

$$T_{J} = \Delta T_{J} + T_{A}. \tag{10}$$

If the operating junction temperature exceeds the maximum junction temperature in item 3 above, then a heat sink is required. When using a heat sink, the junction temperature rise can be determined by the following:

$$\Delta T_{J} = P_{D} \bullet (\theta_{JC} + \theta_{Interface} + \theta_{Heat Sink}) \tag{11}$$

Again, the operating junction temperature will be:

$$T_{J} = \Delta T_{J} + T_{A} \tag{12}$$

As before, if the maximum junction temperature is exceeded, a larger heat sink is required (one that has a lower thermal resistance).

Included in the **Switchers Made Simple**® design software is a more precise (non-linear) thermal model that can be used to determine junction temperature with different input-output parameters or different component values. It can also calculate the heat sink thermal resistance required to maintain the regulator junction temperature below the maximum operating temperature.

To further simplify the flyback regulator design procedure, Texas Instruments is making available computer design software to be used with the Simple Switcher [®] line of switching regulators. **Switchers Made Simple** is available on a 3½" diskette for IBM compatible computers from a Texas Instruments sales office in your area or the Texas Instruments Customer Response Center ((800) 477-8924).



10 Device and Documentation Support

10.1 Device Support

10.1.1 Third-Party Products Disclaimer

TI'S PUBLICATION OF INFORMATION REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE AN ENDORSEMENT REGARDING THE SUITABILITY OF SUCH PRODUCTS OR SERVICES OR A WARRANTY, REPRESENTATION OR ENDORSEMENT OF SUCH PRODUCTS OR SERVICES, EITHER ALONE OR IN COMBINATION WITH ANY TI PRODUCT OR SERVICE.

10.1.2 Development Support

10.1.2.1 Custom Design With WEBENCH® Tools

Click here to create a custom design using the LM2586 device with the WEBENCH® Power Designer.

- 1. Start by entering the input voltage (V_{IN}), output voltage (V_{OUT}), and output current (I_{OUT}) requirements.
- 2. Optimize the design for key parameters such as efficiency, footprint, and cost using the optimizer dial.
- 3. Compare the generated design with other possible solutions from Texas Instruments.

The WEBENCH Power Designer provides a customized schematic along with a list of materials with real-time pricing and component availability.

In most cases, these actions are available:

- Run electrical simulations to see important waveforms and circuit performance
- Run thermal simulations to understand board thermal performance
- Export customized schematic and layout into popular CAD formats
- Print PDF reports for the design, and share the design with colleagues

Get more information about WEBENCH tools at www.ti.com/WEBENCH.

10.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

10.3 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E™ Online Community TI's Engineer-to-Engineer (E2E) Community. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

10.4 Trademarks

E2E is a trademark of Texas Instruments.

WEBENCH is a registered trademark of Texas Instruments.

Switchers Made Simple, Simple Switcher are registered trademarks of dcl owner.

All other trademarks are the property of their respective owners.



10.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

10.6 Glossary

SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.





30-May-2019

PACKAGING INFORMATION

| Orderable Device | Status | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead/Ball Finish | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|-------------------|--------|------------------|--------------------|------|----------------|--------------------------|------------------|---------------------|--------------|-------------------------|---------|
| LM2586S-12/NOPB | ACTIVE | DDPAK/ TO-263 | KTW | 7 | 45 | Pb-Free (RoHS Exempt) | CU SN | Level-3-245C-168 HR | -40 to 125 | LM2586S -12 P+ | Samples |
| LM2586S-3.3/NOPB | ACTIVE | DDPAK/ TO-263 | KTW | 7 | 45 | Pb-Free (RoHS Exempt) | CU SN | Level-3-245C-168 HR | -40 to 125 | LM2586S -3.3 P+ | Samples |
| LM2586S-5.0/NOPB | ACTIVE | DDPAK/ TO-263 | KTW | 7 | 45 | Pb-Free (RoHS Exempt) | CU SN | Level-3-245C-168 HR | -40 to 125 | LM2586S -5.0 P+ | Samples |
| LM2586S-ADJ/NOPB | ACTIVE | DDPAK/ TO-263 | KTW | 7 | 45 | Pb-Free (RoHS Exempt) | CU SN | Level-3-245C-168 HR | -40 to 125 | LM2586S -ADJ P+ | Samples |
| LM2586SX-3.3/NOPB | ACTIVE | DDPAK/ TO-263 | KTW | 7 | 500 | Pb-Free (RoHS Exempt) | CU SN | Level-3-245C-168 HR | -40 to 125 | LM2586S -3.3 P+ | Samples |
| LM2586SX-5.0/NOPB | ACTIVE | DDPAK/ TO-263 | KTW | 7 | 500 | Pb-Free (RoHS Exempt) | CU SN | Level-3-245C-168 HR | -40 to 125 | LM2586S -5.0 P+ | Samples |
| LM2586SX-ADJ/NOPB | ACTIVE | DDPAK/ TO-263 | KTW | 7 | 500 | Pb-Free (RoHS Exempt) | CU SN | Level-3-245C-168 HR | -40 to 125 | LM2586S -ADJ P+ | Samples |
| LM2586T-3.3/NOPB | ACTIVE | TO-220 | NDZ | 7 | 45 | Pb-Free (RoHS Exempt) | CU SN | Level-1-NA-UNLIM | -40 to 125 | LM2586T -3.3 P+ | Samples |
| LM2586T-5.0/NOPB | ACTIVE | TO-220 | NDZ | 7 | 45 | Pb-Free (RoHS Exempt) | CU SN | Level-1-NA-UNLIM | -40 to 125 | LM2586T -5.0 P+ | Samples |
| LM2586T-ADJ | NRND | TO-220 | NDZ | 7 | 45 | TBD | Call TI | Call TI | -40 to 125 | LM2586T -ADJ P+ | |
| LM2586T-ADJ/NOPB | ACTIVE | TO-220 | NDZ | 7 | 45 | Pb-Free (RoHS Exempt) | CU SN | Level-1-NA-UNLIM | -40 to 125 | LM2586T -ADJ P+ | Samples |

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".



PACKAGE OPTION ADDENDUM

30-May-2019

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 30-May-2019

TAPE AND REEL INFORMATION





| | Dimension designed to accommodate the component width |
|----|---|
| | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | | Package Drawing | | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------------|------------------|--------------------|---|-----|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| LM2586SX-3.3/NOPB | DDPAK/ TO-263 | KTW | 7 | 500 | 330.0 | 24.4 | 10.75 | 14.85 | 5.0 | 16.0 | 24.0 | Q2 |
| LM2586SX-5.0/NOPB | DDPAK/ TO-263 | KTW | 7 | 500 | 330.0 | 24.4 | 10.75 | 14.85 | 5.0 | 16.0 | 24.0 | Q2 |
| LM2586SX-ADJ/NOPB | DDPAK/ TO-263 | KTW | 7 | 500 | 330.0 | 24.4 | 10.75 | 14.85 | 5.0 | 16.0 | 24.0 | Q2 |

PACKAGE MATERIALS INFORMATION

www.ti.com 30-May-2019



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|-------------------|--------------|-----------------|------|-----|-------------|------------|-------------|
| LM2586SX-3.3/NOPB | DDPAK/TO-263 | KTW | 7 | 500 | 367.0 | 367.0 | 45.0 |
| LM2586SX-5.0/NOPB | DDPAK/TO-263 | KTW | 7 | 500 | 367.0 | 367.0 | 45.0 |
| LM2586SX-ADJ/NOPB | DDPAK/TO-263 | KTW | 7 | 500 | 367.0 | 367.0 | 45.0 |







IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2019, Texas Instruments Incorporated