







DO NOT SCALE DIMENSIONS IN MM.



WIRE RANGE: 0.75 TO 2.00 mm².
 FOR SEALED APPLICATIONS, SINGLE WIRES ONLY MUST BE USED.
 FOR UNSEALED APPLICATIONS, SINGLE WIRES ARE SUITABLE FOR THE RANGE 0.75 TO 2.00 mm² OR DOUBLE WIRES 2 X 0.50 mm² ONLY.

INSULATION RANGE: SINGLE WIRES 1.65 TO 2.70 MM DIA. OR DOUBLE WIRES 2 X 1.6 MM DIA. ONLY. THIN WALLED CABLE TO BE USED.

PRE-TINNED		BRASS		345806-1					
FINISH		MATERIAL		PART NUMBER					
CUSTOMER DWG FOR REFERENCE ONLY		© COPYRIGHT 1990 BY AMP OF GREAT BRITAIN LTD. ALL INTERNATIONAL RIGHTS RESERVED. ALL PRODUCTS MAY BE COVERED BY BRITISH AND FOREIGN PATENTS AND/OR PATENTS PENDING.		RELEASED FOR PUBLICATION 14 SEP 1990					
		TOLERANCES UNLESS OTHERWISE STATED : DEC ± 0.5 ANGLES ± 1°		DR. R. S. 14.9.90 CH. R. J. S. APP. J. P.					
A RELEASED		E800-0041-01 14.02.01		AMP of Great Britain Ltd. TERMINAL HOUSE STANMORE MIDD.					
3 BOX HT. TOL ALTERED		EB00-0344-95 10.10.95							
2 REL. TO CUSTOMER		C8171 24.04.92		.070 RECEPTACLE ECONOSEAL 3					
1 PRELIM. ISSUE		14.09.90							
REV	APPROVED	ECN	DATE	SCALE	LOC	SIZE	DWG. No.	REV	SHEET
				5 / 1	E	A 3	C345806	A	1 / 1