
Spec Sheet

Wire-wound Chip Power Inductors (CB series)

CBMF1608T100K



Features

- Item Summary
 10uH±10%, 0.115A, 0603/1608 (EIA/JIS)
- Lifecycle Stage
 - Mass Production
- Standard packaging quantity (minimum)
 Taping Embossed 3000pcs

Products characteristics table

Inductance	10 uH ± 10 %
Case Size (EIA/JIS)	0603/1608
Rated Current (max)	0.115 A
Saturation Current (max)	0.115 A
Temperature Rise Current (max)	0.38 A
DC Resistance (max)	0.468 Ω
DC Resistance (typ)	0.36 Ω
LQ Measuring Frequency	2.52 MHz
Self Resonant Frequency (min)	32 MHz
Operating Temp. Range	-40 to +105 ℃
	(Including-self-generated heat)
Temperature characteristic	± 25 %
(Inductance change)	
RoHS2 Compliance (10 subst.)	Yes
REACH Compliance (168 subst.)	Yes
Soldering	Reflow

■ External Dimensions

Dimension L	1.6 ±0.2 mm
Dimension W	0.8 ±0.2 mm
Dimension T	0.8 ±0.2 mm
Dimension e	0.45 ±0.15 mm

2017.01.02

Wire-wound Chip Power Inductors (CB series)

CBMF1608T100K



Dimension unit: mm unit: inch

Length: 1.6 + / - 0.2 (0.063 + / - 0.008)

Width: 0.8 + / - 0.2 (0.031 + / - 0.008)

Height: 0.8 + / - 0.2 (0.031 + / - 0.008)

Inductance: 10 uH (test freq at 2.52MHz)

DC Resistance: 0.36 / 0.468 ohm (typ / max)

Saturation Current: 115 mA (max) Temp. rise Current: 380 mA (max)

Saturation current typical: 30% reduction from initial L value.

Temp rise Current typical: Temperature will rise by 40 deg C

