www.vishay.com

Vishay Semiconductors

RoHS

COMPLIANT

**GREEN** (5-2008)

# **IR Receiver Modules for Remote Control Systems**



### **MECHANICAL DATA**

Pinning for TSOP381.., TSOP383.., TSOP385..: 1 = OUT, 2 = GND,  $3 = V_S$ Pinning for TSOP391.., TSOP393.., TSOP395..: 1 = OUT,  $2 = V_S$ , 3 = GND

#### **FEATURES**

- Very low supply current
- Photo detector and preamplifier in one package
- Internal filter for PCM frequency
- Improved shielding against EMI
- Supply voltage: 2.5 V to 5.5 V
- · Improved immunity against ambient light
- Insensitive to supply voltage ripple and noise
- Material categorization: For definitions of compliance please see www.vishav.com/doc?99912

### **DESCRIPTION**


These products are miniaturized receivers for infrared remote control systems. A PIN diode and a preamplifier are assembled on a lead frame, the epoxy package acts as an IR filter.

The demodulated output signal can be directly decoded by a microprocessor. The TSOP381..., TSOP391... are compatible with all common IR remote control data formats. The TSOP383..., TSOP393... are optimized to better suppress spurious pulses from energy saving fluorescent lamps. The TSOP385.., TSOP395.. have an excellent noise suppression. It is immune to dimmed LCD backlighting and any fluorescent lamps. AGC3 and AGC5 may also suppress some data signals in case of continuous transmission.


This component has not been qualified according to automotive specifications.

PARTS TABLE							
	SHORT BURST AND HIGH DATA RATE (AGC1)		NOISY ENVIROMENTS AND SHORT BURST (AGC3)		VERY NOISY ENVIROMENTS AND SHORT BURSTS (AGC5)		
CARRIER FREQUENCY		PINNING					
THEGOLINOT	1 = OUT, 2 = GND, 3 = V <sub>S</sub>	1 = OUT, 2 = V <sub>S</sub> , 3 = GND	1 = OUT, 2 = GND, 3 = V <sub>S</sub>	1 = OUT, 2 = V <sub>S</sub> , 3 = GND	1 = OUT, 2 = GND, 3 = V <sub>S</sub>	1 = OUT, 2 = V <sub>S</sub> , 3 = GND	
30 kHz	TSOP38130	TSOP39130	TSOP38330	TSOP39330	TSOP38530	TSOP39530	
33 kHz	TSOP38133	TSOP39133	TSOP38333	TSOP39333	TSOP38533	TSOP39533	
36 kHz	TSOP38136	TSOP39136	TSOP38336	TSOP39336	TSOP38536	TSOP39536	
38 kHz	TSOP38138	TSOP39138	TSOP38338	TSOP39338	TSOP38538	TSOP39538	
40 kHz	TSOP38140	TSOP39140	TSOP38340	TSOP39340	TSOP38540	TSOP39540	
56 kHz	TSOP38156	TSOP39156	TSOP38356	TSOP39356	TSOP38556	TSOP39556	

## **BLOCK DIAGRAM**



## **APPLICATION CIRCUIT**



 $R_{_1}$  and  $C_{_1}$  are recommended for protection against EOS. Components should be in the range of 33  $\Omega$  <  $R_{_1}$  < 1 k $\Omega,$   $C_{_1}$  > 0.1  $\mu F.$ 

Rev. 1.7, 16-Aug-12 **1** Document Number: 81744



www.vishay.com

## Vishay Semiconductors

ABSOLUTE MAXIMUM RATINGS						
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT		
Supply voltage		Vs	- 0.3 to + 6	V		
Supply current		I <sub>S</sub>	3	mA		
Output voltage		V <sub>O</sub>	- 0.3 to (V <sub>S</sub> + 0.3)	V		
Output current		Io	5	mA		
Junction temperature		T <sub>j</sub>	100	°C		
Storage temperature range		T <sub>stg</sub>	- 25 to + 85	°C		
Operating temperature range		T <sub>amb</sub>	- 25 to + 85	°C		
Power consumption	T <sub>amb</sub> ≤ 85 °C	P <sub>tot</sub>	10	mW		
Soldering temperature	t ≤ 10 s, 1 mm from case	T <sub>sd</sub>	260	°C		

#### Note

• Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect the device reliability.

<b>ELECTRICAL AND OPTICAL CHARACTERISTICS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Supply current	$E_{V} = 0, V_{S} = 3.3 V$	I <sub>SD</sub>	0.27	0.35	0.45	mA
Supply current	$E_v = 40$ klx, sunlight	I <sub>SH</sub>		0.45		mA
Supply voltage		Vs	2.5		5.5	V
Transmission distance	$E_{v}=0$ , test signal see fig. 1, IR diode TSAL6200, $I_{F}=250~\text{mA}$	d		45		m
Output voltage low	$I_{OSL} = 0.5 \text{ mA}, E_e = 0.7 \text{ mW/m}^2,$ test signal see fig. 1	V <sub>OSL</sub>			100	mV
Minimum irradiance	Pulse width tolerance: $t_{pi}$ - $5/f_o < t_{po} < t_{pi} + 6/f_o$ , test signal see fig. 1	E <sub>e min.</sub>		0.15	0.35	mW/m²
Maximum irradiance	$t_{pi}$ - 5/f <sub>o</sub> < $t_{po}$ < $t_{pi}$ + 6/f <sub>o</sub> , test signal see fig. 1	E <sub>e max.</sub>	30			W/m <sup>2</sup>
Directivity	Angle of half transmission distance	Ψ1/2		± 45		deg

## TYPICAL CHARACTERISTICS (T<sub>amb</sub> = 25 °C, unless otherwise specified)




Fig. 1 - Output Active Low





Fig. 2 - Pulse Length and Sensitivity in Dark Ambient


www.vishay.com Vishay Semiconductors

3.5

3

2.5









Fig. 3 - Output Function



Correlation with Ambient Light Sources: 10 W/m<sup>2</sup> = 1.4 kLx (Std. illum. A, T = 2855 K

10 W/m<sup>2</sup> = 8.2 kLx (Daylight, T = 5900 K)

Wavelength of Ambient Illumination:  $\lambda$  = 950 nm




Fig. 4 - Output Pulse Diagram




Fig. 7 - Sensitivity vs. Supply Voltage Disturbances




Fig. 5 - Frequency Dependence of Responsivity




Fig. 8 - Sensitivity vs. Electric Field Disturbances

www.vishay.com Vishay Semiconductors




Fig. 9 - Max. Envelope Duty Cycle vs. Burst Length




Fig. 10 - Sensitivity vs. Ambient Temperature




Fig. 11 - Relative Spectral Sensitivity vs. Wavelength




Fig. 12 - Horizontal Directivity




Fig. 13 - Vertical Directivity




Fig. 14 - Sensitivity vs. Supply Voltage

Vishay Semiconductors

## **SUITABLE DATA FORMAT**

These products are designed to suppress spurious output pulses due to noise or disturbance signals. Data and disturbance signals can be distinguished by the devices according to carrier frequency, burst length and envelope duty cycle. The data signal should be close to the band-pass center frequency (e.g. 38 kHz) and fulfill the conditions in the table below.

When a data signal is applied to the IR receiver in the presence of a disturbance signal, the sensitivity of the receiver is reduced to insure that no spurious pulses are present at the output. Some examples of disturbance signals which are suppressed are:

- DC light (e.g. from tungsten bulb or sunlight)
- · Continuous signals at any frequency
- Modulated noise from fluorescent lamps with electronic ballasts (see figure 15 or figure 16)




Fig. 15 - IR Signal from Fluorescent Lamp with Low Modulation




Fig. 16 - IR Signal from Fluorescent Lamp with High Modulation

	TSOP381, TSOP391	TSOP383, TSOP393	TSOP385, TSOP395
Minimum burst length	6 cycles/burst	6 cycles/burst	6 cycles/burst
After each burst of length a minimum gap time is required of	6 to 70 cycles ≥ 10 cycles	6 to 35 cycles ≥ 10 cycles	6 to 24 cycles ≥ 10 cycles
For bursts greater than a minimum gap time in the data stream is needed of	70 cycles > 1.2 x burst length	35 cycles > 6 x burst length	24 cycles > 25 ms
Maximum number of continuous short bursts/second	2000	2000	2000
Recommended for NEC code	yes	yes	yes
Recommended for RC5/RC6 code	yes	yes	yes
Recommended for Sony code	yes	no	no
Recommended for RCMM code	yes	yes	yes
Recommended for r-step code	yes	yes	yes
Recommended for XMP code	yes	yes	yes
Suppression of interference from fluorescent lamps	Common disturbance signals are supressed (example: signal pattern of fig. 15)	Even critical disturbance signals are suppressed (examples: signal pattern of fig. 15 and fig. 16)	Even critical disturbance signals are suppressed (examples: signal pattern of fig. 15 and fig. 16)


#### Note

• For data formats with long bursts (more than 10 carrier cycles) please see the datasheet for TSOP382.., TSOP384.., TSOP394...

www.vishay.com

## Vishay Semiconductors

## **PACKAGE DIMENSIONS** in millimeters





## **Legal Disclaimer Notice**

Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.