

### Features

- RoHS compliant\*
- Protects one or two lines
- Unidirectional and bidirectional configurations
- ESD protection 30 kV max.

### **Applications**

- RS-232, RS-422 and RS-423 data lines
- Portable electronics
- Wireless bus protection
- Control and monitoring systems

## CDS0T23-T03~T36C - TVS Diode Array Series

#### **General Information**


Portable communications, computing and video equipment manufacturers are challenging the semiconductor industry to develop increasingly smaller electronic components.


Bourns offers Transient Voltage Suppressor Array diodes for surge and ESD protection applications, in compact chip package SOT23 size format. The TransientVoltage Supressor Array series offers a choice of voltage types ranging from 3 V to 36 V. Bourns® Chip Diodes conform to JEDEC standards, are easy to handle on standard pick and place equipment and their flat configuration minimizes roll away.

The Bourns device will meet IEC 61000-4-2 (ESD), IEC 61000-4-4 (EFT) and IEC 61000-4-5 (Surge) requirements.

### Thermal Characteristics (@ T<sub>A</sub> = 25 °C Unless Otherwise Noted)

Parameter	Symbol	Value	Unit		
Operating Temperature	ТJ	-55 to +150	°C		
Storage Temperature	T <sub>STG</sub>	-55 to +150	°C		





### Electrical Characteristics (@ T<sub>A</sub> = 25 °C Unless Otherwise Noted)

			CDSOT23-													
Parameter	Symbol	Uni-	Bi-	Uni-	Bi-	Uni-	Bi-	Uni-	Bi-	Uni-	Bi-	Uni-	Bi-	Uni-	Bi-	Unit
		T03	T03C	T05	T05C	T08	T08C	T12	T12C	T15	T15C	T24	T24C	T36	T36C	
Minimum Breakdown Voltage @ 1 mA	V <sub>BR</sub>	4	4.0 6		.0	8.5		13.3		16.7		26.7		40.0		V
Maximum Working Peak Voltage	V <sub>WM</sub>	3	.3	5	.0	8.0		12.0		15.0		24.0		36.0		V
Maximum Clamping Voltage $V_{C} @ I_{P} = 1 A^{(1)}$	V <sub>F</sub>	7	.0	9.8		13	3.4	19.0		24.0		43.0		51.0		v
Maximum Clamping Voltage @ 8/20 $\mu s$ V_C $=$ I_PP $^{(1)}$	V <sub>F</sub>		.9 V 13 A		5 V 2 A	16.9 V @ 34 A		25.9 V @ 21 A		30.0 V @ 17 A		49.0 V @ 12 A		76.8 V @ 9 A		v
Maximum Leakage Current @ V <sub>WM</sub>	I <sub>D</sub>	1:	125		20		10		2 1		1		1		μA	
Typical Capacitance - Unidirectional @ 0 V, 1 MHz	C <sub>j(SD)</sub>	5	00	350		250		150		100		88		80		pF
Typical Capacitance - Bidirectional @ 0 V, 1 MHz	C <sub>j(SD)</sub>	3	00	2 <sup>.</sup>	10	15	150 90		0	60		63		60		pF
ESD Protection (per IEC 61000-4-2) Contact - Min. Contact - Max. Air - Min. Air - Max.	ESD	±8 ±30 ±15 ±30								kV						
Peak Pulse Power (t <sub>p</sub> @ 8/20 µs) <sup>(2)</sup>	P <sub>PP</sub>	500							w							
Forward Voltage @ 100 mA, 300 µs - Square Wave <sup>(3)</sup>	V <sub>F</sub>	1.5						v								

Notes: 1. See Pulse Wave Form.

2. See Peak Pulse Power vs. Pulse Time.

WARNING Cancer and Reproductive Harm

3. Only applies to unidirectional devices.

4. Part numbers with a "C" suffix are bidirectional devices, i.e., CDSOT23-T03C.

\*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.


The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at <a href="http://www.bourns.com/docs/legal/disclaimer.pdf">www.bourns.com/docs/legal/disclaimer.pdf</a>.

## CDS0T23-T03~T36C - TVS Diode Array Series


## Bourns

### **Product Dimensions**

This is a molded JEDEC SOT-323 package with 100 % Matte Sn plating on the lead frame. It weighs approximately 0.6 g and has a flammability rating of UL 94V-0.




### **Recommended Footprint**



 $DIMENSIONS = \frac{MILLIMETERS}{(INCHES)}$ 

Dimensions					
А	<u>0.95</u> (0.037)				
В	<u>0.95</u> (0.037)				
С	<u>2.00</u> (0.079)				
D	<u>0.85</u> (0.033)				
E	<u>0.85</u> (0.033)				

### **Typical Part Marking**



Specifications are subject to change without notice.


Users should verify actual device performance in their specific applications.

The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.


# CDS0T23-T03~T36C - TVS Diode Array Series

### BOURNS


### **Performance Graphs**




**Power Derating Curve** 








### **Pulse Waveform**



### **Block Diagram**

The device block diagrams below include the pin names and basic electrical connections associated with each channel.



#### **Environmental Specifications**

Moisture Sensitivity Level1	
ESD Classification (HBM)	

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications. The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at <u>www.bourns.com/docs/legal/disclaimer.pdf</u>.


# CDS0T23-T03~T36C - TVS Diode Array Series


### BOURNS

### **Packaging Information**

The surface mount product is packaged in an 12 mm x 8 mm tape and reel format per EIA-481 standard.

Direction of Feed





Devices are packed in accordance with EIA standard RS-481-A.



#### **Asia-Pacific:**

Tel: +886-2 2562-4117 Email: asiacus@bourns.com

#### Europe:

Tel: +36 88 885 877 Email: eurocus@bourns.com

The Americas: Tel: +1-951 781-5500 Email: americus@bourns.com www.bourns.com

REV. 09/19

Specifications are subject to change without notice. Users should verify actual device performance in their specific applications. The products described herein and this document are subject to specific legal disclaimers as set forth on the last page of this document, and at www.bourns.com/docs/legal/disclaimer.pdf.

Item	Symbol	SOT23
Carrier Width	A	$\frac{2.25 \pm 0.10}{(0.088 \pm 0.004)}$
Carrier Length	В	$\frac{2.34 \pm 0.10}{(0.092 \pm 0.004)}$
Carrier Depth	С	$\frac{1.22 \pm 0.10}{(0.048 \pm 0.004)}$
Sprocket Hole	d	$\frac{1.55 \pm 0.05}{(0.061 \pm 0.002)}$
Reel Outside Diameter	D	<u>178</u> (7.008)
Reel Inner Diameter	D <sub>1</sub>	<u>50.0</u> (1.969) MIN.
Feed Hole Diameter	D <sub>2</sub>	$\frac{13.0 \pm 0.20}{(0.512 \pm 0.008)}$
Sprocket Hole Position	E	$\frac{1.75 \pm 0.10}{(0.069 \pm 0.004)}$
Punch Hole Position	F	$\frac{3.50 \pm 0.05}{(0.138 \pm 0.002)}$
Punch Hole Pitch	Р	$\frac{4.00 \pm 0.10}{(0.157 \pm 0.004)}$
Sprocket Hole Pitch	P <sub>0</sub>	$\frac{4.00 \pm 0.10}{(0.157 \pm 0.004)}$
Embossment Center	P <sub>1</sub>	$\frac{2.00 \pm 0.05}{(0.079 \pm 0.002)}$
Overall Tape Thickness	Т	$\frac{0.20 \pm 0.10}{(0.008 \pm 0.004)}$
Tape Width	w	$\frac{8.00 \pm 0.20}{(0.315 \pm 0.008)}$
Reel Width	W <sub>1</sub>	14.4 (0.567) MAX.
Quantity per Reel		3,000

### **Legal Disclaimer Notice**

This legal disclaimer applies to purchasers and users of Bourns<sup>®</sup> products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns<sup>®</sup> products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns<sup>®</sup> products.

The characteristics and parameters of a Bourns<sup>®</sup> product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain types of applications are based on Bourns' knowledge of typical requirements in generic applications. The characteristics and parameters of a Bourns<sup>®</sup> product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns<sup>®</sup> product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns<sup>®</sup> product also can and do vary in different applications and actual performance may vary over time. Users should always verify the actual performance of the Bourns<sup>®</sup> product in their specific devices and applications, and make their own independent judgments regarding the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real world conditions.

Unless Bourns has explicitly designated an individual Bourns<sup>®</sup> product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns<sup>®</sup> product to meet the requirements of such industry standard or particular qualification. Users of Bourns<sup>®</sup> products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns<sup>®</sup> products are not recommended, authorized or intended for use in nuclear, lifesaving, life-critical or life-sustaining applications, nor in any other applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage. Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any Bourns<sup>®</sup> products in such unauthorized applications might not be safe and thus is at the user's sole risk. Life-critical applications include devices identified by the U.S. Food and Drug Administration as Class III devices and generally equivalent classifications outside of the United States.

Bourns expressly identifies those Bourns<sup>®</sup> standard products that are suitable for use in automotive applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns<sup>®</sup> standard products in an automotive application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk. If Bourns expressly identifies a sub-category of automotive application in the data sheet for its standard products (such as infotainment or lighting), such identification means that Bourns has reviewed its standard product and has determined that if such Bourns<sup>®</sup> standard product is considered for potential use in automotive applications, it should only be used in such sub-category of automotive applications. Any reference to Bourns<sup>®</sup> standard product in the data sheet as compliant with the AEC-Q standard or "automotive grade" does not by itself mean that Bourns has approved such product for use in an automotive application.

Bourns<sup>®</sup> standard products are not tested to comply with United States Federal Aviation Administration standards generally or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aircraft or space applications. Bourns expressly identifies Bourns<sup>®</sup> standard products that are suitable for use in aircraft or space applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns<sup>®</sup> standard product in an aircraft or space application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk.

The use and level of testing applicable to Bourns<sup>®</sup> custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns<sup>®</sup> custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns<sup>®</sup> standard products shall also apply to such Bourns<sup>®</sup> custom products.

Users shall not sell, transfer, export or re-export any Bourns<sup>®</sup> products or technology for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns<sup>®</sup> products or technology in any facility which engages in activities relating to such devices. The foregoing restrictions apply to all uses and applications that violate national or international prohibitions, including embargos or international regulations. Further, Bourns<sup>®</sup> products and Bourns technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns<sup>®</sup> products may not, without prior authorization from Bourns and/or the U.S. Government, be resold, transferred, or re-exported to any party not eligible to receive U.S. commodities, software, and technical data.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties, including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: http://www.bourns.com/legal/disclaimers-terms-and-policies PDF: http://www.bourns.com/docs/Legal/disclaimer.pdf