






-  CEE 7/XVI
-  BS 1363
-  NEMA 5-15P



Height (m)	Beam Diameter (m)	Light Intensity (lx)
0.25	0.37 0.39	7232
0.50	0.74 0.78	1808
0.75	1.11 1.18	804
1.00	1.48 1.57	452

- light source
- work equipment
- connected load
- power consumption
- luminous flux
- luminous efficiency
- light type/-color
- colour temperatur
- color rendering index
- light distribution
- direct ratio
- beam angle
- chromaticity tolerance LED
- luminance (L65)
- unified glare rating (4H 8H)
- system of protection
- class of protection
- operation
- housing
- cover
- arm
- mains lead
- fastening
- decorative contrast side parts

- LED
- electronic transformer
- 100-240 V, 50/60 Hz; secondary 24 V, DC
- env. 12 W
- approx. 700 lm
- approx. 70 lm/W
- cold white
- approx. 4.000 K
- CRI > 90; R9 > 50
- direct
- approx. 100 %
- 75°
- < 3 SDCM
- <= 12000 cd/m²
- <= 25
- IP 20
- II with plug-in power supply, III without plug-in power supply
- multi-function switch
- aluminium coloured anodised
- structured; plastic
- silver metallic
- ca. 3,00 m; mains plug; CEE 7/XVI; BS 1363; NEMA 5-15P
- table base
- black

