

Cable
assemblies

D-Sub / Hoods
Centronics

Multiflex -
DIN41651

Modular

USB
IEEE1394

Switches

Powercords
Powerlets

DIN41612
Hardmetric

MiniDIN

Sockets / Strips
Jumper

Terminal Blocks

Memory Card


FFC / FPC

Kurzschlußbrücken sind kleine Steckbrücken und dienen auf elektronischen Baugruppen zur Konfiguration oder zur Einstellung von Betriebsparametern, die selten oder nur einmalig bei Inbetriebnahme von Baugruppe vorgenommen werden.

Lötstützpunkte dienen als Abgriffspunkte auf Leiterplatten. Kurzschlussbrücken bietet ASSMANN WSW components für die Raster 2.00 mm und 2.54 mm, in offenen und geschlossenen Bauformen, als auch als Mehrfachtypen an. Verschiedenste Farben und Ausführungen sind ab Lager verfügbar.

Plugs for shorting and addressing (Jumper) are small plugs and used on connector or other electronic modules for configuration or for adjustment of process parameters, which normally will be done seldom or once during set-up phase of a machine or an electronic module.

Solder terminals are used as possibility to tap power from a pcb at prefixed positions. Jumpers from ASSMANN WSW components are available for 2.00 mm and 2.54 mm pitches, as open and closed design and as well in multiple types. Various colours and types are available from stock.



Produktbeschreibung

Seite

Kurzschlußbrücken, Raster 2.00mm	290
Kurzschlußbrücken, Raster 2.54mm	291
Mehrfach-Kurzschlußbrücken, Raster 2.00mm / 2.54mm	293
Steckbuchsen	294
Lötstützpunkte	296

Product description

page

Jumper, pitch 2.00mm	290
Jumper, pitch 2.54mm	291
Multi-jumper, pitch 2.00mm / 2.54mm	293
Connector-sleeves	294
Solder terminals	296



Cable assemblies

D-Sub / Hoods Centronics

Multiflex - DIN41651

Modular

USB IEEE1394

Switches

Powercards Powerinlets

DIN41612 Hardmetric

MiniDIN


Sockets / Strips Jumper

Terminal Blocks

Memory Card

FFC / FPC

- Cable assemblies
- D-Sub / Hoods Centronics
- Multiflex - DIN41651
- Modular
- USB IEEE1394
- Switches
- Powercords Powerlets
- DIN41612 Hardmetric
- MiniDIN
- Sockets / Strips Jumper
- Terminal Blocks
- Memory Card
- FFC / FPC



Isolierkörpermaterial
PBT, UL94V-0

Kontaktmaterial
Messing

Kontaktfläche
Ni, Au

Kontaktwiderstand
30mΩ max

Isolationswiderstand
1000MΩ min

Strombelastbarkeit
3A

Betriebstemperatur
-40°C - +105°C

Verpackung
Kunststoffbeutelverpackung

Insulator material
PBT, UL94V-0

Contact material
Brass

Plating
Ni, Au

Contact resistance
30mΩ max

Insulation resistance
1000MΩ min

Current rating
3A

Operating temperature
-40°C to +105°C

Packing
Polybag packing


Bestellcode / Ordercode

Oberfläche
G - Gold Flash
Z - Verzinkt

Contact plating
G - Gold flash
Z - Tinned

AKSO - 200 / x

Bitte „x“ durch die geeignete Option ersetzen
 Please replace „x“ with appropriate option



Isolierkörpermaterial
PBT, UL94V-0

Kontaktmaterial
Messing

Kontaktfläche
Ni, Au

Kontaktwiderstand
30mΩ max

Isolationswiderstand
1000MΩ min

Strombelastbarkeit
3A

Betriebstemperatur
-40°C - +105°C

Verpackung
Kunststoffbeutelverpackung

Insulator material
PBT, UL94V-0

Contact material
Brass

Plating
Ni, Au

Contact resistance
30mΩ max

Insulation resistance
1000MΩ min

Current rating
3A

Operating temperature
-40°C to +105°C

Packing
Polybag packing

Bestellcode / Ordercode

Oberfläche
G - Gold Flash
Z - Verzinkt



Contact plating
G - Gold flash
Z - Tinned

AKSG - 200 / x

Bitte „x“ durch die geeignete Option ersetzen
 Please replace „x“ with appropriate option

Isolierkörpermaterial
 PBT, UL94V-0
Kontaktmaterial
 Messing
Kontaktoberfläche
 Ni, Au
Kontaktwiderstand
 30mΩ max
Isolationswiderstand
 1000MΩ min
Strombelastbarkeit
 3A
Betriebstemperatur
 -40°C - +105°C
Verpackung
 Kunststoffbeutelverpackung

Insulator material
 PBT, UL94V-0
Contact material
 Brass
Plating
 Ni, Au
Contact resistance
 30mΩ max
Insulation resistance
 1000MΩ min
Current rating
 3A
Operating temperature
 -40°C to +105°C
Packing
 Polybag packing



Bestellcode / [Ordercode](#)

Kontaktoberfläche
 G - Gold Flash
 Z - Verzinkt
Farbe
 GREY - Grau
 RED - Rot
 BLUE - Blau
 BLACK - Schwarz



Plating
 G - Gold flash
 Z - Tinned
Colour
 GREY - Grey
 RED - Red
 BLUE - Blue
 BLACK - Black

AKSPT / x - x

Bitte „x“ durch die geeignete Option ersetzen
 Please replace „x“ with appropriate option

Isolierkörpermaterial
 PBT, UL94V-0
Kontaktmaterial
 Messing
Kontaktoberfläche
 Ni, Au
Kontaktwiderstand
 30mΩ max
Isolationswiderstand
 1000MΩ min
Strombelastbarkeit
 3A
Betriebstemperatur
 -40°C - +105°C
Verpackung
 Kunststoffbeutelverpackung

Insulator material
 PBT, UL94V-0
Contact material
 Brass
Plating
 Ni, Au
Contact resistance
 30mΩ max
Insulation resistance
 1000MΩ min
Current rating
 3A
Operating temperature
 -40°C to +105°C
Packing
 Polybag packing



Bestellcode / [Ordercode](#)

Oberfläche
 G - Gold Flash
 Z - Verzinkt


Contact plating
 G - Gold flash
 Z - Tinned

AKSNT / x - BLACK

Bitte „x“ durch die geeignete Option ersetzen
 Please replace „x“ with appropriate option

- Cable assemblies
- D-Sub / Hoods Centronics
- Multiflex - DIN41651
- Modular
- USB IEEE1394
- Switches
- Powercords Powerinlets
- DIN41612 Hardmetric
- MiniDIN
- Sockets / Strips Jumper
- Terminal Blocks
- Memory Card
- FFC / FPC

Cable assemblies
 D-Sub / Hoods Centronics
 Multiflex - DIN41651
 Modular
 USB IEEE1394
 Switches
 Powercords Powerleads
 DIN41612 Hardmetric
 MiniDIN
 Sockets / Strips Jumper
 Terminal Blocks
 Memory Card
 FFC / FPC



Isolierkörpermaterial
PBT, UL94V-0
Kontaktmaterial
Messing
Kontaktfläche
Ni, Au
Kontaktwiderstand
30mΩ max
Isolationswiderstand
1000MΩ min
Strombelastbarkeit
3A
Betriebstemperatur
-40°C - +105°C
Verpackung
Kunststoffbeutelverpackung

Insulator material
PBT, UL94V-0
Contact material
Brass
Plating
Ni, Au
Contact resistance
30mΩ max
Insulation resistance
1000MΩ min
Current rating
3A
Operating temperature
-40°C to +105°C
Packing
Polybag packing



Bestellcode / Ordercode

Oberfläche
 G - Gold Flash
 Z - Verzinkt

Contact plating
 G - Gold flash
 Z - Tinned

AKSCT / x - BLACK

Bitte „x“ durch die geeignete Option ersetzen
 Please replace „x“ with appropriate option



Isolierkörpermaterial
PBT, UL94V-0
Kontaktmaterial
Messing
Kontaktfläche
Ni, Au
Kontaktwiderstand
30mΩ max
Isolationswiderstand
1000MΩ Min
Strombelastbarkeit
3A
Betriebstemperatur
-40°C - +105°C
Verpackung
Kunststoffbeutelverpackung

Insulator material
PBT, UL94V-0
Contact material
Brass
Plating
Ni, Au
Contact resistance
30mΩ max
Insulation resistance
1000MΩ min
Current rating
3A
Operating temperature
-40°C to +105°C
Packing
Polybag packing

Bestellcode / Ordercode

Oberfläche
 G - Gold Flash
 Z - Verzinkt

Contact plating
 G - Gold flash
 Z - Tinned

AKSPLT / x - BLACK

Bitte „x“ durch die geeignete Option ersetzen
 Please replace „x“ with appropriate option

Mehrfach-Kurzschlußbrücken, Raster 2.00mm / 2.54mm
Multi-jumper, pitch 2.00mm / 2.54mm

Isolierkörpermaterial

PBT, UL94V-0

Kontaktmaterial

Messing

Kontaktoberfläche

Ni, Au

Kontaktwiderstand

30mΩ max

Isolationswiderstand

1000MΩ min

Strombelastbarkeit

3A

Betriebstemperatur

-40°C - +105°C

Verpackung

Kunststoffbeutelverpackung

Raster 2.00mm

Insulator material

PBT, UL94V-0

Contact material

Brass

Plating

Ni, Au

Contact resistance

30mΩ max

Insulation resistance

1000MΩ min

Current rating

3A



Operating temperature

-40°C to +105°C

Packing

Polybag packing

Pitch 2.00mm



Bestellcode / [Ordercode](#)

Polzahl

02 / 03 / 04 / 05 / 06 / 07 / 08 / 09 / 10

No of contacts

02 / 03 / 04 / 05 / 06 / 07 / 08 / 09 / 10

AKSO - 200 / G - x

Bitte „x“ durch die geeignete Option ersetzen
 Please replace „x“ with appropriate option

Isolierkörpermaterial

PBT, UL94V-0

Kontaktmaterial

Messing

Kontaktoberfläche

Ni, Au

Kontaktwiderstand

30mΩ max

Isolationswiderstand

1000MΩ Min

Strombelastbarkeit

3A

Betriebstemperatur

-40°C - +105°C

Verpackung

Kunststoffbeutelverpackung

Raster 2.54mm

Insulator material

PBT, UL94V-0

Contact material

Brass

Plating

Ni, Au

Contact resistance

30mΩ max

Insulation resistance

1000MΩ min

Current rating

3A



Operating temperature

-40°C to +105°C

Packing

Polybag packing

Pitch 2.54mm



Bestellcode / [Ordercode](#)

Polzahl

02 / 03 / 04 / 05 / 06 / 07 / 08 / 09 / 10

No of contacts

02 / 03 / 04 / 05 / 06 / 07 / 08 / 09 / 10

AKSPT / G - x

Bitte „x“ durch die geeignete Option ersetzen
 Please replace „x“ with appropriate option

Cable assemblies

D-Sub / Hoods Centronics

Multiflex - DIN41651

Modular

USB IEEE1394

Switches

Powercards Powerinlets

DIN41612 Hardmetric

MiniDIN





















Sockets / Strips Jumper











Terminal Blocks

Memory Card

FFC / FPC










- Cable assemblies
- D-Sub / Hoods Centronics
- Multiflex - DIN41651
- Modular
- USB IEEE1394
- Switches
- Powercords Powerlets
- DIN41612 Hardmetric
- MiniDIN
- Sockets / Strips Jumper
- Terminal Blocks
- Memory Card
- FFC / FPC





















 	 	 	 
AP89	AP90	AP91	AP91A SCHWARZ
 	 	 	 
AP91B SCHWARZ	AP99B SCHWARZ	AP102B/G-T	AP103
AP91B BLAU	AP99B BLAU	AP102B/G-T	AP103
 	 	<p>Kontaktmaterial Messing</p> <p>Kontaktfläche Ni, Au (AP-102-B-Z-T = Ni, Sn) (AP-103-D-Z-T = Ni, Sn)</p>	
AP103D/G-T	AP103D/Z-T	<p>Contact material Brass</p> <p>Plating Ni, Au (AP-102-B-Z-T = Ni, Sn) (AP-103-D-Z-T = Ni, Sn)</p>	

 <p>Technical drawing of terminal AB7 showing dimensions: $\phi 0.8$, $\phi 0.5$, 3.5, 5.5, 2.54.</p>	 <p>Technical drawing of terminal AB8 showing dimensions: $\phi 0.8$, $\phi 0.5$, 5.08, 3.5, 5.5.</p>	 <p>Technical drawing of terminal AB9 showing dimensions: $\phi 0.8$, $\phi 0.5$, 7.62, 3.5, 5.5.</p>	 <p>Technical drawing of terminal AB10 showing dimensions: $\phi 2$, $\phi 1$, 2.1, 8, 5.08.</p>
<p>AB7</p>	<p>AB8</p>	<p>AB9</p>	<p>AB10</p>
 <p>Technical drawing of terminal AB10B showing dimensions: $\phi 2$, $\phi 1$, 4, 8, 7.62.</p>	 <p>Technical drawing of terminal AB11 showing dimensions: $\phi 2$, $\phi 1$, 7, 8, 10.16.</p>	 <p>Technical drawing of terminal AB14 showing dimensions: $\phi 2$, $\phi 1.5$, $\phi 1.3$, $\phi 1$, 2.5, 5, 8, 5.08.</p>	 <p>Technical drawing of terminal AB1U-G showing dimensions: 5.5, $\phi 0.56$, 2.54.</p>
<p>AB10B</p>	<p>AB11</p>	<p>AB14</p>	<p>AB1U-G</p>
 <p>Technical drawing of terminal AB1U-Z showing dimensions: 5.5, $\phi 0.56$, 2.54.</p>	 <p>Technical drawing of terminal AB3U-G showing dimensions: 5.0, 6.0, 4.7, $\phi 0.56$, 3.6, 7.62.</p>	<p>Kontaktmaterial Messing</p> <p>Kontaktoberfläche Ni, Au (AB-1-U-Z = Ni, Sn)</p> <p>Contact material Brass</p> <p>Plating Ni, Au (AB-1-U-Z = Ni, Sn)</p>	
<p>AB1U-Z</p>	<p>AB3U-G</p>		

- Cable assemblies
- D-Sub / Hoods
Centronics
- Multiflex -
DIN41651
- Modular
- USB
IEEE1394
- Switches
- Powercords
Powerinlets
- DIN41612
Hardmetric
- MiniDIN
- Sockets / Strips
Jumper
- Terminal Blocks
- Memory Card
- FPC / FPC

- Cable assemblies
- D-Sub / Hoods Centronics
- Multiflex - DIN41651
- Modular
- USB IEEE1394
- Switches
- Powercords Powerlets
- DIN41612 Hardmetric
- MiniDIN
- Sockets / Strips Jumper
- Terminal Blocks
- Memory Card
- FFC / FPC

			
AL-ST-G-T	AL32	AL33	AL33G
			
AL41B	AL45	AP101C	AW105
	<p>Kontaktmaterial Messing</p> <p>Kontaktoberfläche Ni, Au</p>		<p>Contact material Brass</p> <p>Plating Ni, Au</p>
AW106			

 	 	 	 
<p>AL21</p>	<p>AL23</p>	<p>AL24</p>	<p>AL28</p>
 	 	 	 
<p>AL33A</p>	<p>AL46</p>	<p>AL50</p>	<p>ALP52</p>
 	 	<p>Kontaktmaterial Messing</p> <p>Kontaktoberfläche Ni, Au</p> <p>Contact material Brass</p> <p>Plating Ni, Au</p>	
<p>ALP53</p>	<p>ALP53A</p>		

- Cable assemblies
- D-Sub / Hoods Centronics
- Multiflex - DIN41651
- Modular
- USB IEEE1394
- Switches
- Powercords Powernets
- DIN41612 Hardmetric
- MiniDIN
- Sockets / Strips Jumper
- Terminal Blocks
- Memory Card
- FPC / FPC

Cable
assemblies

D-Sub / Hoods
Centronics

Multiflex -
DIN41651

Modular

USB
IEEE1394

Switches

Powercords
Powerlets

DIN41612
Hardmetric


MiniDIN

Sockets / Strips
Jumper


Terminal Blocks

Memory Card


FFC / FPC




ALP54




ALP55




ALP56




ALP57




ALP58




ALP60



ALP62




ALP63



ALP65

Kontaktmaterial
Messing
Kontaktfläche
Ni, Au

Contact material
Brass
Plating
Ni, Au



Cable assemblies

D-Sub / Hoods
Centronics

Multiflex -
DIN41651

Modular

USB
IEEE1394

Switches

Powercords
Powerinlets

DIN41612
Hardmetric

MiniDIN

Sockets / Strips
Jumper

Terminal Blocks

Memory Card

FFC / FPC