

PRODUCT-DETAILS

## CT-MFD.12

### CT-MFD.12 Time relay, multifunction 1c/o, 24-240VAC 24-48VDC



#### General Information

Extended Product Type	CT-MFD.12
Product ID	1SVR500020R0000
EAN	4013614350634
Catalog Description	CT-MFD.12 Time relay, multifunction 1c/o, 24-240VAC 24-48VDC
Long Description	The CT-MFD.12 is a multifunction electronic time relay from the CT-D timer range. It provides 7 timing functions with 7 time ranges from 0.05 s to 100 h. This time relay operates with a rated control supply voltage of 24 - 48 V DC / 24 - 240 V AC and has a 1 c/o (SPDT) output rated at 250 V / 6 A. A control input works with voltage-related (non-floating) triggering.

#### Ordering

EAN	4013614350634
Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

#### Popular Downloads

Data Sheet, Technical Information	2CDC110004C0210_01
Instructions and Manuals	1SVC500010M0000

## Dimensions

Product Net Width	17.5 mm
Product Net Height	70 mm
Product Net Depth / Length	63 mm
Product Net Weight	0.053 kg

## Technical

Timer Relay Type	ON-Delay OFF-Delay Impulse ON Impulse OFF Flasher Starting with ON Flasher Starting with OFF Pulse Former
Time Range	0.05 s ... 100 h
Rated Control Supply Voltage (U <sub>s</sub> )	24 ... 240 V AC 24 ... 48 V DC
Output	1 c/o (SPDT) contact
Terminal Type	Screw Terminals
Rated Operational Current AC-12 (I <sub>e</sub> )	(230 V) 6 A
Rated Operational Current AC-15 (I <sub>e</sub> )	(230 V) 3 A
Rated Operational Current DC-12 (I <sub>e</sub> )	(24 V) 6 A
Rated Operational Current DC-13 (I <sub>e</sub> )	(24 V) 2 A
Degree of Protection	Housing IP50 Terminals IP20
Overvoltage Category	III
Pollution Degree	3
Short-Circuit Protective Devices	Output Circuit NC - F Type Fuses 6 A Output Circuit NO - F Type Fuses 10 A
Connecting Capacity	Flexible 1x 0.5 ... 2.5 mm <sup>2</sup> Flexible 2x 0.5 ... 1.5 mm <sup>2</sup> Rigid 1x 0.5 ... 4 mm <sup>2</sup> Rigid 2x 0.5 ... 1.5 mm <sup>2</sup>
Tightening Torque	0.5 ... 0.8 N·m
Wire Stripping Length	7 mm
Recommended Screw Driver	Pozidriv 1 0.8 x 4
Mounting Position	Any
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Standards	CAN/CSA C22.2 No.14 IEC/EN 63000 IEC/EN 61812-1 UL 508

## Technical UL/CSA

Maximum Operating Voltage UL/CSA	Output Circuit 300 V AC
Contact Rating UL/CSA	C300
Connecting Capacity UL/CSA	Flexible 1x 18-14 AWG Flexible 2x 18-16 AWG Rigid 1x 20-12 AWG Rigid 2x 20-16 AWG
Tightening Torque UL/CSA	4.43 ... 7.08 in·lb

---

**Environmental**


---

Ambient Air Temperature	Operation -20 ... +60 °C Storage -40 ... +85 °C
RoHS Status	Following EU Directive 2011/65/EU

---



---

**Certificates and Declarations (Document Number)**


---

CB Certificate	CB_DK-8574
CCC Certificate	CCC_2019010303150608
CQC Certificate	CQC2019010303150608
cULus Certificate	cULus_20031209-E140448
Data Sheet, Technical Information	2CDC110004C0210_01
Declaration of Conformity - CCC	2020980303000209
Declaration of Conformity - CE	1SVD981010-00
Declaration of Conformity - UKCA	1SVD981010-10
EAC Certificate	EAC_RU_C-DE.ME77.B.00568/20
Instructions and Manuals	1SVC500010M0000
RMRS Certificate	RMRS_1740021250
RoHS Information	1SVD981010-00

---



---

**Container Information**


---

Package Level 1 Units	box 1 piece
Package Level 1 Width	89 mm
Package Level 1 Depth / Length	20 mm
Package Level 1 Height	65 mm
Package Level 1 Gross Weight	0.065 kg
Package Level 1 EAN	4013614350634

---



---

**Classifications**


---

Object Classification Code	K
ETIM 4	EC001439 - Timer relay
ETIM 5	EC001439 - Timer relay
ETIM 6	EC001439 - Timer relay
ETIM 7	EC001439 - Timer relay
eClass	V11.0 : 27371605
UNSPSC	39121519
E-Number (Finland)	2712639
E-Number (Sweden)	4033001

---

---

## Categories

---

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Time Relays → CT-D

