


LQM18FN2R2M00#

" # " indicates a package specification code.



< List of part numbers with package codes >
 LQM18FN2R2M00D , LQM18FN2R2M00J , LQM18FN2R2M00B

Shape



L size	1.6 ± 0.1mm
W size	0.8 ± 0.1mm
T size	0.8 ± 0.1mm
Size code in inch (mm)	0603 (1608)

References

Packaging code	Specifications	Minimum quantity
D	180mm Paper taping	4000
J	330mm Paper taping	10000
B	Packing in bulk	1000

Mass (Typ.)	
1 piece	0.005g


Specifications

Inductance	2.2μH ± 20%
Inductance test frequency	1MHz
Rated current (I _{sat}) (Based on Inductance change)	120mA
Rated current (I _{temp}) (Based on Temperature rise)	120mA
Max. of DC resistance	0.52
Avg. of DC resistance	0.40 ± 30%
Self resonance frequency (min.)	80MHz
Operating temperature range (Self-temperature rise is not included)	-55 ~ 125
Class of magnetic shield	Magnetic shield of ferrite


⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ' s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

▪ Inductance-Current characteristics (Typ.)



▪ Impedance-Frequency characteristics (Typ.)



This PDF data has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.