

RG58A/U COAXIAL CABLE

<b>Construction Inspection</b>	
Inner conductor	19*0.18mm BARE COPPER
Dielectric	2.95±0.05mm Solid PE
1'st shield	Bonded AL-foil
2'nd shield	112*0.12mm BARE COPPER
Coverage rate	90%
Jacket	5.0±0.05mm PVC
Jacket Color	Black/White
<b>Electrical Inspection</b>	
Inner conductor DC resistance	≤99Ω/km
Sparker Test(vac)	3000
Impedance	50±2Ω
Capacitance	55±3 pF/m
SRL	5-300MHz ≧ 20Db, 300-1000MHz ≧ 18Db,
<b>Attenuation [ @68° F.(20°C) ]</b>	
Frequency(MHz)	(dB/100m)
50	14.8
200	28.90
400	33.50
900	61.20
1000	67.96