



PCB terminal block

Rated current: 10 A

Rated voltage: 300 V

Wire range: 24-18 AWG

Pitch: 3.5 mm/3.96 mm

Mounting: Wave soldering



For reference only!version1.0

UL/CUL

Use Group	B	C	D
Rate Voltage [V]	300	-	-
Rated Current [A]	10	-	-
Wire Range [AWG]	24~18		
Dielectric Voltage-Withstand	1.6KV		

IEC

Overvoltage Category	III	III	II
Contamination Class	3	2	2
Rated Voltage [V]	160	250	320
Rated Current [A]	13.5	13.5	13.5
Impulse withstand voltage [KV]	2.5	2.5	2.5
Conductor cross section[solid/flexible] [mm²]	0.5~1.0		

Material

Insulation Material	PA66
Flame retardant rating	UL94V-0
Conductor Material	Copper alloy
Plating of conductor surface	Sn plated

Other Data

Pitch/Poles [mm]/[P]	3.5 , 3.96/2~24
Stripping Length [mm]	5~6
Screw/Torque(Max)[N.m]	M2/0.2
Operating temperature [°C]	-40~+105
Soldering temperature	260°C/5S
Pin dimensions [mm]	Ø0.8
PCB Hole Diameter [mm]	Ø1.0

Dimensions

PCB opening diagram

