

# MY510

## FEED THROUGH TERMINAL BLOCK



For reference only!version1.0

### UL/CUL

Use Group	B	C	D
Rate Voltage [V]	300	300	300
Rated Current [A]	15	15	10
Wire Range [AWG]	22-14		
Dielectric Voltage-Withstand	1.6KV		

### IEC

Overvoltage Category	III	III	II
Contamination Class	3	2	2
Rated Voltage [V]	-	250	-
Rated Current [A]	-	6.3	-
Impulse withstand voltage [KV]	-	2	-
Conductor cross section[solid/flexible] [mm²]	0.2-2.5		

### Material

Insulation Material	PA66
Flame retardant rating	UL94V-0

Conductor Material	Copper alloy
Plating of conductor surface	Ni plated

### Other Data

Pitch/Poles [mm]/[P]	2-5
Stripping Length [mm]	7-8
Screw/Torque(Max)[N.m]	M3/0.5
Operating temperature [°C]	-40~+105
Soldering temperature	/
Pin dimensions [mm]	/
PCB Hole Diameter [mm]	/

### Dimensions

