


1487594-2 ✓ ACTIVE

TE Internal #: 1487594-2

USB 4-Position Plug, Type A to Type B Cable Assembly, Black
Cable, USB Type A Plug End A, USB Type B Plug End B, Double
Ended, 28 AWG

[View on TE.com >](#)



Cable Assembly Type: **USB 4-Position Plug, Type A to Type B**

Cable Color: **Black**

Cable Assembly (End A): **USB Type A Plug**

Cable Assembly (End B): **USB Type B Plug**

Cable Assembly Configuration: **Double Ended**

Features

Configuration Features

Number of Positions	4
---------------------	---

Operation/Application

Shielded	Yes
----------	-----

Body Features

Equalized	No
Cable Color	Black

Product Type Features

Cable Assembly Type	USB 4-Position Plug, Type A to Type B
Cable Assembly (End A)	USB Type A Plug
Cable Assembly (End B)	USB Type B Plug

Other

Cable Assembly Configuration	Double Ended
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Dimensions



Wire Size	28 AWG
-----------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5787617-1
RECP ASSY, R/A, STACKED, THRU-HOLE, USB,



TE Part # 1487594-1
USB, A-B, 28/28, BLACK, 0.5M




TE Part # 1734366-1
Std USB Type A, VT, T/H



TE Part # 292336-1
Std USB Type A, Flag, T/H



Customers Also Bought



Documents

Product Drawings

USB, A-B, 28/28, BLACK, 0.25M

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1487594-2_H.2d_dxf.zip

1487594-2

USB 4-Position Plug, Type A to Type B Cable Assembly, Black Cable, USB Type A Plug End A, USB Type B Plug End B, Double Ended, 28 AWG



English

Customer View Model

[ENG_CVM_CVM_1487594-2_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1487594-2_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.