

# FORTEX

## A3 AND A2 LIGHTBOXES (LP-0330-01 & LP-0650-01)



The Fortex range of LED Light Pad Boxes are professional high quality aids giving superior contrast and even spread of light from the back lights making them invaluable for ease of artwork preparation, tracing designs and patterns for stencilling and displaying slides and transparencies and also inspection.

The LED light source creates a soft and uniform light without creating shadows or dark spots. No heat is generated from the luminaires like a conventional light box. The surface of the light pad is completely flush. These Lightboxes are super thin and are only 8 mm in depth.

The Light pads have LED backlights giving a 6500K Daylight correlated colour temperature, and provide an even spread of light from edge to edge. They are supplied with Four Artwork retaining clips. The light pads can be used in both Landscape or Portrait Modes.

The light boxes are portable and easy to use are available in two sizes – A3 or A2 size.

### Product Model Data

MODELS	LP-0650-01	LP0-330-01
	A2 (420 x 594mm)	A3 (297 x 420mm)
FRAME COLOR	BLACK/WHITE	
SURFACE	PLASTIC	PLASTIC
THICKNESS	8mm	8mm
POWER ADAPTER	AC 110-240V 50-60HZ TO DC 12V 1A	AC 110-240V 50-60HZ TO DC 12V 1A
RATED POWER	12W	9W
LUX	361 Lumens	356 Lumens
LIGHT SOURCE	LED	LED
NET WEIGHT	2.5KG	1.2KG



## **Instructions for Use**

### **IMPORTANT**

This Product is not a toy

### **USER ADVICE**

Keep all packaging until after a successful installation and retain instruction for future use.

### **LOCATION**

Indoor use only

The lamp must be situated on a flat stable surface

This product should be placed in a location where it cannot present a hazard or be knocked over

### **OPERATION**

Attach the supply cable to the socket in the side of the base

Connect the plug into the mains socket outlet (Ensure the cable does not present a tripping hazard)

Take care when using or moving the metal artwork retaining clips not to scratch/damage the light pad

WARNING Do not open the unit there are no user serviceable parts inside.

### **SAFETY INFORMATION**

If the supply cord is damaged it shall be replaced by a special cord or cable exclusively available from the service agent.

Indoor use only. Do not operate in areas exposed to moisture.

Switch OFF when not in use.

Only use with the adapter supplied.

Only clean with a soft cloth, do not use abrasive cleaners.

The bulbs used are LED and are none replaceable.