34420A NanoVolt/Micro-Ohm Meter

RoHS compliant

(Serial Number MY61000101 & SG61000101 onwards)



Nanovolt Performance at a Microvolt Price

The Keysight Technologies 34420A nanoVolt/micro-Ohm meter is a high-sensitivity multimeter optimized for performing low-level measurements. It combines low-noise voltage measurements with resistance and temperature functions, setting a new standard in low-level flexibility and performance.

Take the Uncertainty Out of Your Low-Level Measurements

Low-noise input amplifiers and a highly tuned input protection scheme bring reading noise down to 8 nVpp. Combine this with 71/2 digits of resolution, selectable analog and digital filtering, 2 ppm basic 24-hour dcV accuracy, and a shielded, copper pin connector and you've got accurate, repeatable measurements you can count on.

Two Input Channels

An integral two-channel programmable scanner simplifies voltage comparisons. Built-in ratio and difference functions enable automated two channel measurements without the need for an external nanoVolt scanner. Both channels share the same low noise specifications to ensure accurate comparisons.

Built-in Resistance and Temperature

The 34420A combines its low-noise nano-Volt input circuits with a high-stability current source to provide precise low-level resistance measurements – no more hassling with the cost and complexity of an external current source. Three resistance modes are included:

- Standard
- Low-power
- Voltage-limited for dry-circuit testing

Offset compensation is also provided to minimize thermal EMFs and associated errors.



Features

- 71/2 digit resolution
- 100 pV, 100 nΩ sensitivity
- 1.3 nVrms, 8 nVpp noise performance
- Built-in low noise 2 channel scanner
- Direct SPRT, RTD, Thermistor, and Thermocouple



SPRT Measurements

Built-in ITS-90 conversion routines accept the calibration coefficients from your SPRT probe for direct temperature measurement and conversion. Thermocouples, thermistors, and RTDs are also supported.

Unequaled Versatility

The 34420A gives you the versatility to tackle your most challenging tasks, both on the benchtop and in your automated system. Standard features include RS-232 and GPIB interfaces, SCPI and Keithley 181 programming language, 1024-reading memory, scaling and statistics, and a chart recorder analog output.

Quality You Can Count On

The 34420A gives you the quality and reliability you expect from Keysight Technologies. From the Keysight proven > 150,000 hour Mean Time Between Failure, to its standard 1-year warranty, Keysight stands behind you to bring a new level of confidence to your low-level measurements.

BenchVue Software (now included)

Data capture simplified. Click. Capture. Done.

BenchVue software for the PC makes it simple to connect, control, capture and view Keysight's DMMs simultaneously with other Keysight bench instruments with no additional programming.

- · Visualize multiple measurements simultaneously
- Easily log data, screen shots and system state
- Rapidly prototype custom test sequences
- · Recall past state of your bench to replicate results
- Export measurement data in desired format fast
- · Quickly access manuals, drivers, FAQs and videos
- Monitor and control bench from mobile devices

The Digital Multimeter App within BenchVue enables control of digital multimeters to visualize measurements, perform unrestricted data logging and statistical analysis.

Benefit from a new perspective by visualizing multiple DMM's at the same time

Display single measurements, charts, tables, or histograms from a single instrument or multiple DMMs simultaneously to correlate trends you might otherwise miss.

Record measurements and export results in a few clicks

Log and export data quickly to popular tools such as Microsoft Excel, Microsoft Word and MATLAB for documentation or further analysis.

Access and control tests on your DMM remotely

With the companion BenchVue Mobile app, monitor and respond to long-running tests from anywhere. Download BenchVue software at no cost today www.keysight.com/find/benchvue



Figure 1. See your measurements across instruments in one place to quickly correlate measurement activities and obtain actionable insights.



Figure 2. BenchVue enables control of your DMM to data log and visualize measurements in a wide array of display options.

Specifications

Accuracy specifications ± (% of reading + % of range) 1

| Function | Range ² | Test current | 24-hour 23 °C ± 1 °C | 90 day 23 °C ± 5 °C | 1 year 23 °C ± 5 °C | Temperature coefficient 28 °C to 55 °C | Maximum per lead resistance |
|---|---|-----------------------------|--------------------------|------------------------|------------------------|--|-----------------------------|
| DC voltage | 1.0000000 mV ³ | | 0.0025 + .0020 | 0.0040 + .0020 | 0.0050 + .0020 | 0.0004 + .0001 | |
| | 10.000000 mV ³ | | 0.0025 + .0020 | 0.0040 + .0002 | 0.0050 + .0003 | 0.0004 + .0001 | |
| | 100.00000 mV | | 0.0015 + .0003 | 0.0030 + .0004 | 0.0040 + .0004 | 0.0004 + .00006 | |
| | 1.0000000 V | | 0.0010 + .0003 | 0.0025 + .0004 | 0.0035 + .0004 | 0.0004 + .00004 | |
| | 10.000000 V | | 0.0002 + .0001 | 0.0020 + .0004 | 0.0030 + .0004 | 0.0001 + .00002 | |
| | 100.00000 V ⁴ | | 0.0010 + .0004 | 0.0025 + .0005 | 0.0035 + .0005 | 0.0004 + .00005 | |
| Resistance 5 | 1.0000000 Ω | 10 mA | 0.0015 + .0002 | 0.0050 + .0002 | 0.0070 + .0002 | 0.0005 + .00002 | 1 Ω |
| | 10.000000 Ω | 10 mA | 0.0015 + .0002 | 0.0040 + .0002 | 0.0060 + .0002 | 0.0005 + .00001 | 1 Ω |
| | 100.00000 Ω | 10 mA | 0.0015 + .0002 | 0.0040 + .0002 | 0.0060 + .0002 | 0.0005 + .00001 | 10 Ω |
| | 1.0000000 kΩ | 1 mA | 0.0015 + .0002 | 0.0040 + .0002 | 0.0060 + .0002 | 0.0005 + .00001 | 100 Ω |
| | 10.000000 kΩ | 100 μΑ | 0.0015 + .0002 | 0.0040 + .0002 | 0.0060 + .0002 | 0.0005 + .00001 | 1 ΚΩ |
| | 100.00000 kΩ | 10 μΑ | 0.0015 + .0003 | 0.0040 + .0004 | 0.0060 + .0004 | 0.0005 + .00002 | 1 ΚΩ |
| | 1.0000000 MΩ | 5 μΑ | 0.0020 + .0003 | 0.0050 + .0004 | 0.0070 + .0004 | 0.0006 + .00003 | 1 ΚΩ |
| Low power | 1.0000000 Ω | 10 mA | 0.0015 + .0002 | 0.0050 + .0002 | 0.0070 + .0002 | 0.0005 + .00002 | 1 Ω |
| resistance 5 | 10.000000 Ω | 10 mA | 0.0015 + .0002 | 0.0040 + .0002 | 0.0060 + .0002 | 0.0005 + .00001 | 1 Ω |
| | 100.00000 Ω | 1 mA | 0.0015 + .0002 | 0.0040 + .0002 | 0.0060 + .0002 | 0.0005 + .00001 | 10 Ω |
| | 1.0000000 kΩ | 100 μΑ | 0.0015 + .0002 | 0.0040 + .0002 | 0.0060 + .0002 | 0.0005 + .00001 | 100 Ω |
| | 10.000000 kΩ | 10 μΑ | 0.0015 + .0004 | 0.0040 + .0004 | 0.0060 + .0004 | 0.0005 + .00001 | 1 ΚΩ |
| | 100.00000 kΩ | 5 μΑ | 0.0015 + .0012 | 0.0040 + .0015 | 0.0060 + .0015 | 0.0005 + .00003 | 1 ΚΩ |
| | 1.0000000 MΩ | 5 μΑ | 0.0020 + .0003 | 0.0050 + .0004 | 0.0070 + .0004 | 0.0006 + .00003 | 1 ΚΩ |
| Voltage limited | 10.000000 Ω | 1 mA | 0.0020 + .0002 | 0.0050 + .0002 | 0.0070 + .0002 | 0.0005 + .00002 | 1 Ω |
| resistance 5, 6 | 100.00000 Ω | 100 μΑ | 0.0025 + .0002 | 0.0050 + .0002 | 0.0070 + .0002 | 0.0005 + .00002 | 5 Ω |
| Channel 1 / Channel 2 (DCV Ratio) | Ratio error in % = 0 | Channel 1 a | ccuracy in % + Channe | 2 accuracy in % | ' | | |
| Channel 1 - Channel 2 (DCV difference) | Difference error = 0 | Channel 1 (% | % of reading + % of rang | ge) + Channel 2 (% of | reading + % of range) | | |
| Temperature | Resolution = 0.001 | °C | | | | | |
| SPRT ⁷ RTD Thermistor Thermocouple ⁸ | SPRT probe accur RTD probe accura Thermistor probe a Thermocouple prol | cy + 0.05°C accuracy + 0 | .1 °C | | | | |

^{1.} Specifications are for Channel 1 or Channel 2, after 2-hour warm-up, resolution at 7.5 digits (100 NPLC), with FILTERS off. RESISTANCE specifications are for 4-wire ohms or 2-wire ohms using Null. Without Null, add 0.2 Ohms additional error in 2-wire Ohms function. With Analog Filter ON, add 0.002% of reading to listed specifications.

2. 20% overrange on all ranges except 5% on Voltage Limited Resistance. 3. After using Null. If Null is not used add 100 nanoVolts.

^{4.} Channel 1 only.

Channel 1 only.
 Channel 1 only. Resistance measurements, for NPLC < 1, add 160 μΩ RMS noise.
 Voltage limit can be set to 20 mV (default), 100 mV, or 500 mV. Measured resistance plus Channel 1 HI and LO lead resistance is limited to 10.5 Ω on the 10 Ω range and 105 Ω on the 100 Ω range.
 For 25 Ω SPRT with triple-point of water check within the last 4 hours. Without the triple-point of water check, add 0.013 °C for 24 hours, add 0.035 °C for 90 day, and add 0.055 °C for 1 year specifications.
 For fixed reference junction. Add 0.3 °C for external reference junction, add 2.0 ûC for internal reference junction.

DC voltage noise ¹

| Observational period | | | |
|----------------------|--------------------|--------------------------|-------------------------|
| Range | 2-minute RMS noise | 2-minute peak-peak noise | 24-hour peak-peak noise |
| 1 mV | 1.3 nVrms | 8 nVpp | 12 nVpp |
| 10 mV | 1.5 nVrms | 10 nVpp | 14 nVpp |
| 100 mV | 10 nVrms | 65 nVpp | 80 nVpp |
| 1 V | 100 nVrms | 650 nVpp | 800 nVpp |
| 10 V | 450 nVrms | 3 µVрр | 3.7 µVpp |
| 100 V | 11 μVrms | 75 μVpp | 90 μVpp |

DC voltage noise vs source resistance ²

| Source resistance | Noise | Analog filter | Digital filter |
|-------------------|-----------|---------------|----------------|
| 0 Ω | 1.3 nVrms | Off | Med |
| 100 Ω | 1.7 nVrms | Off | Med |
| 1 kΩ | 4 nVrms | Off | Med |
| 10 kΩ | 13 nVrms | Off | Med |
| 100 kΩ | 41 nVrms | On | Med |
| 1 ΜΩ | 90 nVrms | On | Slow |

After a 2-hour warm-up, ± 1 °C, 6.5 digits (10 PLC) with Analog Filter Off and Digital Filter Medium (50 reading average).
 2-minute rms and 24-hour noise typical. For measurements using 0.02 or 0.2 NPLC, add 800 nV rms noise.
 Typical noise behavior for Ch 1 or Ch 2, after 2 hour warm-up, 6.5 digits (10 PLC), 2 minute observation period on 1 mV range. For peak-to-peak noise, multiply rms noise by 6.

Measurement Characteristics

| DC voltage | | | |
|-----------------------------|--|--|--|
| Measurement method | Continuously integrating multi-slope III | | |
| | A-D Converter | | |
| A-D linearity | 0.00008% of reading + 0.00005% of range | | |
| Input resistance | 100 V (Ch1 only): 10 M Ω ± 1% | | |
| | 1 mV through 10 V: > 10 GΩ, in parallel with < 3.6 nF | | |
| Input bias current | < 50 pA at 25 °C | | |
| Injected current | < 50 nA pp at 50 or 60 Hz | | |
| Input protection | 150 V peak any input terminal to Channel 1 LO, continuous | | |
| | Channel-to-channel switching error (typical): 3 nV | | |
| Channel isolation | Isolation between input channels > $10^{10} \Omega$ | | |
| Earth isolation | 350 V peak any input terminal to earth | | |
| | Impedance from any input terminal to earth is > 10 GΩ and < 400 pF | | |
| Maximum voltage | Channel 1 LO to Channel 2 LO, 150 V peak | | |
| Resistance | | | |
| Measurement method | Selectable 4-wire or 2-wire ohms | | |
| | Current source referenced to Channel 1 LO input | | |
| Offset compensation | Used on all ranges except 100 k Ω and 1 M Ω | | |
| | Can be turned off if desired | | |
| Protection | 150 V peak | | |
| Open circuit voltage | For resistance and low power resistance | | |
| | < 14 V. 20 mV, 100 mV, 500 mV selectable clamp | | |
| Temperature | | | |
| SPRT | ITS-90 calibrated temperature with the range of –190 °C to +660 °C | | |
| Thermocouple | Type B, E, J, K, N, R, S, T Range: -210° C to 1820° C | | |
| Thermistor | 5 kΩ Range: -80° C to 150° C | | |
| RTD | 4-wire, 4.9 W to 2.1 kW | | |
| | types: | | |
| | a = .00385 (DIN/IEC 751) | | |
| | and a = .00391 | | |
| Measurement noise rejection | Range: -200° C to 850° C | | |
| dc CMRR | 140 dB | | |
| ac CMRR | 70 dB | | |
| ac Civirk | 10 UD | | |

^{1.} For 1 $k\Omega$ unbalanced in LO lead.

Operating Characteristics ¹

| Function | Digits | Integration time | Readings/s ² | |
|------------------|--------|------------------|-------------------------|--|
| DCV thermocouple | 7.5 | 200 plc | .15 (.125) | |
| | 7.5 | 100 plc | .3 (.25) | |
| | 6.5 | 20 plc | .1.5 (1.25) | |
| | 6.5 | 10 plc | 3 (2.5) | |
| | 5.5 | 1 plc | 25 (20.8) | |
| | 5.5 | 0.2 plc | 100 (100) | |
| | 4.5 | 0.02 plc | 250 (250) | |
| Resistance | 7.5 | 200 plc | .075 (.062) | |
| DCV1/DCV2 | 7.5 | 100 plc | .15 (.125) | |
| DCV 1-2 | 6.5 | 20 plc | .75 (.625) | |
| RTD | 6.5 | 10 plc | 1.5 (1.25) | |
| Thermistor | 5.5 | 1 plc | 12.5 (10.4) | |
| | 5.5 | 0.2 plc | 50 (50) | |
| | 4.5 | 0.02 plc | 125 (125) | |

Speeds are for delay 0, Display OFF, Filters OFF, Offset Compensation OFF.
 Reading speeds for 60 Hz or (50 Hz), 100 mV through 100 V ranges. 1 mV range 30/s MAX, 10 mV range 170/s MAX, thermocouple 120/s MAX.

Operating Characteristics ¹ (continued)

| Integration time | Normal mode rejection ² |
|------------------------------------|---|
| 200 plc/3.335 s (4 s) | 110 dB ³ |
| 100 plc/1.675 s (2 s) | 105 dB ³ |
| 20 plc/334 ms (400 ms) | 100 dB ³ |
| 10 plc/167 ms (200 ms) | 95 dB ³ |
| 2 plc/33.3 ms (40 ms) | 90 dB |
| 1 plc/16.7 ms (20 ms) | 60 dB |
| < 1 plc | 0 |
| System speeds ⁴ | |
| Configuration rates | 26/s to 50/s |
| Autorange rate (Volts) | > 30/s |
| ASCII reading to RS-232 | 55/s |
| ASCII reading to GPIB | 250/s |
| Max. internal trigger rate | 250/s |
| Max. ext. trig. rate to memory | 250/s |
| Triggering and memory | |
| Reading HOLD sensitivity | 10%, 1%, 0.1%, or 0.01% of range |
| Samples/Trigger | 1 to 50,000 |
| Trigger delay | 0 to 3600 s; 10 μs step size |
| External trigger delay | <1 ms |
| External trigger jitter | < 500 μs |
| Memory | 1024 readings |
| Math functions | |
| NULL | Channel 1 dcV, Channel 2 dcV, Difference, Resistance, Temperature |
| STATS | Min, Max, Average, Peak-Peak, Standard Deviation, Number of readings |
| SCALE | Allows linear scaling as y = mx+b |
| CHART NULL | Establishes zero for rear panel output |
| Filter (Analog or digital or both) | |
| Analog | Low pass 2 pole at 13 Hz, available for dcV on 1 mV, 10 mV, 100 mV range |
| Digital | Moving average filter, 10 (fast), 50 (medium), or 100 (slow) reading averages |
| Chart Out (Analog out) | |
| Maximum output | ± 3 V |
| Resolution | 16 bits |
| Accuracy | ± 0.1% of output + 1 mV |
| Output resistance | $1 \text{ k}\Omega \pm 5\%$ |
| Update rate | Once per reading |
| Span and offset | Adjustable |
| Standard programming languages | |
| SCPI (IEEE 488.2), Keithley 181 | |
| Accessories included | |

4 ft low thermal cable with copper spade lugs, Kelvin clip set, 4-wire shorting plug, user's manual, service manual, test report, contact cleaner, and power

- 1. For 1 $k\Omega$ unbalanced in LO lead.
- 2. For power line frequency ± 0.1%, Filters OFF. For Digital Filter slow add 20 db, for medium or fast add 10 db for NPLC ≥ 1.

 3. For power line frequency ± 1%, use 80 db, for ± 3% use 60 db.

 4. Speeds are for NPLC 0.02, Delay 0, Display OFF, Chart Out OFF.

General Specifications

| Options | Description | |
|------------------------|--|--|
| Front panel connection | Shielded, low thermal, 99% copper contacts | |
| Power supply | 100 V/120 V/220 V (230 V)/240 V ± 10% | |
| Power line frequency | 45 Hz to 66 Hz and 360 Hz to 440 Hz | |
| | Automatically sensed at power-on | |
| Power consumption | 25 VA peak (10 W average) | |
| Operating environment | Full accuracy for 0 °C to 55 °C | |
| | Full accuracy to 80% RH at 40 °C (non condensing) | |
| | Full accuracy to 40% RH for 41 °C to 55 °C (non-condensing) | |
| | Pollution Degree 2 | |
| Storage environment | −40 °C to 75 °C | |
| Size | 254.4 mm W x 374.0 mm L x 103.6 mm H (10.02" W x 14.72" L x 4.08" H) | |
| Weight | 3 kg (6.5 lbs) | |
| Safety and EMC | Refer to Declaration of Conformity for the latest revisions of | |
| | regulatory compliance at: www.keysight.com/go/conformity | |

Ordering Information

Includes low thermal input cable (34102A), low thermal shorting plug (34103A), Kelvin clip set (11062A), calibration certificate, power cord.

| Options | Description |
|------------|---------------------------------|
| 34420A-A6J | ANSI Z540 compliant calibration |

Accessories

| Options | Description |
|---------|--|
| 34102A | Low-thermal input cable (four conductor) with copper spade lugs |
| 34103A | Low-thermal shorting plug |
| 34104A | Low-thermal input connector |
| 34131A | Transit case |
| 34161A | Accessory pouch |
| 34190A | Rackmount Kit: Designed for use with only one instrument, mounted on either the left or the right |
| | side of the rack. |
| 34191A | 2U Dual Flange Kit: Secures the instrument to the front of the rack. This kit can be used with the |
| | instrument to the front of the rack. |
| 34194A | Dual Lock Link Kit: Recommended for side-by-side combinations and includes links for |
| | instruments of different depths. This kit can be used with the 34191A 2U Dual Flange Kit to |
| | mount two half-width, 2U height instruments side-by-side. |

Learn more at: www.keysight.com

For more information on Keysight Technologies' products, applications, or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Keysight: 34420A