



Permanent Magnets & Assemblies
Materials & Parts

Cores & Components

Applications

- Chokes
- Transformers
- Current Transformers
- Current Sensors / Transducers

Cores

Markets

Home > Products > Cores & Components > Applications > Cores
> VITROPERM Standard types, encapsulated



NANOCRYSTALLINE VITROPERM CORES IN PLASTIC CASING FOR COMMON MODE CHOKES

Common Mode Chokes with toroidal tape wound cores of VITROPERM® allow the effective attenuation of asymmetrical and conducted high frequency noise. The high permeability of the nanocrystalline core material achieves superior characteristics at low and middle frequencies, as well as in the high frequency range, when an optimized winding arrangement is chosen. In comparison to conventional ferrite, advantages over the entire frequency range are obtained. Further information is available in our application note → [EMC Products based on Nanocrystalline VITROPERM](#)

Our VITROPERM cores are available with different A_L -levels for many core sizes. Thus, saturation-resistant solutions are available for various fields of applications. If the common mode currents exceed the saturation currents (I_{cm}) of the cores or chokes, cores with higher saturation resistance must be used. High A_L values (high μ) are more suitable for typical single-phase applications with low unbalanced current (e.g. switched-mode power supplies), while cores with lower A_L values are often used in 3-phase applications with high unbalanced currents (e.g. frequency converters with long motor cables).

The plastic cases are suitable for direct winding and offer good mechanical protection of the nanocrystalline core material. This enables the best magnetic properties and highest permeability levels to be maintained. Additional winding protection is optional for heavy wire windings, where there may be a danger of core damage. The plastic materials comply with the standards UL94-V0 (UL file number: E41871), class B (130 °C) and UL94-V0 (UL file number E41938), class F (155 °C).

Epoxy coated designs are listed in the table → [Nanocrystalline VITROPERM cores with epoxy coating](#).

We recommend to examine the theoretical calculations experimentally. For testing purposes VAC offers a special sample kit consisting of selected cores → [Core Sample Kit VITROPERM](#).

The main areas of application are:

- _ EMC filters
- _ Switched-mode power supplies (SMPS), Power supplies
- _ Solar inverters
- _ Uninterruptible power supplies (UPS)
- _ Welding equipment
- _ Wind generators
- _ Frequency converters
- _ Inductive cooking

VAC-product	nominal core dimensions	limiting dimensions (incl. case)			iron cross section	mean path length	weight	A_L nominal		saturation current I_{cm}^{**} , typical				
		OD	ID	H				A_{Fe}	l_{Fe}	m_{Fe}	10 kHz	100 kHz	10 kHz	100 kHz
		mm	mm	mm				cm ²	cm	g	μH	μH	A	A
T60006-L2009-W914	9.8 x 6.5 x 4.5	11.2	5.1	5.8	0.06	2.6	1.1	25.5	6.4	0.14	0.3			
T60006-L2012-W902	12 x 8 x 4.5	14.1	6.6	6.3	0.07	3.1	1.7	28.0	6.8	0.15	0.31			
T60006-L2012-W498	12.5 x 10 x 5	14.3	8.5	7.0	0.05	3.5	1.3	10.0	3.6	0.3	0.56			
T60006-L2014-V098	14.4 x 11.4 x 3.2	16.5	9.6	5.0	0.04	4.1	1.1	10.5	2.6	0.21	0.44			
T60006-L2015-W865	15 x 10 x 4.5	17.1	7.9	6.5	0.09	3.9	2.6	27.0	6.7	0.2	0.41			
T60006-L2016-W403	16 x 10 x 6	17.9	8.1	8.1	0.14	4.1	4.0	43.0	10.1	0.2	0.41			
T60006-L2016-W308								11.7	6.5	1.2	1.7			
T60006-L2016-V165								2.1	2.0	5.4	5.7			
T60006-L2017-W515	17.5 x 12.6 x 6	19.2	10.9	8.1	0.12	4.7	4.1	30.0	6.9	0.23	0.48			
T60006-L2019-V184	19 x 15 x 5	21.2	13.0	7.3	0.08	5.3	3.1	18.0	4.4	0.26	0.54			
T60006-L2019-W838	19 x 15 x 10	21.2	13.0	12.3	0.16	5.3	6.3	36.1	8.8	0.26	0.54			
T60006-L2020-W409	20 x 12.5 x 8	22.6	10.3	10.2	0.24	5.1	9.0	55.2	13.6	0.25	0.51			
T60006-L2020-W450								14.3	9.1	1.5	2.2			
T60006-L2025-W523	25 x 20 x 10	27.6	17.4	12.8	0.20	7.1	10.0	28.4	7.3	0.41	0.84			
T60006-L2025-W380	25 x 16 x 10	27.9	13.6	12.5	0.4	6.4	17.0	67.0	15.5	0.32	0.65			
T60006-L2025-W451								17.1	11.5	1.8	2.7			
T60006-L2025-V349								8.6	7.6	3.6	4.1			
T60006-L2025-W980								3.2	3.1	9.3	9.6			
T60006-L2030-W423	30 x 20 x 10	32.8	17.6	12.5	0.40	7.9	23.0	59.3	14.0	0.5	1.0			
T60006-L2030-W358								15.5	11.1	2.1	3.1			
T60006-L2030-W981								2.9	2.8	11.4	11.8			
T60006-L2030-W514	30 x 20 x 15	32.8	17.5	17.8	0.57	7.9	33.0	88.0	20.0	0.38	0.79			
T60006-L2030-V188								26.9	16.2	1.8	2.8			
T60006-L2030-V129								15.7	14.1	3.1	3.9			
T60006-L2040-W422	40 x 32 x 15	43.1	28.7	18.5	0.46	11.3	38.0	48.0	11.3	0.55	1.1			
T60006-L2040-V113								13.0	8.4	3.0	4.6			
T60006-L2040-W452								10.2	7.9	3.8	5.2			
T60006-L2040-W964								2.3	2.2	17.0	17.0			
T60006-L2040-W424								99.0	23.1	0.5	1.0			
T60006-L2040-W453	40 x 25 x 15	43.1	22.5	18.5	0.9	10.2	64.0	25.0	28.2	2.9	4.4			

T60006-L2040-V296									12.8	11.3	5.7	6.5							
T60006-L2045-V102	45 x 30 x 15	48.3	26.4	18.2	0.86	11.8	74.0	87.6	20.0	0.59	1.2								
T60006-L2045-V118								24.3	15.8	3.0	4.6								
T60006-L2045-V101								15.7	14.1	4.6	5.9								
T60006-L2050-W516	50 x 40 x 20	53.5	36.3	23.4	0.76	14.1	79.0	45.0	13.5	1.0	2.0								
T60006-L2050-W565			36.6					18.0	10.0	3.6	5.5								
T60006-L2050-V146								11.7	10.0	5.5	7.1								
T60006-L2050-V166								3.1	3.0	20.0	21.0								
T60006-L2054-V172	54 x 40 x 20	57.5	37.7	24.1	1.06	14.8	115	87.0	19.9	0.72	1.5								
T60006-L2054-V178								24.0	15.7	3.7	5.8								
T60006-L2063-W517	63 x 50 x 25	67.3	46.5	28.6	1.2	17.8	161	59.0	17.5	1.2	2.5								
T60006-L2063-V110								23.3	13.8	4.5	6.9								
T60006-L2063-V144								163	15.1	13.5	6.9	8.9							
T60006-L2063-V348									10.6	9.3	9.9	11.0							
T60006-L2063-W985									3.3	3.2	30.0	31.0							
T60006-L2080-V140	80 x 50 x 20	85.8	44.6	25.5	2.3	20.4	342	94.0	28.0	1.4	2.8								
T60006-L2080-W531								86.0	44.7	25.7	35.0	24.0	5.5	8.4					
T60006-L2080-V091											347	9.6	9.2	26.0	28.0				
T60006-L2090-W518											395	81.0	25.1	1.7	3.3				
T60006-L2090-V173	90 x 60 x 20	95.4	54.7	24.7	2.3	23.6	400	32.5	21.1	5.9	9.1								
T60006-L2090-W984								4.6	4.5	41.0	42.0								
T60006-L2100-V082								100 x 80 x 25	105.5	75.0	29.6	1.9	28.3	379	56.3	16.9	2.0	3.9	
T60006-L2100-V081	14.6	13.1	11.0	14.0															
T60006-L2102-W468	102 x 76 x 25	108.1	70.0	30.3	2.5	28.0	508	55.0	21.6	2.7	4.9								
T60006-L2102-V080								515	19.1	17.2	11.0	14.0							
T60006-L2063-V347									13.5	11.9	16.0	18.0							
T60006-L2102-W947									4.3	4.2	48.0	49.0							
T60006-L2160-V074									160 x 130 x 25	166.9	123.9	30.5	2.7	45.6	917	28.0	14.0	8.5	14.0
T60006-L2160-V088																20.0	13.1	11.0	18.0
T60006-L2160-V066	13.0	11.7	18.0	23.0															
T60006-L2160-V350	160 x 130 x 25	166.9	123.9	30.5	2.9	45.6	970	9.5	8.4	26.0	29.0								
T60006-L2160-W982								3.0	2.9	80.0	82.0								

A_L = inductance for N = 1 (tolerance +45 % / -25 %)

I_{cm} : the listed saturation currents are guidelines, only. They are calculated for nominal core dimensions at room temperature and for approx. 70 % saturation flux density.

Further information can be found here:

General information

→ [Application note \(brochure\)](#)

RoHS information

Nanocrystalline Cores

→ [Epoxy coated designs](#)

→ [Core Sample Kit VITROPERM](#)

→ [Core stack assemblies](#)

Common Mode Chokes

→ [Chokes](#)

CONTACT

Do you have general questions about our products?
We would be pleased to assist you!

→ [Email](#)

→ [Contact form](#)

Last update: 18.12.2018

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vacuumschmelze:](#)

[T60006-L2017-W515](#) [T60006-L2016-W403](#) [T60006-L2020-W409](#) [T60006-L2025-W380](#)